

■ PRODUCT CHARACTERISTICS

$V_{DSS}$	60V
$R_{DS(ON)}$ Typ(@ $V_{GS}=10V$ )	26m $\Omega$
$R_{DS(ON)}$ Typ(@ $V_{GS}=4.5V$ )	33m $\Omega$
$I_D$	30A

■ APPLICATIONS

- \* Motor Control
- \* High Performance SMPS
- \* DC/DC Converter

■ FEATURE

- \* Low Gate Charge
- \* Ultra-low RDS(ON)

■ ORDER INFORMATION

Order Codes		Package	Packing
Halogen-Free	Halogen		
N/A	MOT6525J	PDFN3X3	5000 pieces/Reel


■ ABSOLUTE MAXIMUM RATINGS( $T_A=25^{\circ}C$ , unless otherwise specified)

Parameter	Symbol	Ratings	Unit
Drain-Source Voltage	$V_{DSS}$	60	V
Gate-Source Voltage	$V_{GSS}$	$\pm 20$	V
Drain Current Continuous(@ $V_{GS}=10V, T_A=25^{\circ}C$ )	$I_D$	30	A
Drain Current Pulsed	$I_{DM}$	120	A
Avalanche Energy *	$E_{AS}$	60	mJ
Power Dissipation	$P_D$	50	W
Junction Temperature	$T_J$	+150	$^{\circ}C$
Storage Temperature	$T_{STG}$	-55~ +150	$^{\circ}C$

■ THERMAL CHARACTERISTICS

Parameter	Symbol	Typ	Unit
Junction to Case	$R_{thJC}$	2.5	$^{\circ}C/W$

Note: \* EAS condition:  $T_J=25^{\circ}C, V_{DD}=30V, V_G=10V, L=0.5mH, R_g=25\Omega$



**■ ELECTRICAL CHARACTERISTICS** ( $T_C=25^{\circ}\text{C}$ , unless otherwise noted)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Off characteristics						
Drain to Source Breakdown Voltage	$V_{DSS}$	$V_{GS}=0V, I_D=250\mu A$	60	-	-	V
Drain to Source Leakage Current	$I_{DSS}$	$V_{DS}=60V, V_{GS}=0V$	-	-	1	$\mu A$
Gate to Source Forward Leakage	$I_{GSS(F)}$	$V_{DS}=0V, V_{GS}=+20V$	-	-	100	nA
Gate to Source Reverse Leakage	$I_{GSS(R)}$	$V_{DS}=0V, V_{GS}=-20V$	-	-	-100	nA
On characteristics						
Drain to Source On-Resistance	$R_{DS(ON)}$	$V_{GS}=10V, I_D=20A$	-	26	29	$m\Omega$
		$V_{GS}=4.5V, I_D=20A$	-	33	40	$m\Omega$
Gate Threshold Voltage	$V_{GS(TH)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	1	1.6	2.5	V
Dynamic characteristics						
Gate capacitance	$R_g$	$V_{GS}=0V, V_{DS}=0V, f=1.0MHz$	-	1.4	-	$\Omega$
Forward Transconductance	$g_{fs}$	$V_{DS}=10V, I_D=2A$	-	5	-	S
Input Capacitance	$C_{iss}$	$V_{DS}=20V, V_{GS}=0V$ $f=1.0MHz$	-	1100	-	pF
Output Capacitance	$C_{oss}$		-	98	-	pF
Reverse Transfer Capacitance	$C_{rss}$		-	57	-	pF
Resistive Switching Characteristics						
Turn-on Delay Time	$t_{d(ON)}$	$I_D=30A, V_{DS}=30V$ $R_G=1.6\Omega, V_{GS}=10V$	-	4.8	-	ns
Rise Time	$t_r$		-	16.6	-	ns
Turn-off Delay Time	$t_{d(OFF)}$		-	28	-	ns
Fall Time	$t_f$		-	19	-	ns
Total Gate Charge	$Q_g$	$I_D=30A, V_{DS}=30V$ $V_{GS}=10V$	-	40	-	nC
Gate to Source Charge	$Q_{gs}$		-	8.4	-	nC
Gate to Drain("Miller") Charge	$Q_{gd}$		-	15	-	nC
Source-Drain Diode Characteristics						
Continuous Source Current(Body Diode)	$I_S$		-	-	30	A
Maximum Pulsed Current(Body Diode)	$I_{SM}$		-	-	120	A
Diode Forward Voltage	$V_{SD}$	$I_{SD}=1A, V_{GS}=0V$	-	0.74	1.2	V
Reverse Recovery Time	$t_{rr}$	$I_{SD}=30A, T_J=25^{\circ}\text{C}$ $di/dt=100A/\mu s$	-	32	-	ns
Reverse Recovery Charge	$Q_{rr}$		-	58	-	nC

■ TYPICAL CHARACTERISTICS




Figure 1: Drain current vs. drain-source voltage




Figure 2: Source current vs. source-drain voltage




Figure 3: Gate charge characteristics




Figure 4: Capacitance characteristics




Figure 5: Drain-source on-resistance vs. junction temperature




Figure 6: Break voltage vs. junction temperature

■ TYPICAL CHARACTERISTICS(Cont.)




Figure 7: Drain-source on-resistance vs. junction temperature




Figure 8: Drain-source on-resistance vs. drain current




Figure 9: Drain current vs. gate-source voltage




Figure 10: Drain current vs. junction temperature




Figure 11: Power dissipation vs. junction temperature








Figure 12: Safe operating safe

■ PDFN3X3 PACKAGE OUTLINE DIMENSIONS



Land Pattern  
(Only for Reference)



SYMBOL	DIMENSIONAL REQOMTS		
	MIN	NOM	MAX
A	0.70	0.75	0.80
b	0.25	0.30	0.35
c	0.10	0.15	0.25
D	3.25	3.35	3.45
D1	3.00	3.10	3.20
D2	1.78	1.88	1.98
D3	---	0.13	---
E	3.20	3.30	3.40
E1	3.00	3.15	3.20
E2	2.39	2.49	2.59
e	0.65BSC		
H	0.30	0.39	0.50
L	0.30	0.40	0.50
L1	---	0.13	---
θ	---	10°	12°
M	*	*	0.15
* Not specified			