


Description

The WPE0581D3H is designed to protect voltage sensitive components from ESD and transient voltage events. Excellent clamping capability, low leakage, and fast response time, make these parts ideal for ESD protection on designs where board space is at a premium. This device has been specifically designed to protect sensitive components which are connected to data and transmission lines from overvoltage caused by ESD (electrostatic discharge), CDE (Cable Discharge Events), and EFT (electrical fast transients).

Features

- 500W peak pulse power (8/20us)
- Protects one data or power line
- Low leakage: <1μA
- Stand-off Voltage: 5 V
- Low clamping voltage
- Complies with following standards:
 - IEC 61000-4-2 (ESD) immunity test Air discharge: ±30kV
 - Contact discharge: ±30kV
- IEC61000-4-4 (EFT) 40A(5/50ns)
- IEC61000-4-5 (Lightning) 25A (8/20μs)
- RoHS Compliant

Dimensions & Symbol (Unit: mm Max)




Mechanical Characteristics

- Package: SOD-323
- Terminals: Tin plated, solderable per MIL-STD-750, method 2026
- Terminal Connections: See Diagram Below
- Marking Information: See Below

Applications

- Cell Phone Handsets and Accessories
- Microprocessor based equipment
- Personal Digital Assistants (PDA's)
- Notebooks, Desktops, and Servers
- Portable Instrumentation
- Networking and Telecom
- Serial and Parallel Ports
- Peripherals

Marking information



Ordering Information

Part Number	Packaging	Reel Size
WPE0581D3H	3000/Tape & Reel	7 inch

WPMtek


Absolute Maximum Ratings ($T_A=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20 μs)	Ppk	500	W
ESD per IEC 61000-4-2 (Air)	VESD	± 30	kV
ESD per IEC 61000-4-2 (Contact)		± 30	
Operating Temperature Range	TJ	-40 to +150	$^{\circ}\text{C}$
Storage Temperature Range	Tstg	-40 to +150	$^{\circ}\text{C}$


Electrical Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Working Voltage	V_{RWM}			5	V	
Breakdown Voltage	V_{BR}	5.8		7.8	V	$I_T = 1\text{mA}$
Reverse Leakage Current	I_R			1.0	μA	$V_{\text{RWM}} = 5\text{V}$
Clamping Voltage	V_C			9.8	V	$I_{\text{PP}} = 1\text{A}$ (8 x 20 μs pulse)
Clamping Voltage	V_C		18	20	V	$I_{\text{PP}} = 25\text{A}$ (8 x 20 μs pulse)
Junction Capacitance	C_J		35	45	pF	$V_R = 0\text{V}$, $f = 1\text{MHz}$

ELECTRICAL CHARACTERISTICS CURVE




Pulse Waveform




Power Derating Curve

Soldering Parameters

Reflow Condition		Pb-Free assembly
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150°C
	-Temperature Max($T_{s(max)}$)	+200°C
	-Time (Min to Max) (t_s)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3°C/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/sec. Max
Reflow	-Temperature(T_L) (Liquid us)	+217°C
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_p)		+260(+0/-5)°C
Time within 5°C of actual Peak Temp (t_p)		30 secs. Max
Ramp-down Rate		6°C/sec. Max
Time 25°C to Peak Temp (T_P)		8 min. Max
Do not exceed		+260°C




Package Mechanical Data



Symbol	Dimensions (mm)	
	Min	Max
A		1.00
A1	0.000	0.100
A2	0.800	0.900
b	0.250	0.350
c	0.080	0.150
D	1.200	1.400
E	1.600	1.800
E1	2.500	2.700
e	1.800	2.040
L	0.475 Ref	
L1	0.250	0.400
θ	0	8°

Suggested Land Pattern



WPMtek reserves the right to make changes to the product specification and data in this document without notice. WPMtek makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does WPMtek assume any liability arising from the application or use of any products or circuits, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Any enquiry, please write to sales@wpmtek.com for further information.