






RoHS Compliant



SEE SECTION O-O







深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名 (ITEM NO)	NGFF M.2 M KEY 4.2H		
		料号 (PART NO)	MLD-NGFF-M-4.2H		
单位 (UNIT): MM	未注公差 TOLERANCE UNSPECIFIED X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	版次 (REV): A/0	页次 (PAGE): 1/1	设计 (DESIGN)	柯南
比例 (SCALE) 1:1		模号 (MODEL NO)	MLD-2509031032	审核 (CHECKED)	邱敏
 		图号 (DWG NO)		核准 (APPROVED)	陈镇

RoHS Compliant

A
B
C
D
E
F

Assembly stack height schematic diagram



HOW TO MATE AND EXTRACT

MATE: ① → ④




EXTRACT: ⑤ → ⑥

NOTE: Mating force will generate from step 3 to step 4.

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名 (ITEM NO)	NGFF M.2 M KEY 4.2H		
		料号 (PART NO)	MLD-NGFF-M-4.2H		
单位 (UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次 (REV): A/0	页次 (PAGE): 1/1	设计 (DESIGN)	柯南
比例 (SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	模号 (MODEL NO)		审核 (CHECKED)	邱敏
		图号 (DWG NO)		核准 (APPROVED)	陈镇
		MLD-2509031032			

1 2 3 4 5 6 7 8

RoHS Compliant



RECOMMENDED PCB LAYOUT(TOP VIEW)

DEFAULT TOLERANCE $\pm 0.05\text{MM}$

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.			品名(ITEM NO)	NGFF M.2 M KEY 4.2H	
			料号(PART NO)	MLD-NGFF-M-4.2H	
单位(UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次(REV): A/0	页次(PAGE):1/1	设计 (DESIGN)	柯南
比例(SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	模号 (MODEL NO)		审核 (CHECKED)	邱敏
		图号 (DWG NO)		MLD-2509031032	核准(APPROVED)