





Specification:
1.Rating: DC 30V 50mA
2.Travel: 2.5±0.1mm
3.Operating Force:A-B 200gf±75gf
B-A 200gf±75gf
4.Contact Resistance:100mΩ Max
5.Life:10,000 Cycles Min



Circuit Diagram

X	
PART NO	vigor
2	G2
3	G3
4	G4
5	G5
6	G6
7	G7
8	G8
9	G9
10	G10

⑥		1	Phosphor Bronze	Ag Plated
⑤	Spring	1	Steel Wire	Temper
④	Terminal	3	Brass Strip	Ag Plated
③	Base	1	Phenolic Resin	Natural
②	Frame	1	Spcc	Black
①	Knob	1	POM	Black
ITEM	PART NAME	QTY.	MATERIAL	FINISHING

APPROVALS		DATE	DEALON 德之隆® ELECTRONICS CO.,LTD	
DRAWN	G.M.Chen	2024/11/11	TITLE: VERTICAL SLIDE SWITCHES	
CHECKED			PART NO. SS-12F15-GX	
APPROVALS			SCALE: 1:1	
TOLERANCES ARE		ANGLE	UNIT: mm	SHEET 1 OF 1
		30°±0.1°		
		10°~30°		
		5°~10°		
		±0.30		
		±0.20		
		±0.15		
		±0.10		
		±2°	DRAWING NO.	PROJ. 1 OF 1
ECN NO.	REV.	DATE.	DESCRIPTION.	
	A		NEW	
			CHANGE.	
			CHECK.	
			APPRO.	