

RoHS		2	3	4	5	6	7	8	9																																																																															
		技术指标(Technical Index): 1. 温度范围(Temperature range): -40° C~+ 105° C. 2. 额定电压(Rated voltage): 200V, AC. 3. 额定电流(Rated Current):2A AC/DC 4. 接触电阻(Contact resistance): ≤20mΩ 5. 绝缘电阻(Insulation resistance): ≥1000MΩ. 6. 产品料号(Product material No.):																																																																																						
		<table><tr><th>CTK</th><th>DIM A</th><th>DIM B</th><th>DIM C</th></tr><tr><td>2</td><td>2.00</td><td>4.90</td><td>8.00</td></tr><tr><td>3</td><td>4.00</td><td>6.90</td><td>10.00</td></tr><tr><td>4</td><td>6.00</td><td>8.90</td><td>12.00</td></tr><tr><td>5</td><td>8.00</td><td>10.90</td><td>14.00</td></tr><tr><td>6</td><td>10.00</td><td>12.90</td><td>16.00</td></tr><tr><td>7</td><td>12.00</td><td>14.90</td><td>18.00</td></tr><tr><td>8</td><td>14.00</td><td>16.90</td><td>20.00</td></tr><tr><td>9</td><td>16.00</td><td>18.90</td><td>22.00</td></tr><tr><td>10</td><td>18.00</td><td>20.90</td><td>24.00</td></tr><tr><td>11</td><td>20.00</td><td>22.90</td><td>26.00</td></tr><tr><td>12</td><td>22.00</td><td>24.90</td><td>28.00</td></tr><tr><td>13</td><td>24.00</td><td>26.90</td><td>30.00</td></tr><tr><td>14</td><td>26.00</td><td>28.90</td><td>32.00</td></tr><tr><td>15</td><td>28.00</td><td>30.90</td><td>34.00</td></tr><tr><td>16</td><td>30.00</td><td>32.90</td><td>36.00</td></tr><tr><td>17</td><td>32.00</td><td>34.90</td><td>38.00</td></tr><tr><td>18</td><td>34.00</td><td>36.90</td><td>40.00</td></tr><tr><td>19</td><td>36.00</td><td>38.90</td><td>42.00</td></tr><tr><td>20</td><td>38.00</td><td>40.90</td><td>44.00</td></tr></table>						CTK	DIM A	DIM B	DIM C	2	2.00	4.90	8.00	3	4.00	6.90	10.00	4	6.00	8.90	12.00	5	8.00	10.90	14.00	6	10.00	12.90	16.00	7	12.00	14.90	18.00	8	14.00	16.90	20.00	9	16.00	18.90	22.00	10	18.00	20.90	24.00	11	20.00	22.90	26.00	12	22.00	24.90	28.00	13	24.00	26.90	30.00	14	26.00	28.90	32.00	15	28.00	30.90	34.00	16	30.00	32.90	36.00	17	32.00	34.90	38.00	18	34.00	36.90	40.00	19	36.00	38.90	42.00	20	38.00	40.90	44.00	
CTK	DIM A	DIM B	DIM C																																																																																					
2	2.00	4.90	8.00																																																																																					
3	4.00	6.90	10.00																																																																																					
4	6.00	8.90	12.00																																																																																					
5	8.00	10.90	14.00																																																																																					
6	10.00	12.90	16.00																																																																																					
7	12.00	14.90	18.00																																																																																					
8	14.00	16.90	20.00																																																																																					
9	16.00	18.90	22.00																																																																																					
10	18.00	20.90	24.00																																																																																					
11	20.00	22.90	26.00																																																																																					
12	22.00	24.90	28.00																																																																																					
13	24.00	26.90	30.00																																																																																					
14	26.00	28.90	32.00																																																																																					
15	28.00	30.90	34.00																																																																																					
16	30.00	32.90	36.00																																																																																					
17	32.00	34.90	38.00																																																																																					
18	34.00	36.90	40.00																																																																																					
19	36.00	38.90	42.00																																																																																					
20	38.00	40.90	44.00																																																																																					
		<table><tr><td colspan="2">OPERATION</td><td rowspan="2">DRAW</td><td rowspan="2">SCALE</td><td rowspan="2">FIT</td><td colspan="2" rowspan="3">深圳市连盛精密连接器有限公司</td></tr><tr><td>X.X</td><td>±0.30</td></tr><tr><td>X.XX</td><td>±0.20</td><td rowspan="2">CHECK</td><td>UNIT</td><td>mm</td></tr><tr><td>X.XXX</td><td>±0.10</td><td>SIZE</td><td>A4</td><td>PART NO.</td><td>1130300235</td></tr><tr><td>Angle</td><td>±3°</td><td rowspan="2">APPROVE</td><td>SHEET</td><td>1/1</td><td>TITLE:</td><td>HY-NAWR</td></tr><tr><td>DIM</td><td>TOL</td><td>PROJ.</td><td>◆</td><td></td></tr></table>						OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司		X.X	±0.30	X.XX	±0.20	CHECK	UNIT	mm	X.XXX	±0.10	SIZE	A4	PART NO.	1130300235	Angle	±3°	APPROVE	SHEET	1/1	TITLE:	HY-NAWR	DIM	TOL	PROJ.	◆																																																		
OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司																																																																																			
X.X	±0.30																																																																																							
X.XX	±0.20	CHECK	UNIT	mm																																																																																				
X.XXX	±0.10		SIZE	A4	PART NO.	1130300235																																																																																		
Angle	±3°	APPROVE	SHEET	1/1	TITLE:	HY-NAWR																																																																																		
DIM	TOL		PROJ.	◆																																																																																				
A0		2012.04.18	NEW DRAWING																																																																																					
REV		DATE	MODIFICATION DESCRIPTION	CHANGE																																																																																				

[illegible]

	RoHS		2	3	4	5	6	7	8	9																																																																																
G										<table border="1"><thead><tr><th>序号 (NO.)</th><th>品名 (Name)</th><th>材质 (Material)</th></tr></thead><tbody><tr><td>①</td><td>2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)</td><td>LCP UL94V-0 本色 Natural</td></tr><tr><td>②</td><td>2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)</td><td>铜合金/表面镀锡 Copper Alloy/ Tin Plating</td></tr><tr><td>③</td><td>2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)</td><td>铜合金/表面镀锡 Copper Alloy/ Tin Plating</td></tr></tbody></table>	序号 (NO.)	品名 (Name)	材质 (Material)	①	2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)	LCP UL94V-0 本色 Natural	②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating	③	2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																				
序号 (NO.)	品名 (Name)	材质 (Material)																																																																																								
①	2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)	LCP UL94V-0 本色 Natural																																																																																								
②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																																								
③	2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																																								
F																																																																																										
E			技术指标(Technical Index): - 温度范围(Temperature range): -40° C~+ 105° C. - 额定电压(Rated voltage): 200V, AC. - 额定电流(Rated Current):2A AC/DC - 接触电阻(Contact resistance): ≤20mΩ - 绝缘电阻(Insulation resistance): ≥1000MΩ. - 产品料号(Product material No.):																																																																																							
D										<table border="1"><thead><tr><th>CKT</th><th>DIM A</th><th>DIM B</th><th>DIM C</th></tr></thead><tbody><tr><td>2</td><td>2.00</td><td>4.90</td><td>8.00</td></tr><tr><td>3</td><td>4.00</td><td>6.90</td><td>10.00</td></tr><tr><td>4</td><td>6.00</td><td>8.90</td><td>12.00</td></tr><tr><td>5</td><td>8.00</td><td>10.90</td><td>14.00</td></tr><tr><td>6</td><td>10.00</td><td>12.90</td><td>16.00</td></tr><tr><td>7</td><td>12.00</td><td>14.90</td><td>18.00</td></tr><tr><td>8</td><td>14.00</td><td>16.90</td><td>20.00</td></tr><tr><td>9</td><td>16.00</td><td>18.90</td><td>22.00</td></tr><tr><td>10</td><td>18.00</td><td>20.90</td><td>24.00</td></tr><tr><td>11</td><td>20.00</td><td>22.90</td><td>26.00</td></tr><tr><td>12</td><td>22.00</td><td>24.90</td><td>28.00</td></tr><tr><td>13</td><td>24.00</td><td>26.90</td><td>30.00</td></tr><tr><td>14</td><td>26.00</td><td>28.90</td><td>32.00</td></tr><tr><td>15</td><td>28.00</td><td>30.90</td><td>34.00</td></tr><tr><td>16</td><td>30.00</td><td>32.90</td><td>36.00</td></tr><tr><td>17</td><td>32.00</td><td>34.90</td><td>38.00</td></tr><tr><td>18</td><td>34.00</td><td>36.90</td><td>40.00</td></tr><tr><td>19</td><td>36.00</td><td>38.90</td><td>42.00</td></tr><tr><td>20</td><td>38.00</td><td>40.90</td><td>44.00</td></tr></tbody></table>	CKT	DIM A	DIM B	DIM C	2	2.00	4.90	8.00	3	4.00	6.90	10.00	4	6.00	8.90	12.00	5	8.00	10.90	14.00	6	10.00	12.90	16.00	7	12.00	14.90	18.00	8	14.00	16.90	20.00	9	16.00	18.90	22.00	10	18.00	20.90	24.00	11	20.00	22.90	26.00	12	22.00	24.90	28.00	13	24.00	26.90	30.00	14	26.00	28.90	32.00	15	28.00	30.90	34.00	16	30.00	32.90	36.00	17	32.00	34.90	38.00	18	34.00	36.90	40.00	19	36.00	38.90	42.00	20	38.00	40.90	44.00
CKT	DIM A	DIM B	DIM C																																																																																							
2	2.00	4.90	8.00																																																																																							
3	4.00	6.90	10.00																																																																																							
4	6.00	8.90	12.00																																																																																							
5	8.00	10.90	14.00																																																																																							
6	10.00	12.90	16.00																																																																																							
7	12.00	14.90	18.00																																																																																							
8	14.00	16.90	20.00																																																																																							
9	16.00	18.90	22.00																																																																																							
10	18.00	20.90	24.00																																																																																							
11	20.00	22.90	26.00																																																																																							
12	22.00	24.90	28.00																																																																																							
13	24.00	26.90	30.00																																																																																							
14	26.00	28.90	32.00																																																																																							
15	28.00	30.90	34.00																																																																																							
16	30.00	32.90	36.00																																																																																							
17	32.00	34.90	38.00																																																																																							
18	34.00	36.90	40.00																																																																																							
19	36.00	38.90	42.00																																																																																							
20	38.00	40.90	44.00																																																																																							
C																																																																																										
B																																																																																										
A			<table border="1"><thead><tr><th colspan="2">OPERATION</th><th rowspan="2">DRAW</th><th rowspan="2">SCALE</th><th rowspan="2">FIT</th><th colspan="2" rowspan="4">深圳市连盛精密连接器有限公司</th></tr><tr><th>X.X</th><th>±0.30</th></tr></thead><tbody><tr><td>X.XX</td><td>±0.20</td><td rowspan="2">CHECK</td><td>UNIT</td><td>mm</td></tr><tr><td>X.XXX</td><td>±0.10</td><td>SIZE</td><td>A4</td></tr><tr><td>Angle</td><td>±3'</td><td rowspan="2">APPROVE</td><td>SHEET</td><td>1/1</td><td>PART NO.</td><td>1130300235</td></tr><tr><td>DIM</td><td>TOL</td><td>PROJ.</td><td></td><td>TITLE:</td><td>HY-NAWR</td></tr></tbody></table>							OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司		X.X	±0.30	X.XX	±0.20	CHECK	UNIT	mm	X.XXX	±0.10	SIZE	A4	Angle	±3'	APPROVE	SHEET	1/1	PART NO.	1130300235	DIM	TOL	PROJ.		TITLE:	HY-NAWR																																																		
OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司																																																																																					
X.X	±0.30																																																																																									
X.XX	±0.20	CHECK	UNIT	mm																																																																																						
X.XXX	±0.10		SIZE	A4																																																																																						
Angle	±3'	APPROVE	SHEET	1/1	PART NO.	1130300235																																																																																				
DIM	TOL		PROJ.		TITLE:	HY-NAWR																																																																																				
	1	2	3	4	5	6	7	8	9																																																																																	

- [illegible]

[illegible]

RoHS		2	3	4	5	6	7	8	9																																																																																	
									<table><tr><td>序号 (NO.)</td><td>品名 (Name)</td><td>材质 (Material)</td></tr><tr><td>①</td><td>2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing (H=5.2)</td><td>LCP UL94V-0 本色 Natural</td></tr><tr><td>②</td><td>2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal (H=5.2)</td><td>铜合金/表面镀锡 Copper Alloy/ Tin Plating</td></tr><tr><td>③</td><td>2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail (H=5.6)</td><td>铜合金/表面镀锡 Copper Alloy/ Tin Plating</td></tr></table>		序号 (NO.)	品名 (Name)	材质 (Material)	①	2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing (H=5.2)	LCP UL94V-0 本色 Natural	②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal (H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating	③	2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail (H=5.6)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																				
序号 (NO.)	品名 (Name)	材质 (Material)																																																																																								
①	2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing (H=5.2)	LCP UL94V-0 本色 Natural																																																																																								
②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal (H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																																								
③	2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail (H=5.6)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																																								
									<table><tr><td>CKT</td><td>DIM A</td><td>DIM B</td><td>DIM C</td></tr><tr><td>2</td><td>2.00</td><td>4.90</td><td>8.00</td></tr><tr><td>3</td><td>4.00</td><td>6.90</td><td>10.00</td></tr><tr><td>4</td><td>6.00</td><td>8.90</td><td>12.00</td></tr><tr><td>5</td><td>8.00</td><td>10.90</td><td>14.00</td></tr><tr><td>6</td><td>10.00</td><td>12.90</td><td>16.00</td></tr><tr><td>7</td><td>12.00</td><td>14.90</td><td>18.00</td></tr><tr><td>8</td><td>14.00</td><td>16.90</td><td>20.00</td></tr><tr><td>9</td><td>16.00</td><td>18.90</td><td>22.00</td></tr><tr><td>10</td><td>18.00</td><td>20.90</td><td>24.00</td></tr><tr><td>11</td><td>20.00</td><td>22.90</td><td>26.00</td></tr><tr><td>12</td><td>22.00</td><td>24.90</td><td>28.00</td></tr><tr><td>13</td><td>24.00</td><td>26.90</td><td>30.00</td></tr><tr><td>14</td><td>26.00</td><td>28.90</td><td>32.00</td></tr><tr><td>15</td><td>28.00</td><td>30.90</td><td>34.00</td></tr><tr><td>16</td><td>30.00</td><td>32.90</td><td>36.00</td></tr><tr><td>17</td><td>32.00</td><td>34.90</td><td>38.00</td></tr><tr><td>18</td><td>34.00</td><td>36.90</td><td>40.00</td></tr><tr><td>19</td><td>36.00</td><td>38.90</td><td>42.00</td></tr><tr><td>20</td><td>38.00</td><td>40.90</td><td>44.00</td></tr></table>		CKT	DIM A	DIM B	DIM C	2	2.00	4.90	8.00	3	4.00	6.90	10.00	4	6.00	8.90	12.00	5	8.00	10.90	14.00	6	10.00	12.90	16.00	7	12.00	14.90	18.00	8	14.00	16.90	20.00	9	16.00	18.90	22.00	10	18.00	20.90	24.00	11	20.00	22.90	26.00	12	22.00	24.90	28.00	13	24.00	26.90	30.00	14	26.00	28.90	32.00	15	28.00	30.90	34.00	16	30.00	32.90	36.00	17	32.00	34.90	38.00	18	34.00	36.90	40.00	19	36.00	38.90	42.00	20	38.00	40.90	44.00
CKT	DIM A	DIM B	DIM C																																																																																							
2	2.00	4.90	8.00																																																																																							
3	4.00	6.90	10.00																																																																																							
4	6.00	8.90	12.00																																																																																							
5	8.00	10.90	14.00																																																																																							
6	10.00	12.90	16.00																																																																																							
7	12.00	14.90	18.00																																																																																							
8	14.00	16.90	20.00																																																																																							
9	16.00	18.90	22.00																																																																																							
10	18.00	20.90	24.00																																																																																							
11	20.00	22.90	26.00																																																																																							
12	22.00	24.90	28.00																																																																																							
13	24.00	26.90	30.00																																																																																							
14	26.00	28.90	32.00																																																																																							
15	28.00	30.90	34.00																																																																																							
16	30.00	32.90	36.00																																																																																							
17	32.00	34.90	38.00																																																																																							
18	34.00	36.90	40.00																																																																																							
19	36.00	38.90	42.00																																																																																							
20	38.00	40.90	44.00																																																																																							
		2 PIN 结构样式 (Structural style) 3 PIN 结构样式 (Structural style)																																																																																								
		<table><tr><td colspan="2">OPERATION</td><td rowspan="2">DRAW</td><td rowspan="2">SCALE</td><td rowspan="2">FIT</td><td colspan="2" rowspan="4">深圳市连盛精密连接器有限公司</td></tr><tr><td>X.X</td><td>±0.30</td></tr><tr><td>X.XX</td><td>±0.20</td><td rowspan="2">CHECK</td><td>UNIT</td><td>mm</td></tr><tr><td>X.XXX</td><td>±0.10</td><td>SIZE</td><td>A4</td></tr><tr><td>Angle</td><td>±3°</td><td rowspan="2">APPROVE</td><td>SHEET</td><td>1/1</td><td>PART NO.</td><td>1130300235</td></tr><tr><td>DIM</td><td>TOL</td><td>PROJ.</td><td></td><td>TITLE:</td><td>HY-NAWR</td></tr></table>				OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司		X.X	±0.30	X.XX	±0.20	CHECK	UNIT	mm	X.XXX	±0.10	SIZE	A4	Angle	±3°	APPROVE	SHEET	1/1	PART NO.	1130300235	DIM	TOL	PROJ.		TITLE:	HY-NAWR																																																						
OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司																																																																																					
X.X	±0.30																																																																																									
X.XX	±0.20	CHECK	UNIT	mm																																																																																						
X.XXX	±0.10		SIZE	A4																																																																																						
Angle	±3°	APPROVE	SHEET	1/1	PART NO.	1130300235																																																																																				
DIM	TOL		PROJ.		TITLE:	HY-NAWR																																																																																				
		<table><tr><td>1</td><td>2</td><td>3</td><td>4</td><td>5</td><td>6</td><td>7</td><td>8</td><td>9</td></tr></table>				1	2	3	4	5	6	7	8	9																																																																												
1	2	3	4	5	6	7	8	9																																																																																		