



1	2	3	4	5	6	7	8	9	10	11	12	13	14
↓		↓		↓		↓		↓		↓		↓	
系列	代码	产品直径	代码	产品高度	代码	额定电压(V)	代码	静电容量(μF)	代码	容量范围	代码	附属码(国内)	
L3M	L3M	3.5	F	3.95	039	6.3	0J	0.1	R10	±20%	M	O	引线30F/35F
LMM	LMM	3.55	W	4.5	045	10	1A	0.22	R22	±10%	K	H	引线33F/38F
LK7	LK7	4	A	5	050	16	1C	0.33	R33	0%~+10%	R	F	引线22F/27F
LK	OLK	4.5	G	5.4	054	20	1D	0.47	R47	0%~-10%	T	A	切直脚A图
KCX	KCX	5	B	5.7	057	25	1E	0.56	R56	-10%~+20%	V	B	切脚成型B图
KCG	KCG	5.5	H	5.8	058	27	1N	0.68	R68	-20%~+5%	L	C	切脚成型C图
KCM	KCM	6.3	C	6.5	065	35	1V	0.82	R82	-10%~+5%	G	D	切脚成型D图
LKF	LKF	7	T	7	070	40	1G	1.0	1R0	-10%~+15%	H	E	切脚成型E图
LKM	LKM	8	D	7.7	077	50	1H	2.2	2R2	0%~+40%	I	Q	切脚折弯90° F图A型(右)
LKG	LKG	10	E	8	080	63	1J	3.3	3R3	±15%	J	P	切脚折弯90° F图B型(左)
LKZ	LKZ	12.5	L	8.5	085	70	1L	3.9	3R9	-20%~+50%	A	X	切脚成型G图
LLK	LLK	13	S	9	090	80	1K	4.7	4R7	-5%~-20%	B	g	切脚双折弯90° H图A型(右)
LKX	LKX	14.5	U	9.5	095	90	1F	5.6	5R6	-5%~+20%	E	f	切脚双折弯90° H图B型(左)
LKL	LKL	16	I	10	100	100	2A	6.8	6R8	-15%~+5%	C	K	编带A图
LKL(R)	LKL(R)	18	J	10.5	105	110	2R	8.2	8R2	-15%~-5%	D	J	编带B图
LKJ	LKJ	20	N	11	110	120	2K	10	100	0%~+20%	F	V	SMD
LKD	LKD	22	K	11.5	115	125	2B	12	120	0%~+15%	N	TM	涂膜
LED	LED	25	M	12	120	130	1Q	15	150	-5%~+15%	W	CG	车规
LKE	LKE			12.5	125	140	2Q	22	220	-20%~+0%	S	TJ	透明
V4M	V4M			13	130	160	2C	33	330	-20%~+10%	P	SLYP	塑料圆盘
V3MC	V3MC			13.5	135	180	2M	47	470	0%~+5%	Q	附属码(IND)	
V3M	V3M			14	140	200	2D	56	560	-15%~+20%	u	2	引线30F/35F
VMM	VMM			14.5	145	250	2E	68	680			3	引线33F/38F
VK7	VK7			15	150	270	2N	82	820			4	切直脚A图
VKO	VKO			16	160	300	2S	100	101			5	切脚成型B图
VKM	VKM			16.5	165	315	2F	120	121			6	切脚成型C图
VKG	VKG			17	170	320	1U	150	151			7	切脚成型D图
VKL	VKL			18	180	330	2U	180	181			8	切脚成型E图
VKL(R)	VKL(R)			19	190	350	2V	220	221			9	引线22F/27F
				20	200	375	2P	330	331			M	编带A图
				21	210	400	2G	470	471			N	编带B图
				22	220	420	2T	560	561				
				23	230	450	2W	680	681				
				25	250	480	2L	820	821				
				28	280	500	2H	1000	102				
				30	300	550	2I	1500	152				
				31.5	315	600	2J	2200	222				
				32	320	630	2Y	3300	332				
				35.5	355	650	2X	4700	472				
				36	360			6800	682				
				40	400			10000	103				
				41.5	415			22000	223				
				45	450			33000	333				
				50	500								



LKG


- ◆长寿命 耐高频大纹波电流 高频低阻抗 电源专用产品
- ◆105℃环境下8000~12000小时
- ◆符合AEC-Q200 RoHS指令对应品




主要技术参数

项目		特性									
使用温度范围		≤120V -55~+105℃ ; 160~500V -40~+105℃									
标称电压范围		10~500V									
容量允许偏差		±20% (25±2℃ 120Hz)									
漏电流(μA)		10~120WV I≤0.01CV or 3μA 取大者 C:标称容量(μF) V:额定电压(V) 2分钟读数									
		160~500WV I≤0.02CV+10(μA) C:标称容量(μF) V:额定电压(V) 2分钟读数									
损耗角正切值 (25±2℃ 120Hz)		额定电压(V)	10	16	25	35	50	63	80	100	
		tg δ	0.19	0.16	0.14	0.12	0.10	0.09	0.09	0.09	
		额定电压(V)	120	160	200	250	350	400	450	500	
		tg δ	0.09	0.09	0.08	0.08	0.10	0.10	0.12	0.20	
		标称容量超过1000μF者, 则每增加1000μF, 损耗角正切值增加0.02									
温度特性 (120Hz)		额定电压(V)		10	16	25	35	50	63	80	100
		阻抗比Z(-40℃)/Z(20℃)		6	4	3	3	3	3	3	3
		额定电压(V)		120	160	200	250	350	400	450	500
		阻抗比Z(-40℃)/Z(20℃)		5	5	5	5	7	7	7	8
耐久性		在105℃烘箱中, 施加含额定纹波电流的额定电压, 持续规定时间后, 置于常温16小时后测试, 测试温度: 25±2℃, 电容器的性能应满足如下要求									
		容量变化率				在初始值的±20%以内					
		损耗角正切值				在规定值的200%以下					
		漏电流				在规定值以下					
		负荷寿命				10~120WV		Φ5 8000小时			
								Φ6.3 10000小时			
160~500WV						≥Φ8 12000小时					
						Φ5~Φ6.3 10000小时 ≥Φ8 12000小时					
高温储存		在105℃下, 储存1000小时, 置于常温16小时后测试, 测试温度25±2℃, 电容器的性能应满足如下要求									
		容量变化率				在初始值的±20%以内					
		损耗角正切值				在规定值的200%以下					
		漏电流				在规定值的200%以下					

产品尺寸图 (单位: mm)



备注: ≥Φ6.3 产品有安全阀



L=9	α=1.0
L≤16	α=1.5
L>16	α=2.0

D	5	6.3	8	10	12.5~13	12.5~13(高度≥30)	14.5	16	18
d	0.5	0.5	0.6	0.6	0.7	0.6	0.8	0.8	0.8
F	2.0	2.5	3.5	5.0	5.0	5.0	7.5	7.5	7.5

纹波电流补偿系数

①频率修正系数

频率(Hz)	50	120	1K	10K~50K	100K
修正因子	0.40	0.50	0.80	0.90	1.00

②温度修正系数

环境温度(℃)	50℃	70℃	85℃	105℃
修正因子	2.1	1.8	1.4	1.0



LKG

■ 标准品一览表

电压(V)	10			16			25			35		
项目 容量 (μF)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2°C)	纹波电流 (mA r.m.s/ 105°C 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2°C)	纹波电流 (mA r.m.s/ 105°C 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2°C)	纹波电流 (mA r.m.s/ 105°C 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2°C)	纹波电流 (mA r.m.s/ 105°C 100kHz)
10	5×9	1.05	57	5×9	1.05	72	5×9	1.05	92	5×9	1.50	102
15	5×9	1.05	77	5×9	1.05	92	5×9	1.05	112	5×9	1.50	122
22	5×9	0.40	92	5×9	0.4	112	5×9	0.40	122	5×9	1.50	170
33	5×9	0.40	107	5×9	0.4	122	5×9	0.40	152	5×9	0.40	220
39	5×9	0.40	137	5×9	0.4	152	5×9	0.40	182	5×11	0.36	240
47	5×9	0.25	144	5×9	0.25	162	5×9	0.25	212	5×11	0.32	350
56	5×9	0.25	152	5×9	0.25	172	5×9	0.25	320	6.3×9	0.32	495
68	5×9	0.25	162	5×9	0.25	182	5×11	0.23	350	6.3×11	0.260	550
68										8×9	0.260	580
82	5×9	0.25	172	5×9	0.25	212	6.3×9	0.20	550	6.3×11	0.250	550
82										8×9	0.250	580
100	5×9	0.25	182	5×11	0.23	350	6.3×9	0.20	550	6.3×11	0.250	550
100										8×9	0.250	580
120	5×9	0.25	320	5×11	0.23	550	6.3×11	0.0980	550	8×9	0.250	864
120							8×9	0.0980	580			
150	5×11	0.23	350	6.3×9	0.20	550	6.3×11	0.0980	550	8×11.5	0.0980	960
150							8×9	0.0980	580	10×9	0.0980	980
180	5×11	0.23	350	6.3×9	0.1600	550	8×9	0.0980	864	8×11.5	0.0980	960
180										10×9	0.0980	980
220	6.3×9	0.20	550	6.3×11	0.0980	550	8×11.5	0.0608	960	8×11.5	0.0980	1270
220				8×9	0.0980	580	10×9	0.0608	980			
270	6.3×9	0.1600	550	8×9	0.0980	580	8×11.5	0.0608	960	8×16	0.0700	1270
270							10×9	0.0608	980	10×12.5	0.0629	1330
330	6.3×11	0.0980	550	8×9	0.0980	864	8×14	0.0532	960	10×12.5	0.0629	1330
330	8×9	0.0980	580									
390	8×9	0.0980	580	8×11.5	0.0608	960	8×16	0.0485	1270	8×20	0.0550	1720
390				10×9	0.0608	980	10×12.5	0.0485	1270	10×16	0.0550	1850
470	8×9	0.0980	864	8×11.5	0.0608	960	10×12.5	0.0429	1330	10×16	0.0550	1850
470				10×9	0.0608	980				12.5×14	0.0550	1890
560	8×11.5	0.0608	960	8×16	0.0485	1270	8×20	0.0313	1530	10×20	0.0480	2250
560	10×9	0.0608	980	10×9	0.0485	1330	10×14	0.0313	1850	12.5×16	0.0480	2330
680	8×11.5	0.0608	960	8×16	0.0485	1270	10×16	0.0308	1850	10×23	0.0398	2330
680	10×9	0.0608	980	10×12.5	0.0429	1330				12.5×20	0.0350	2330
820	8×14	0.0585	1170	8×20	0.0313	1530	10×20	0.0280	2250	12.5×20	0.0280	2480
820	10×12.5	0.0608	1270	10×14	0.0313	1850	12.5×16	0.0350	2330			
1000	8×16	0.0485	1270	8×20	0.0313	1530	10×20	0.0280	2330	12.5×20	0.0280	2480
1000	10×12.5	0.0429	1330	10×16	0.0308	1850	12.5×16	0.0350	2330			
1200	8×20	0.0313	1530	10×16	0.0308	1960	12.5×20	0.0280	2480	12.5×25	0.0265	2900
1200	10×14	0.0308	1760							14.5×16	0.0580	1467



LKG

■ 标准品一览表

电压(V)	10			16			25			35		
项目 容量 (μF)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)
1500	8×20	0.0313	1530	10×20	0.0280	1960	12.5×20	0.0280	2480	12.5×30	0.0243	3450
1500	10×16	0.0308	1850	12.5×16	0.0350	2330				14.5×20	0.0450	1620
1500										16×20	0.0265	3250
1800	10×20	0.0280	1960	10×20	0.0280	2250	12.5×25	0.0230	2900	12.5×35	0.0220	3570
1800	12.5×16	0.0201	2330	12.5×16	0.0280	2480	14.5×16	0.1350	1944	14.5×23	0.0320	1845
1800										16×25	0.0243	3630
2200	10×20	0.0280	1960	12.5×20	0.0280	2480	12.5×25	0.0143	3450	14.5×25	0.0180	2088
2200	12.5×16	0.0201	2330				14.5×20	0.1120	2124	16×25	0.0243	3630
2200							16×20	0.0165	3250			
2700	10×23	0.0198	2250	12.5×20	0.0218	2900	12.5×35	0.0132	3570	14.5×27	0.0120	2385
2700	12.5×20	0.0280	2480	14.5×16	0.0810	1935	14.5×23	0.0950	2358	16×35.5	0.0210	4010
2700							16×25	0.0143	3630	18×31.5	0.0210	4180
3300	12.5×20	0.0280	2480	12.5×25	0.0165	3450	12.5×40	0.0121	3890	16×40	0.0210	4220
3300				14.5×20	0.0680	2232	14.5×25	0.0800	2520	18×35.5	0.0160	4220
3300							16×25	0.0143	3630			
3900	12.5×25	0.0165	2900	12.5×30	0.0143	3450	14.5×27	0.0660	2718	18×35.5	0.0160	4500
3900	14.5×16	0.0720	1890	16×20	0.0165	3250	16×31.5	0.0121	3890			
3900							18×25	0.0132	3650			
4700	12.5×30	0.0143	3450	12.5×30	0.0143	3570	16×31.5	0.0110	4010			
4700	14.5×20	0.0600	2160	14.5×23	0.0580	2475	18×25	0.0110	4180			
4700	16×20	0.0165	3450	16×25	0.0143	3630						
5600	12.5×30	0.0143	3570	14.5×25	0.0480	2745	18×35.5	0.0100	4220			
5600	14.5×23	0.0480	2385	16×31.5	0.0121	3890						
5600	16×20	0.0165	3250	18×25	0.0132	3650						
6800	12.5×35	0.0132	3570	14.5×27	0.0350	2880	18×40	0.0100	4500			
6800	14.5×25	0.0400	2592	16×31.5	0.0121	3890						
6800	16×25	0.0143	3630	18×25	0.0132	3650						
8200	14.5×27	0.0320	2745									
8200	16×31.5	0.0121	3890	16×35.5	0.0110	4010						
8200	18×25	0.0132	3650	18×31.5	0.0110	4010						
10000	16×31.5	0.0121	3890	18×35.5	0.0100	4080						
10000	18×25	0.0132	3650									

电压(V)	50			63			80			100		
项目 容量 (μF)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)
0.47	5×9	4.00	22	5×9	3.00	24	5×9	3.00	25	5×9	3.00	25
1.0	5×9	4.00	32	5×9	3.00	35	5×9	3.00	36	5×9	3.00	36
1.2	5×9	4.00	32	5×9	3.00	35	5×9	3.00	36	5×9	3.00	36
1.5	5×9	4.00	38	5×9	3.00	42	5×9	3.00	44	5×9	3.00	44
1.8	5×9	4.00	38	5×9	3.00	42	5×9	3.00	44	5×9	3.00	44



LKG

■ 标准品一览表

电压(V)	50			63			80			100		
项目 容量 (μF)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2°C)	纹波电流 (mA r.m.s/ 105°C 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2°C)	纹波电流 (mA r.m.s/ 105°C 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2°C)	纹波电流 (mA r.m.s/ 105°C 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2°C)	纹波电流 (mA r.m.s/ 105°C 100kHz)
2.2	5×9	1.50	40	5×9	3.00	46	5×9	3.00	48	5×9	3.00	48
2.7	5×9	1.50	40	5×9	3.00	56	5×9	3.00	56	5×9	3.00	56
3.3	5×9	1.50	55	5×9	3.00	60	5×9	3.00	63	5×9	3.00	63
3.9	5×9	1.50	55	5×9	3.00	79	5×9	3.00	82	5×9	1.35	82
4.7	5×9	1.50	90	5×9	3.00	99	5×9	3.00	102	5×9	1.35	102
5.6	5×9	1.50	92	5×9	3.00	101	5×9	3.00	107	5×11	1.12	107
6.8	5×9	1.50	95	5×9	3.00	105	5×9	3.00	112	5×11	1.12	112
8.2	5×9	1.50	97	5×9	3.00	110	5×9	1.35	127	5×11	0.88	127
10	5×9	1.50	102	5×9	3.00	112	5×11	1.35	170	6.3×9	0.88	275
12	5×9	1.50	122	5×9	3.00	122	5×11	0.78	248	6.3×11	0.78	300
12										8×9	0.78	300
15	5×9	1.50	122	5×9	1.35	170	6.3×9	0.61	275	6.3×11	0.78	400
15										8×9	0.78	416
18	5×9	1.05	170	5×11	0.78	278	6.3×9	0.61	275	6.3×11	0.61	400
18										8×9	0.61	416
22	5×11	0.95	180	6.3×9	0.74	356	6.3×11	0.78	400	8×11.5	0.39	462
22							8×9	0.78	416	10×9	0.39	500
27	5×11	0.95	180	6.3×9	0.61	356	6.3×11	0.78	400	8×11.5	0.27	585
27							8×9	0.78	416	10×9	0.27	624
33	6.3×9	0.74	356	6.3×11	0.38	400	6.3×11	0.61	400	8×11.5	0.27	585
33				8×9	0.38	482	8×9	0.61	416	10×9	0.27	624
39	6.3×9	0.62	356	6.3×11	0.38	400	8×11.5	0.39	462	8×16	0.27	585
39				8×9	0.38	482	10×9	0.61	500	10×12.5	0.27	624
47	6.3×11	0.32	356	6.3×11	0.32	520	8×11.5	0.39	462	8×16	0.27	585
47	8×9	0.26	395	8×9	0.24	520	10×9	0.61	500	10×12.5	0.27	624
56	6.3×11	0.21	666	8×9	0.24	520	8×11.5	0.27	585	10×12.5	0.25	750
56	8×9	0.21	666				10×9	0.28	585			
68	8×9	0.21	666	8×11.5	0.23	520	8×16	0.27	585	8×20	0.20	770
68				10×9	0.24	535	10×12.5	0.25	624	10×14	0.19	780
82	8×11.5	0.15	740	8×11.5	0.17	722	8×20	0.25	624	10×16	0.19	780
82	10×9	0.15	666	10×9	0.17	650	10×12.5	0.25	624	12.5×14	0.18	858
100	8×11.5	0.15	740	8×16	0.17	722	8×20	0.20	800	10×20	0.13	1040
100	10×9	0.15	666	10×12.5	0.17	722	10×16	0.19	780	12.5×16	0.14	975
120	8×14	0.13	970	8×16	0.17	722	10×16	0.19	780	10×23	0.12	1170
120	10×12.5	0.13	985	10×12.5	0.17	722	12.5×14	0.18	858	12.5×20	0.0930	1430
150	8×16	0.11	970	8×20	0.12	890	10×20	0.13	1040	12.5×20	0.0930	1430
150	10×12.5	0.11	985	10×16	0.12	998	12.5×16	0.14	975			
180	8×20	0.10	1220	10×16	0.12	998	10×20	0.13	1040	12.5×25	0.0660	1620
180	10×14	0.10	1370				12.5×16	0.14	975			
220	8×20	0.0500	1220	10×20	0.0860	1200				12.5×25	0.0660	1620
220	10×16	0.0460	1370	12.5×16	0.0804	1250	12.5×20	0.0940	1430	14.5×16	0.35	1040
270	10×20	0.0420	1580	10×20	0.0860	1200	12.5×20	0.0940	1430	12.5×30	0.0560	1950
270	12.5×14	0.0500	1752	12.5×16	0.0804	1250				14.5×20	0.31	1098
270										16×20	0.0640	1750
330	10×20	0.0420	1580	10×23	0.0760	1410	12.5×20	0.0660	1620	12.5×35	0.0470	2140
330							14.5×16	0.0760	945	14.5×23	0.23	1206



LKG

■ 标准品一览表

电压(V)	50			63			80			100		
项目 容量 (μF)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)
330	12.5×16	0.0500	1752	12.5×20	0.0660	1570				16×25	0.0480	2210
390	10×20	0.0420	1870	12.5×20	0.0660	1570	12.5×30	0.0560	1950	12.5×40	0.0400	2340
390							14.5×20	0.0630	1044	14.5×25	0.1900	1314
390							16×20	0.0640	1750	16×25	0.0480	2210
470	12.5×20	0.0560	2050	12.5×25	0.0470	1990	12.5×35	0.0470	2140	14.5×27	0.1500	1422
470				14.5×16	1.12	1350	14.5×23	0.0570	1125	16×31.5	0.0360	2400
470							16×25	0.0480	2210	18×25	0.0420	2270
560	12.5×20	0.0560	2410	12.5×30	0.0390	2410	12.5×40	0.0400	2340	16×35.5	0.0320	2600
560				14.5×20	0.9500	1422	14.5×25	0.0520	1188	18×31.5	0.0340	2470
560				16×20	0.0390	2410	16×25	0.0480	2210			
680	12.5×25	0.0560	2410	12.5×30	0.0360	2620	14.5×27	0.0480	1260	16×40	0.0300	2860
680	14.5×16	0.1350	1485	14.5×23	0.7800	1449	16×31.5	0.0360	2400	18×35.5	0.0300	2860
680				16×25	0.0350	2730	18×25	0.0420	2270			
820	12.5×25	0.0450	2960	12.5×35	0.0300	2940	16×35.5	0.0320	2600	18×40	0.0285	3510
820	14.5×20	0.1120	1737	14.5×25	0.6000	1530	18×25	0.0420	2270			
820	16×20	0.0420	2730	16×25	0.0350	2730						
1000	12.5×30	0.0350	2960	14.5×27	0.4500	1665	16×40	0.0300	2860			
1000	14.5×23	0.0950	1908	16×31.5	0.0260	2990	18×31.5	0.0340	2470			
1000	16×25	0.0350	3010	18×25	0.0340	2800						
1200	14.5×25	0.0700	2034	16×31.5	0.0260	2990	18×35.5	0.0300	2860			
1200	16×31.5	0.0247	3280	18×25	0.0340	2800						
1200	18×25	0.0323	3060									
1500	14.5×27	0.0500	2088	16×35.5	0.0230	3040	18×40	0.0285	3510			
1500	16×31.5	0.0247	3280	18×31.5	0.0280	3300						
1500	18×25	0.0323	3300									
1800	16×35.5	0.0218	3040	16×40	0.0210	3570						
1800	18×31.5	0.0266	3300	18×35.5	0.0220	3570						
2200	18×35.5	0.0210	3570	18×40	0.0285	3900						
2700	18×40	0.0200	3900									

电压(V)	120			160			200			250		
项目 容量 (μF)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)
0.47	5×9	3.00	25									
1.0	5×9	3.00	38	5×11	27.00	52	5×11	27.00	52	6.3×9	26.00	72
1.2	5×9	3.00	38	5×11	27.00	57	5×11	27.00	57	6.3×9	26.00	72
1.5	5×9	3.00	44	5×11	27.00	64	5×11	27.00	64	6.3×9	26.00	72
1.8	5×9	3.00	44	5×11	27.00	70	5×11	27.00	70	6.3×9	26.00	108
2.2	5×9	3.00	48	5×11	27.00	77	5×11	27.00	77	6.3×9	26.00	117
2.7	5×9	3.00	56	5×11	27.00	85	5×11	27.00	85	6.3×9	26.00	117
3.3	5×9	3.00	63	5×11	27.00	95	6.3×9	26.00	108	6.3×9	10.15	140
3.9	5×11	1.35	82	5×11	21.00	108	6.3×9	16.00	108	6.3×11	10.15	140
3.9										8×9	10.15	144
4.7	5×11	1.35	102	6.3×9	21.00	108	6.3×11	10.15	130	6.3×11	10.15	144



LKG

■ 标准品一览表

电压(V)	120			160			200			250		
项目 容量 (μF)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2°C)	纹波电流 (mA r.m.s/ 105°C 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2°C)	纹波电流 (mA r.m.s/ 105°C 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2°C)	纹波电流 (mA r.m.s/ 105°C 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2°C)	纹波电流 (mA r.m.s/ 105°C 100kHz)
4.7							8×9	10.15	153	8×9	10.15	144
5.6	6.3×9	1.12	107	6.3×9	12.78	130	6.3×11	10.15	130	8×9	10.15	144
5.6							8×9	10.15	153			
6.8	6.3×9	1.12	112	6.3×11	12.78	130	8×9	10.15	153	8×9	10.15	160
6.8				8×9	12.78	117						
8.2	6.3×9	1.12	127	8×9	12.78	140	8×9	10.15	160	8×11.5	10.15	160
8.2										10×9	10.15	144
10	6.3×11	0.88	275	8×9	12.78	140	8×11.5	10.15	170	8×11.5	9.50	290
10							10×9	10.15	180	10×9	9.50	365
12	8×9	0.80	300	8×11.5	10.15	168	8×14	8.5	270	8×14	8.5	270
12				10×9	10.15	168						
15	8×11.5	0.78	358	8×11.5	10.00	261	8×16	3.65	290	8×16	3.65	290
15	10×9	0.78	358	10×9	10.00	261	10×12.5	4.50	365	10×12.5	3.24	380
18	8×11.5	0.61	358	8×14	7.50	290	8×20	3.24	370	8×20	3.24	370
18	10×9	0.61	358	10×9	7.50	261	10× 14	3.24	380	10×14	3.24	400
22	8×14	0.48	450	8×14	7.50	350	8×20	3.24	370	8×20	3.24	370
22	10×9	0.48	450	10×12.5	7.50	380	10×14	3.24	400	10×14	3.24	400
27	8×16	0.37	550	8×16	2.65	350						
27	10×12.5	0.37	550	10×12.5	2.65	380						
33	8×16	0.37	585	8×20	2.65	650	10×20	1.65	650	10×20	1.65	650
33	10×12.5	0.37	585	10×14	2.65	760	12.5×14	1.65	760	12.5×14	1.65	760
39	8×20	0.28	624	10×16	2.65	650						
39	10×14	0.28	624	12.5×14	2.65	760						
47	10×14	0.28	624	10×20	2.65	750	12.5×20	1.38	980	12.5×20	1.38	980
47				12.5×14	2.65	760						
56	10×16	0.25	750	10×20	2.65	920	12.5×20	1.38	980	12.5×20	1.38	980
56	12.5×14	0.25	750	12.5×16	2.27	1180						
68	10×20	0.21	770	12.5×16	2.27	1280	12.5×25	1.25	1300	12.5×25	1.25	1300
68	12.5×14	0.21	780				16×20	1.25	1420	14.5×16	1.98	558
68										16×20	1.25	1420
82	12.5×16	0.19	900	12.5×20	2.27	1280	12.5×25	1.25	1390	12.5×30	1.15	1390
82							14.5×16	1.98	612	14.5×20	1.85	612
82							16×20	1.18	1420	16×20	1.18	1420
100	12.5×20	0.13	1040	12.5×20	2.27	1280	12.5×30	1.15	1390	14.5×23	1.70	675
100				14.5×16	4.20	770	14.5×20	1.60	675	16×25	1.18	1950
100							16×20	1.18	1420	18×20	1.02	1950
120	12.5×20	0.12	1240	12.5×25	1.43	1550	12.5×30	1.15	1420	14.5×25	1.30	747
120				14.5×20	3.85	882	14.5×23	1.52	738	16×31.5	0.98	1990
120				16×20	1.25	1420	16×25	1.18	1950	18×20	1.02	1950
150	12.5×25	0.0930	1430	12.5×30	1.43	1960	14.5×25	1.35	855	14.5×27	1.20	819
150	16×20	0.0930	1430	14.5×23	3.61	972	16×25	1.18	1950	16×31.5	0.98	2030
150				16×25	1.43	1890				18×25	0.98	2030
180	16×20	0.0930	1530	16×25	1.43	1890	14.5×27	1.22	918	16×35.5	0.80	2300
180							16×35.5	0.80	2300	18×31.5	0.80	2300
180							18×31.5	0.80	2300			



LKG

■ 标准品一览表

电压(V)	120			160			200			250		
项目 容量 (μF)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)
220	16×25	0.0660	1750	16×31.5	1.14	2450	18×31.5	0.80	2300	18×35.5	0.74	2680
220	18×20	0.0660	1750	14.5×25	3.42	1044						
220				18×25	1.14	2370						
270	16×31.5	0.0560	1950	14.5×27	3.15	1107						
270	18×25	0.0640	1950	16×31.5	1.14	2450						
330	16×31.5	0.0470	2210	18×31.5	1.10	3200						
330	18×25	0.0480	2210									
390	16×35.5	0.0400	2430	18×35.5	0.95	3450						
390	18×31.5	0.0400	2430									
470	18×35.5	0.0320	2600									
560	18×40	0.0320	2860									

电压(V)	350			400			450			500		
项目 容量 (μF)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)
1.0	6.3×9	55.00	81	6.3×9	55.00	77	6.3×9	55.00	81	6.3×12	55.00	48
1.2	6.3×9	34.00	99	6.3×9	34.00	81	6.3×9	50.00	81	6.3×12	50.00	48
1.5	6.3×9	34.00	99	6.3×9	34.00	81	6.3×9	50.00	81	6.3×12	50.00	48
1.8	6.3×9	34.00	99	6.3×9	34.00	81	6.3×11	45.00	86	8×11.5	45.00	84
1.8							8×9	38.00	86			
2.2	6.3×9	34.00	130	6.3×9	28.00	100	8×9	38.00	95	8×11.5	16.50	90
2.7	6.3×11	23.00	144	8×9	23.00	144	8×9	38.00	126	8×14	12.00	110
2.7	8×9	23.00	144									
3.3	8×9	16.00	144	8×9	16.00	160	8×11.5	28.00	140	8×14	12.00	110
3.3							10×9	28.00	150			
3.9	8×9	16.00	155	8×11.5	16.00	160	8×11.5	28.00	140	8×16	12.00	130
3.9				10×9	16.00	220	10×9	28.00	150			
4.7	8×11.5	16.00	155	8×11.5	16.00	160	8×14	21.80	175	8×20	12.00	130
4.7	10×9	16.00	180	10×9	16.00	220	10×9	18.50	180			
5.6	8×11.5	12.50	200	8×14	12.50	240	8×16	12.50	190	10×16	12.00	140
5.6	10×9	16.00	170	10×12.5	12.50	250	10×12.5	12.50	200			
6.8	8×14	10.50	220	8×16	10.50	270	8×20	9.80	230	10×16	11.00	250
6.8	10×9	12.50	240	10×12.5	10.50	280	10×14	9.80	210			
8.2	8×16	7.50	290	8×20	7.50	290	8×20	6.20	230	10×20	11.00	250
8.2	10×12.5	12.50	315	10×14	7.50	315	10×14	6.20	280			
10	8×20	12.50	290	8×20	7.50	315	10×16	6.20	280	10×20	10.00	280
10	10×14	7.50	350	10×14	7.50	350	12.5×14	6.20	360	12.5×14	7.00	320



LKG

■ 标准品一览表

电压(V)	350			400			450			500		
项目 容量 (μF)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)	尺寸 ΦD×L(mm)	阻抗 (Ωmax/100kHz 25±2℃)	纹波电流 (mA r.m.s/ 105℃ 100kHz)
12	10×16	6.20	370	10×20	6.20	490	10×20	6.20	410	12.5×16	6.50	420
15	10×16	6.20	370	10×20	6.20	490	10×20	6.20	410	12.5×20	6.00	480
15	12.5×14	6.20	490	12.5×16	6.20	550	12.5×16	6.20	460			
18	10×20	6.20	490				12.5×20	4.50	500	12.5×25	6.00	480
18	12.5×14	6.20	510	12.5×16	6.20	550						
22	10×20	6.20	550	12.5×20	6.20	1000	12.5×20	4.25	500	12.5×25	4.50	520
22	12.5×16	6.20	1060									
27										14.5×16	3.10	558
33	12.5×20	2.25	1060	12.5×25	4.00	1060	12.5×30	2.82	770	12.5×35	2.20	740
33				16×20	3.00	1150	14.5×16	3.10	630	14.5×20	2.90	572
33							16×20	3.00	730	16×25	2.20	740
39				14.5×16	3.10	657	14.5×20	2.80	684	14.5×23	2.50	585
47	12.5×25	2.25	1150	12.5×30	2.00	1180	14.5×23	2.50	729	14.5×25	2.30	594
47	16×20	2.25	1150	14.5×20	2.82	720	16×25	2.82	1240	16×31.5	2.00	850
47				16×25	2.00	1180	18×20	2.82	1200			
56	12.5×30	2.02	1220	14.5×23	2.35	774	14.5×25	2.20	855	14.5×27	2.15	612
56	16×25	2.02	1320	16×25	1.82	1580	16×31.5	1.50	1240	16×35.5	2.00	850
56				18×20	1.82	1530	18×25	1.50	1200	18×31.5	2.00	850
68	16×25	1.38	1580	14.5×25	1.65	828	14.5×27	2.00	900	18×31.5	1.80	1200
68	18×20	1.38	1530	16×31.5	1.38	1580	16×35.5	1.25	1400			
68				18×25	1.38	1530	18×31.5	1.25	1460			
82	16×31.5	1.38	1580	14.5×27	1.35	882	16×40	1.25	1460	18×35.5	1.50	1200
82	18×25	1.38	1530	16×35.5	1.25	2280	18×31.5	1.25	1460			
82				18×31.5	1.25	2280						
100	16×35.5	1.25	1945	18×31.5	1.07	2580	18×35.5	0.90	1970	18×40	1.25	1200
100	18×31.5	1.25	2280									
120	18×31.5	1.25	2780	18×35.5	0.95	2850	18×40	0.90	1970	18×45	0.98	1268
150	18×35.5	0.97	2850	18×40	0.95	2980	18×45	0.85	2080			