

A

B




C

D


E

F


修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
AO		NEW DWG	黄艳兰	



A-A



B-B



C-C

NOTES:

1. Material: Phosphor Bronze, T=0.15mm
2. Finish: Nickel 20u"~60u" Over All.
T-Tin 80u"~120u" Over Nickel
G-Gold Flash(0.8u") Over Nickel
3. Applicable Wire Range: AWG#28~#32
4. Insulation O.D.: 0.90mm (Max.)
5. Current Rating: 1A AC,DC
6. Voltage Rating: 150V AC,DC
7. Temperature Rang: -25°C~+85°C
8. Contact Resistance: 40mΩ Max
9. Insulation Resistance: 100MΩ Min
10. Withstanding Voltage: 500V AC/minute



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-27111216 传真: 0755-29940187

~TOLERANCES~
UNLESS OTHERWISE SPECIFIED
公差参数表



TITLE:
产品名称: 12507TS-G1-HDGC

X.X ±0.30 X.X* ±3°
APPD:
核准: 谢亮

CHECK:
校对: 王建业

PART NO:
产品编号: 12507TS-G1

X.XX ±0.20 X.XX* ±2°

DRAW:
绘图: 黄艳兰

DATE	SCALE	UNIT	CODE NUMBER
	1:1	mm	A001

X.XXX ±0.15 X.XXX* ±1°