





REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	/



面板开孔尺寸



PART NO.:

EC-GX12-P03-C A V

① Model(型号): EC

② Series(系列): GX12

③ Needle core configuration(针芯配置): 3Pin

④ Outer casing(外壳): 锌合金镀镍/Zinc alloy nickel plated

⑤ Insulator(绝缘体): 橡胶黑木/Rubber Ebony

⑥ Needle core(针芯): 母焊接针/Mother welding needle

PCB板开孔尺寸

A-A(比例: 1: 1)

Specifications:

规格:

Number of insertions and removals: 1000

插拔次数: 1000

Temperature: -55° ~ +70°

温度: -55° ~ +70°

Protection level: IP50

防护级别: IP50

Salt spray: 5% NaCl for 25 hours / 25 hours in 5% NaCl mist

盐雾: 5% NaCl for 25 hours/5%NaCl雾气中25小时

Rated Voltage: 400V

额定电压: 400V

Rated current: 5A


额定电流: 5A

Pin material: gold-plated copper alloy

插针材料: 铜合金镀金

Insulation resistance: >100MΩ

绝缘电阻: >100MΩ

AUGLAR	±5°					XKB INDUSTRIAL PRECISION CO., LIMITED			
X.	±0.40								
X.x	±0.30								
X.xx	±0.20								
X.xxx	±0.15								
UNSPECIFIED TOLERANCES		Connection							
		DESIGN	阿控	VIEW:		MODEL TYPE:	EC.GX12.P03.CAV		
		CHECKED		UNIT:	mm/in	PART NO.:	/		
		APPROVED		SIZE:	A4	DWG NO.:			
						SCALE	PAGE	REVISION	

www.helloxkb.com

www.helloxkb.cn

www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO., LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A0