

A

B


C

D




E

F

修订	标记	修改摘要	签名	日期



02P:Clasp on the
rightfrom this view



SPECIFICATIONS

Rated(额定参数): 300V,15A

Dielectric strength(抗电强度): AC2000V/1 Minute

Insulation Resistance(绝缘电阻):1000MΩ Min

Contact Resistance(接触电阻):20mΩ Max

Screw Torque(扭矩): 0.4Nm (3.5Lb.in)

Wire Range(线径):28~12AWG

Strip length(剥线长度):7-8mm

Temp. range(操作温度): -40℃~+105℃

MAX Soldering(瞬时温度):+250℃,5s

Housing Material(塑件): PA66 (UL94 V-0)

Contact(端子): Phosphor Bronze, Tin plating(磷铜镀锡/锡)

Clamp(方块): Brass/Steel(铜/铁), Ni plating(镀镍)

Screw (螺丝): M2.5 Steel, Zinc plating(钢,镀锌)




深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-27111216 传真: 0755-29940187

~TOLERANCES~
UNLESS OTHERWISE SPECIFIED
公差参数表



TITLE:
产品名称: 插拔式接线端子

X.X ±0.30 X.X* ±3°

APPD:
核准: 谢亮

PART NO:
产品编号: HDGC2EDGK-5.08-NP

X.XX ±0.20 X.XX* ±2°

CHECK:
校对: 王建业

DATE SCALE UNIT CODE NUMBER

X.XXX ±0.15 X.XXX* ±1°

DRAW:
绘图: 黄艳兰

1:1 mm A001