







CIRCUIT DIAGRAM



Dustproof;
Protection class IP 54 to IEC 529 (EN 60 529)
Terminals shape similar to ISO 8092-1:
Coil Terminals 6.3 mm ± mm x 0.8 mm±0.05 mm
Load Terminals 9.5 mm± mm x 1.2 mm±0.05 mm




PART	MATERIAL	COLOUR
Cover	PA 66 GF 25	Black sim. to RAL 9005
Base	PA 66 GF 25	Black sim. to RAL 9005
Coil Terminals 85 and 86	Cu Sn	Pre-tinned Sn
Load Terminals 30 and 87	E-Cu	Pre-tinned Sn

Nominal Voltage: 24 V
Coil Resistance: 325,5 Ohm ± 10% at 23° C

1) At Base level
2) Alternative packaging supplied by TE Brazil:
2424386-1 (Carton Box)

PART NUMBER	REV	TE PART NAME	Country of Origin
9-1393303-7	A	V23134-J0053-D642	Portugal
2423486-1 ²⁾	A		
8-1904094-3	A		China

PROPRIETARY THE REPRODUCTION, TRANSMISSION OR USE OF THIS DOCUMENT OR IT'S CONTENTS IS NOT PERMITTED WITHOUT EXPRESSED WRITTEN AUTHORITY. OFFENDERS WILL BE LIABLE FOR ALL DAMAGES. ALL RIGHTS, INCLUDING RIGHTS CREATED BY REGISTERED PATENT(S) GRANTED FOR A UTILITY MODEL OR DESIGN, ARE RESERVED.				CHANGES TO THIS DRAWING MUST BE DONE ONLY IN CAD		PAPER SIZE A2	
APPLICABLE SPEC.:				FINISH			
				DIMENSIONS APPLY PLATING			
				TOLERANCE UNLESS SPECIFIED OTHERWISE			
				DIMENSIONS IN MM		SCALE 2:1 WEIGHT	
				MATERIAL			
				PART NAME			
				POWER F RELAY NO 70A 24V			
				DWG NO.			
				SHT. 1			
B1 ECN-22-176787 07SEP2022 LSand							
B Initial Drawing 09SEP2014 LSand							
A --- 18JUL2013 LSand							
REV. CHANGE ORDER DATE APP.				C - V23134-J0053-D642			
				CUSTOMER DRAWING			
				OF 1			