





REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	/



PART NO.:


PCB板开孔尺寸
A-A(比例: 1: 1)

EC-GX12-P06-C A V

- ① Model(型号): EC
- ② Series(系列): GX12
- ③ Needle core configuration(针芯配置): 6Pin
- ④ Outer casing(外壳): 锌合金镀镍/Zinc alloy nickel plated
- ⑤ Insulator(绝缘体): 橡胶黑木/Rubber Ebony
- ⑥ Needle core(针芯): 母焊接针/Mother welding needle

Specifications:

规格:
Number of insertions and removals: 1000
插拔次数: 1000
Temperature: -55° ~ +70°
温度: -55° ~ +70°
Protection level: IP50
防护级别: IP50
Salt spray: 5% NaCl for 25 hours / 25 hours in 5% NaCl mist
盐雾: 5% NaCl for 25 hours/5%NaCl雾气中25小时
Rated Voltage: 400V
额定电压: 400V
Rated current: 5A
额定电流: 5A
Pin material: gold-plated copper alloy
插针材料: 铜合金镀金
Insulation resistance: >100MΩ
绝缘电阻: >100MΩ

AUGLAR	±5°					DESIGN	阿控	VIEW:	MODEL TYPE:
X.	±0.40					CHECKED		UNIT: mm/in	EC-GX12-P06-CAV
X.xx	±0.30								PART NO.:
X.xxx	±0.20					APPROVED		SIZE: A4	DWG NO.:
UNSPECIFIED TOLERANCES		KKB INDUSTRIAL PRECISION CO., LIMITED						SCALE	PAGE
								N/A	1/1
									REVISION
									A0