






修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
AO		NEW DWG	黄艳兰	



A-A



B-B



NOTES:

1. Material: Phosphor Bronze, T=0.15mm
2. Finish: Nickel 20u"~60u" Over All.
T-Tin 80u"~120u" Over Nickel
G-Gold Flash(0.8u") Over Nickel
3. Applicable Wire Range: AWG#24~#30
4. Insulation O.D.: 1.28mm (Max.)
5. Current Rating: 2A AC,DC
6. Voltage Rating: 100V AC,DC
7. Temperature Rang: -40°C~+105°C
8. Contact Resistance: 20mΩ Max
9. Insulation Resistance: 500MΩ Min
10. Withstanding Voltage: 500V AC/minute




深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-27111216 传真: 0755-29940187

—TOLERANCES—
UNLESS OTHERWISE SPECIFIED
公差参数表



TITLE:
产品名称: MX1.5端子/5025790000

X.X ±0.30 X.X* ±3°

APPD:
核准: 谢亮

PART NO:
产品编号: HDGC1502D-T

X.XX ±0.20 X.XX* ±2°

CHECK:
校对: 王建业

DATE SCALE UNIT CODE NUMBER

X.XXX ±0.15 X.XXX* ±1°

DRAW:
绘图: 黄艳兰

1:1 mm A001