



MATING VIEW
SCALE 1:2

NOTES:

1. Material:
Insulation:LCP,UL94V-0(White)
Pin:Phosphor bronze/Gold Plated
Tab:Phosphor bronze/Tin-Plated
2. Current Rating: 1.5A AC,DC
3. Voltage Rating: 100V AC,DC
4. Temperature Rang: -25°C~+85°C
5. Contact Resistance: 20mΩ Max
6. Insulation Resistance: 500MΩ Min
- 7 Withstanding Voltage: 250V AC/minute

P.C.B Layout



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-27111216 传真: 0755-29940187

~TOLERANCES~
UNLESS OTHERWISE SPECIFIED
公差参数表

X.X	±0.30	X.X*	±3°
X.XX	±0.20	X.XX*	±2°
X.XXX	±0.15	X.XXX*	±1°



APPD:
核准: 谢亮
CHECK:
校对: 王建业
DRAW:
绘图: 黄艳兰

TITLE:
产品名称: 0.8MM间距灯条板对板连接器

PART NO:
产品编号: D0800RS-NP

DATE	SCALE	UNIT	CODE NUMBER
	1:1	mm	A001