

A

B


C

D





E

F

修订	标记	修改摘要	签名	日期



PCB LAYOUT



PART NO.	Dimensions (mm)		PART NO.	Dimensions (mm)		PART NO.	Dimensions (mm)	
	A	B		A	B		A	B
2P	3.81	8.42	10P	34.29	38.90	18P	64.77	69.38
3P	7.62	12.23	11P	38.10	42.71	19P	68.58	73.19
4P	11.43	16.04	12P	41.91	46.52	20P	72.39	77.00
5P	15.24	19.85	13P	45.72	50.33	21P	76.20	80.81
6P	19.05	23.66	14P	49.53	54.14	22P	80.01	84.62
7P	22.86	27.47	15P	53.34	57.95	23P	83.82	88.43
8P	26.67	31.28	16P	57.15	61.76	24P	87.63	92.24
9P	30.48	35.09	17P	60.96	65.57			

SPECIFICATIONS

Rated(额定参数): 300V,8A

Dielectric strength(抗电强度): AC1500V/1 Minute

Insulation Resistance(绝缘电阻):1000MΩ Min

Contact Resistance(接触电阻):20mΩ Max

Temp. range(操作温度): -40℃~+105℃

MAX Soldering(瞬时温度):+250℃,5s

Housing Material(塑件): PA66 (UL94 V-0)


Contact(端子): Brass, Tin plating(黄铜镀锡)



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表TITLE: 插拔式接线端子
产品名称: 插拔式接线端子

X.X	±0.30	X.X°	±3°	APPD: 核准: 谢亮	PART NO: HDGC2EDGVC-3.81-NP 产品编号:			
X.XX	±0.20	X.XX°	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.15	X.XXX°	±1°	DRAW: 绘图: 黄艳兰		1:1	mm	A001