



**Part Number :** [1202530234](#)

**Product Description :** Contrinex Inductive Sensor, M12 Housing, 4mm Operating Distance, Non-embeddable, NPN, NO, 4-pin M12 Connector, 60mm Housing Length



**Series Number :** 120253

**Status :** Not Recommended For New Design

**Product Category :** Inductive and Photoelectric Sensors

**Engineering Number :** DW-AS-611-M12

## Documents & Resources

### Specifications

[1202530230-000.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

### UKCA - Declaration of Conformity

### CE - Declaration of Conformity

## Part Details

### General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M12 Housing, 4mm Operating Distance, Non-embeddable, NPN, NO, 4-pin M12 Connector, 60mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130064045

### Electrical

Output	NO
Polarity	NPN
Switching Frequency	≤ 2000 Hz

### Physical

Connection	Connector (M12, 4-pin)
Length	60mm
Material - Housing	Nickel Plated Brass
Material - Sensing Face	PBTP
Mounting Style	Non-embeddable
Operating Distance	4mm

Output	NO
Sensor Housing Size	M12
Temperature Range - Operating	-25° to +70°C

---

This document was generated on Nov 06, 2025