



Part Number : [1202530230](#)
Product Description : Contrinex Inductive Sensor,
M12 Housing, 4mm Operating Distance, Non-
embeddable, NPN, NO, 2m 3-wire PVC Cable, 50mm
Housing Length
Series Number : 120253
Status : Not Recommended For New Design
Product Category : Inductive and Photoelectric
Sensors
Engineering Number : DW-AD-611-M12



Documents & Resources

Specifications

[1202530230-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M12 Housing, 4mm Operating Distance, Non-embeddable, NPN, NO, 2m 3-wire PVC Cable, 50mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130064007

Electrical

Output	NO
Polarity	NPN
Switching Frequency	≤ 2000 Hz

Physical

Connection	Cable (PVC 2m, 3-wire)
Length	50mm
Material - Housing	Nickel Plated Brass
Material - Sensing Face	PBTP
Mounting Style	Non-embeddable
Operating Distance	4mm

Output	NO
Sensor Housing Size	M12
Temperature Range - Operating	-25° to +70°C