


1. 外形尺寸图 (Dimensions)



2. 规格特性表(Specification and Specifications Table)

料号 Part Number	RXB400V330M35X35	备注 Note
系列 Series	RXB	
标称容量 CAP(uF)	330	
额定电压 WV(V)	400	
尺寸 Size DxL(mm)	35×35	
容差 Tolerance 120Hz	- 20%~20%	
损失角 DF(%)120Hz max	15	
漏电流 LC(uA)60s max	1090	
阻抗 ESR(Ω)100KHz max	N/A	
纹波电流 R.C(mA)120Hz/105°C max	1500	
浪涌电压 SV(V)	450	
寿命 Life(Hrs)	3000	
套管颜色和材质 Sleeve	黑底白字 PET	
工作温度 TEMP(°C)	-25~105	

执行标准(Execution standard) :JISC 5101-4

测试环境(In the test environment) :温度 T 20±2°C , 湿度 RH 65%±5%

3. 纹波电流修正系数(Multiplier for Ripple Current)


3.1 频率系数 Frequency Multipliers

Freq	50Hz/60Hz	120Hz	300Hz	1KHz	10KHz	100KHz
6.3V~100V	0.88	1.0	1.01	1.03	1.05	1.08
160V~250V	0.75	1.0	1.17	1.32	1.45	1.50
315V~450V	0.74	1.0	1.16	1.30	1.41	1.43
500V~550V	0.72	1.0	1.15	1.30	1.40	1.40


3.2 温度系数 Temperature Multipliers

温度系数 Temperature Multipliers					
Temperatrue(°C)	≤45	60	70	85	105
Multiplier	1.65	1.50	1.30	1.20	1.00

4.套管标识示意图 (Marking)

	1.公司商标(Logo)
	2. 工作最高温度与容量范围 (Operating Temperature Range and Capacitance Tolerance)
	3.电容器规格(额定电压和容量) Capacitance and Rated Vlotage
	4.产品系列(Series)
	5.胶管材质(Material PET)
	6.负极表示带 (Polarity bar)
	7.颜色印字 Sleeve Color :黑底白字

5.材料表(Material table)

		
序号 NO	构成部件 Component	材质成分 Material
1	正极箔 Al Foil(+)	高纯铝 Aluminum 99.99%或 99.98%
2	负极箔 Al Foil(-)	高纯铝 Aluminum 99.7%
3	电解纸 Separator	木材纸浆、有机纤维 paper puCP、Cellulose
4	电解液 Electrolyte	乙二醇+有机酸盐 Glycol+organic acid salt
5	盖板 Cover disc	粘胶树脂 Viscose resin
6	铆钉 Rivet	铝 Aluminum
7	导箔条 Tab	铝 Aluminum
8	铝壳 Case	铝 Aluminum
9	套管 Sleeve	聚对苯二甲酸乙二醇酯 PET
10	垫片 Bottom disc	聚丙烯 PP

注:电容产品和构成材料均满足 ROHS2.0、REACH、HF 禁用环境管理物质要求。

6.测试与试验项目 (Test item)

No	项 目 Items	条 件 Conditions		判 定 Decide															
1	静电容量 Capacitance	测试频率:120Hz±10Hz Test Frequency : 120Hz±10Hz 测试电压:≤ 0.5Vrms +1.0V.DC		1.容量偏差符合 2.规格特性表 Tolerance capacitance see the table 2															
2	耗角正切值 Dissipation Factor	Test Voltage:≤ 0.5Vrms +1.0V.DC 测试温度:20±2℃ Test Temperature:20±2℃		2.耗角正切值: Dissipation Factor															
				Vote(V)	63	10	16	25	35	50	63								
				tanδ	0.6	0.55	0.5	0.45	0.4	0.35	0.3								
				Vote(V)	80	100	120	160~450		500~550									
tanδ	0.25	0.2	0.16	0.15		0.20													
3	漏电流 Leakage Current	测试电压:100 V Test Voltage:100 V 充电时间:5 分钟 Charging :5min 测试温度;20±2℃ Test Temperature: 20±2℃		漏电流≤3√CV I≤3√CV															
4	温度循环 Temperature Cycle	<table><tr><td rowspan="6">周期 One Cycle</td><td>温度 Temperature(℃)</td><td rowspan="2">时间 Time (minutes)</td></tr><tr><td>低温特性</td></tr><tr><td>Rated low category temperature±3</td><td>30±3</td></tr><tr><td>25℃</td><td>3max</td></tr><tr><td>Rated low category temperature±3</td><td>30±3</td></tr><tr><td>25℃</td><td>3max</td></tr></table>	周期 One Cycle	温度 Temperature(℃)	时间 Time (minutes)	低温特性	Rated low category temperature±3	30±3	25℃	3max	Rated low category temperature±3	30±3	25℃	3max	1.外观无损坏 No appearance defect. 2.容量变化率在±5%以内 Capacitance change within ±5% 3.损失角小于规格值 DF smaller than specification value. 4.泄漏电流小于规格值 Leakage current smaller than specifica				
周期 One Cycle	温度 Temperature(℃)	时间 Time (minutes)																	
	低温特性																		
	Rated low category temperature±3	30±3																	
	25℃	3max																	
	Rated low category temperature±3	30±3																	
	25℃	3max																	
循环次数 Total number of cycles: 5																			
5	耐焊接热 Resistance to Soldering Heat	预热时间: 120±2 秒 Warm up time :120±2 seconds 达到 120±2℃ to reach 120±2℃ 焊锡炉温度: 260±5℃ . Solder bath temperature: 260±5℃ . 焊料成分: Solder bath composition: Sn-96.5% , Ag-3.0% , Cu-0.5% 浸入深度: 1.5~2.0mm Immersion depth: 1.5 to 2.0mm 浸入时间: 10±1 秒 Immersion duration: 10±1 seconds		1.无外观缺陷 No appearance defect 2.容量变化在±5%以内 Capacitance change within ±5% 3.损失角小于规定值 D.F.smaller than specification value. 4.泄漏电流值小于规定值 Leakage current smaller than specification value.															
6	可焊性 Solder Ability	焊锡炉温度: 235±5℃ . Solder bath temperature: 235±5℃ . 焊料成分: Solder bath composition: Sn-96.5% , Ag-3.0% , Cu-0.5% 浸入深度: 1.5~2.0mm Immersion depth: 1.5 to 2.0mm 浸入时间: 10±1 秒 Immersion duration: 10±1 seconds		锡液要覆盖导针浸入表面积的 95%以上 A minimum of95% the immersed surface is to be coated with the new solder.															

6. 测试与试验项目 (Test item)

No	项 目 Items	条 件 Conditions	判 定 Decide						
7	低温特性 (最大阻抗比) Low Temperature Charcteristics (MaxImpedance Ratio)								
		工作电压 working Voltage (v)	6.3	10	16	25	35	50	63
		阻抗 Impedance Z(-40℃)/Z(+20℃)	8	6	4	3	3	3	3
		工作电压 working Voltage (v)	160	200	250	400	420	450	500
		阻抗 Impedance Z(-25℃)/Z(+20℃)	3	3	4	6	6	8	8
8	高湿度储存 High Humidity storage	温度：40±2℃ Temperature:40±2℃ 相对湿度：90%至 95% Relative humidity :90 to 95% 持续时间： Duration ：240±8 hours			1.无电气或机械损坏。 No electrical or mechanical damage. 2.容量变化率在±15%以内。 Capacitance change within ±15%. 3.损失角值小于规定值。 DF smaller than specification value. 4.泄漏电流小于规定值。 Leakage current smaller than specification value.				
9	防爆 Vent	反向电压试验：电压设定为 100±5V。 Reverse voltage test: Voltage set to 100±5V.			在测试期间或之后，电容器不应发生爆炸、闪光、火焰、火花或火灾，也不应从外壳中喷出任何金属。 There shall be no explosion,flash,flame,spark or fire from the capacitor during or after the test,nor shall there be expulsion of any metal from the casing				
		电容直径 Capacitor diameter	电 流 Current(A)	时 间 Time					
		More than 22.5mm	10	30 分钟内 Within					
10	振动 Vibration	频率范围：10 Hz 至 55 Hz Frequency range : 10 Hz to 55 Hz 振幅：0.75 毫米 Amplitude :0.75 mm 总持续时间：3×2h. X-Y-Z 方向各 2 小时 Total duration: 3× 2h. x-y-z directions each for 2 hours			1.外观:无明显的损伤或电解液漏出 Appearance: No visible damage or leakage of electrolyte. 2.电容量变化: 初始值的±5%以内 Capacitance change: within ±5% of the initial value.				
11	高温负荷 Load Life	试验温度：105 ±2℃ Test Temp: 105±2℃ 额定电压：100 V Rated Voltage: 100V 试验时间：2000(+72 -0)小时 Test Time: 2000(+72 -0)hours 在室温放置 16 小时后再测试。 Restore them to room temperature for 16 hours before testing.			1.外观:无明显的损伤或电解液漏出 Appearance: No visible damage or leakage of electrolyte. 2.电容量变化:初始值的±20%以内。 Capacitance change: within ±20% of the initial value. 3.损耗角正切: ≤200%规定值 tanδ: ≤200% of specified value 4.漏电流: ≤规定值 Leakage Current: ≤Specified value				
12	高温储存 Shelf Life	试验温度:105±2℃ Test Temp: 105±2℃ 试验时间:1000 (+72 -0) 小时 Test Time: 1000 (+72 -0) hours 在室温放置 16 小时后再测试。 Restore them to room temperature for 16hours before testing.			1.外观:无明显的损伤或电解液漏出 Appearance: No visible damage or leakage of electrolyte. 2.电容量变化:初始值的±20%以内。 VCapacitance change: within ±20% of the initial value. 3.损耗角正切: ≤200%规定值 tgδ: ≤200% of specified value 4.漏电流: ≤200%规定值 Leakage Current: ≤200% of specified value				

6.测试与试验项目 (Test item)

No	项 目 Items	条 件 Conditions	判 定 Decide																		
13	浪涌电压 Surge Voltag	试验温度: 15~35 °C, Test Temp: 15~35 °C 试验电压: 浪涌电压 Test voltage: surge voltage 施加浪涌电压 30 秒,然后放电 330 秒, 共循环 1000 次. Charge surge voltage for 30 seconds and discharge for 330 seconds. Repeat this cycle 1000 times.	1.电容量变化:初始值的±15%以内 Capacitance change: within ± 15% of the initial value. 2.损耗角正切: ≤规定值 Tgδ:≤ Specified value 3.漏电流: ≤规定值 Leakage current:≤Specified value 4.外观: 无可见损伤 Appearance: No visible damage																		
		<table><tr><td>UR (V)</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td><td>80</td><td>100</td></tr><tr><td>S.V(V)</td><td>13</td><td>20</td><td>32</td><td>44</td><td>63</td><td>79</td><td>100</td><td>125</td></tr></table>		UR (V)	10	16	25	35	50	63	80	100	S.V(V)	13	20	32	44	63	79	100	125
		UR (V)		10	16	25	35	50	63	80	100										
		S.V(V)		13	20	32	44	63	79	100	125										
		<table><tr><td>UR (V)</td><td>160</td><td>200</td><td>250</td><td>350</td><td>400</td><td>450</td><td>500</td><td>550</td></tr><tr><td>S.V(V)</td><td>200</td><td>250</td><td>300</td><td>400</td><td>450</td><td>500</td><td>550</td><td>600</td></tr></table>		UR (V)	160	200	250	350	400	450	500	550	S.V(V)	200	250	300	400	450	500	550	600
		UR (V)		160	200	250	350	400	450	500	550										
S.V(V)	200	250	300	400	450	500	550	600													