



Part Number : [1202530481](#)
Product Description : Contrinex Inductive Sensor,
4mm Diameter Smooth Housing, 0.8mm Operating
Distance, Embeddable, PNP, NC, 3-pin M8 Connector,
38mm Housing Length
Series Number : 120253
Status : Not Recommended For New Design
Product Category : Inductive and Photoelectric
Sensors
Engineering Number : DW-AS-604-04



Documents & Resources

Specifications

[1202530474-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, 4mm Diameter Smooth Housing, 0.8mm Operating Distance, Embeddable, PNP, NC, 3-pin M8 Connector, 38mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130068265

Electrical

Output	NC
Polarity	PNP
Switching Frequency	≤ 5000 Hz

Physical

Connection	Connector (M8, 3-pin)
Length	38mm
Material - Housing	Stainless Steel
Material - Sensing Face	POM
Mounting Style	Embeddable
Operating Distance	0.8mm
Output	NC

Sensor Housing Size	4mm dia. (smooth)
Temperature Range - Operating	-25° to +70°C