








修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
A0		NEW RELEASE	黄艳兰	2016-08-16
A1		修改尺寸	黄艳兰	2023-04-12
A2	*	10P以上塑胶两侧加胶，改善插口侧面强度	黄艳兰	2025-08-06



RECOMMEND PCB LAYOUT(±0.10)

PIN数	尺寸 (mm)			
	A	B	C	D
2	2.0	7.0	2.5	5.00
3	4.0	9.0	2.5	7.00
4	6.0	11.0	3.5	9.00
5	8.0	13.0	5.5	11.00
6	10.0	15.0	7.5	13.00
7	12.0	17.0	9.5	15.00
8	14.0	19.0	11.5	17.00
9	16.0	21.0	13.5	19.00
10	18.0	23.0	15.5	21.00
11	20.0	25.0	17.5	23.00
12	22.0	27.0	19.5	25.00
13	24.0	29.0	21.5	27.00
14	26.0	31.0	23.5	29.00
15	28.0	33.0	25.5	31.00
16	30.0	35.0	27.5	33.00
17	32.0	37.0	29.5	35.00
18	34.0	39.0	31.5	37.00

Specifications:

- 1.Rated Voltage : 250V AC/DC
- 2.Rated Current : 2A AC,DC
- 3.Withstand Voltage : 1000V AC/minute
- 4.Contact Resistance : 30mΩ(MAX.)
- 5.Insulation Resistance : 1000MΩ(MIN.)
- 6.Storage Temperature Range: -40℃~+85℃;
- 7.Contact Material: Brass;
- 8.plating: Sn Over Ni;
- 9.Insulation Material: Hing Temperature Tnermaplastics LCP,Colour Is Natural;



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

TEL : 0755-27111225 FAX : 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表					TITLE: 产品名称: SMW200-NN			
X.X	±0.30	X.X°	±3°	APPD: 核准: 谢亮	PART NO: 产品编号: SMW200-NN-HDGC2008			
X.XX	±0.30	X.XX°	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.10	X.XXX°	±1°	DRAW: 绘图: 黄艳兰	2016-08-16	1:1	mm	A070