



**Part Number :** [1202530199](#)

**Product Description :** Contrinex Inductive Sensor, M8 Housing, 1.5mm Operating Distance, Embeddable, NPN, NC, 2m 3-wire PVC Cable, 35mm Housing Length

**Series Number :** 120253

**Status :** Not Recommended For New Design

**Product Category :** Inductive and Photoelectric Sensors

**Engineering Number :** DW-AD-602-M8

## Documents & Resources

### Specifications

[1202530198-000.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## UKCA - Declaration of Conformity

## CE - Declaration of Conformity

## **Part Details**

### **General**

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M8 Housing, 1.5mm Operating Distance, Embeddable, NPN, NC, 2m 3-wire PVC Cable, 35mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130063697

### **Electrical**

Output	NC
Polarity	NPN
Switching Frequency	≤ 5000 Hz

### **Physical**

Connection	Cable (PVC 2m, 3-wire)
Length	35mm
Material - Housing	Stainless Steel
Material - Sensing Face	PA66
Mounting Style	Embeddable
Operating Distance	1.5mm
Output	NC
Sensor Housing Size	M8

Temperature Range - Operating

-25° to +70°C

---

This document was generated on Nov 07, 2025