

CMP7N80A/CMB7N80A/CMI7N80A/CMF7N80A

800V, 1.26Ω typ., 7A N-Channel MOSFET

General Description

The 7N80A uses advanced planar stripe DMOS technology and design to provide excellent RDS(ON).

These devices are well suited for high efficiency switch mode power supplies.

Product Summary

BVDSS	R _{DS(on)} max.	ID
800V	1.5Ω	7A


Applications

- Switch Mode Power Supply
- Uninterruptable Power Supply

Features

- Improved dv/dt capability
- 100% avalanche tested
- RoHS Compliant

TO-220/263/262/220F Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	220/263/262	220F	Units
V _{DS}	Drain-Source Voltage	800		V
V _{GS}	Gate-Source Voltage	±30		V
I _D @T _C =25°C	Continuous Drain Current	7	7*	A
I _D @T _C =100°C	Continuous Drain Current	4.9	4.9*	A
I _{DM}	Pulsed Drain Current	28	28*	A
EAS	Single Pulse Avalanche Energy	960		mJ
P _D @T _C =25°C	Total Power Dissipation	200	50	W
T _{STG}	Storage Temperature Range	-55 to 150		°C
T _J	Operating Junction Temperature Range	150		°C

* Drain current limited by maximum junction temperature.

Thermal Data

Symbol	Parameter	220/263/262	220F	Unit
R _{θJA}	Thermal Resistance Junction-ambient Max.	62.5	62.5	°C/W
R _{θJC}	Thermal Resistance Junction-case Max.	0.63	2.50	°C/W

CMP7N80A/CMB7N80A/CMI7N80A/CMF7N80A

800V, 1.26Ω typ., 7A N-Channel MOSFET

Electrical Characteristics (T_J=25°C , unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V , I _D =250μA	800	---	---	V
R _{DS(ON)}	Static Drain-Source On-Resistance	V _{GS} =10V , I _D =3.5A	---	1.26	1.5	Ω
V _{GS(th)}	Gate Threshold Voltage	V _{GS} =V _{DS} , I _D =250μA	3.0	---	5.0	V
I _{DSS}	Drain-Source Leakage Current	V _{DS} =800V , V _{GS} =0V	---	---	10	μA
I _{GSS}	Gate-Source Leakage Current	V _{GS} = ±30V , V _{DS} =0V	---	---	±100	nA
g _{fs}	Forward Transconductance	V _{DS} =15V , I _D =5A	---	10	---	S
R _g	Gate Resistance	V _{DS} =0V , V _{GS} =0V , f=1MHz	---	2.7	---	Ω
Q _g	Total Gate Charge	V _{DS} =640V , I _D =7A V _{GS} =10V (Note 2,3)	---	35	---	nC
Q _{gs}	Gate-Source Charge		---	10	---	
Q _{gd}	Gate-Drain Charge		---	14	---	
T _{d(on)}	Turn-On Delay Time	V _{DD} =400V , I _D =7A R _G =25Ω (Note 2,3)	---	40	---	ns
T _r	Rise Time		---	110	---	
T _{d(off)}	Turn-Off Delay Time		---	65	---	
T _f	Fall Time		---	70	---	
C _{iss}	Input Capacitance	V _{DS} =100V , V _{GS} =0V , f=1MHz	---	1400	---	pF
C _{oss}	Output Capacitance		---	60	---	
C _{rss}	Reverse Transfer Capacitance		---	10	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I _S	Continuous Source Current	V _G =V _D =0V , Force Current	---	---	7	A
I _{SM}	Pulsed Source Current		---	---	28	A
V _{SD}	Diode Forward Voltage	V _{GS} =0V , I _S =7A	---	0.84	1.5	V

Note :







- 1.The EAS data shows Max. rating .The test condition is V_{DS}=100V , V_{GS}=10V , L=30mH , I_{AS}=8A.
2. Pulse Test : Pulse width ≤ 300μs, Duty cycle ≤ 2%.
3. Essentially independent of operating temperature.

This product has been designed and qualified for the consumer market.

Cmos assumes no liability for customers' product design or applications.

Cmos reserves the right to improve product design , functions and reliability without notice. Please refer to the latest version of specification.

Typical Characteristics




CMP7N80A/CMB7N80A/CMI7N80A/CMF7N80A

800V, 1.26Ω typ., 7A N-Channel MOSFET

Package Dimension

TO-220

Unit :mm



DIM	MILLIMETERS
A	10.0±0.3
A1	8.64±0.2
A2	1.15±0.1
A3	5.0±0.2
B	15.8±0.4
B1	13.2±0.3
C	4.56±0.1
C1	1.3±0.2
D	0.8±0.2
E	3.6±0.2
F	2.95±0.3
G	6.5±0.3
H	0.5±0.1
K	3.1±0.2
L	13.2±0.4
M	1.25±0.1
N	2.54±0.1
P	2.4±0.3
Q	9.0±0.3
T	W:0.35
DIA	⊙1.5 (deep 0.2)


CMP7N80A/CMB7N80A/CMI7N80A/CMF7N80A

800V, 1.26Ω typ., 7A N-Channel MOSFET

Package Dimension

TO-263

Unit :mm



DIM	MILLIMETERS
A	9.8 ± 0.2
a	7.4 ± 0.4
B	4.5 ± 0.2
b1	1.3 ± 0.05
b2	2.4 ± 0.2
H	15.5 ± 0.3
h	1.54 ± 0.2
h1	10.5 ± 0.2
h2	9.2 ± 0.1
h3	1.54 ± 0.2
h4	2.7 ± 0.2
L	2.4 ± 0.2
1	1.3 ± 0.1
11	0.8 ± 0.1
12	1.3 ± 0.1
13	0.5 ± 0.1
N	2.54 ± 0.1
R	$0.5R \pm 0.05$


CMP7N80A/CMB7N80A/CMI7N80A/CMF7N80A

800V, 1.26Ω typ., 7A N-Channel MOSFET

Package Dimension

TO-262

Unit :mm



DIM	MILLIMETERS
A	9.98 ± 0.2
a	7.4 ± 0.4
B	4.5 ± 0.2
b1	1.3 ± 0.05
b2	2.4 ± 0.2
H	23.9 ± 0.3
h	3.1 ± 0.2
h1	9.16 ± 0.2
h2	13.2 ± 0.2
L	0.5 ± 0.1
11	1.3 ± 0.1
12	0.8 ± 0.1
N	2.45 ± 0.1


CMP7N80A/CMB7N80A/CMI7N80A/CMF7N80A

800V, 1.26Ω typ., 7A N-Channel MOSFET

Package Dimension

TO-220F

Unit :mm



DIM	MILLIMETERS
A	10.16 ± 0.3
A1	7.00 ± 0.1
A2	3.3 ± 0.2
A3	9.5 ± 0.2
B1	15.87 ± 0.3
B2	4.7 ± 0.2
B3	6.68 ± 0.4
C	3.3 ± 0.2
C1	12.57 ± 0.3
C2	10.02 ± 0.5
D	2.54 ± 0.05
D1	1.28 ± 0.2
D2	0.8 ± 0.1
K	3.1 ± 0.3
E1	2.54 ± 0.1
E3	0.5 ± 0.1
E4	2.76 ± 0.2
DIA	$\varnothing 1.5$ (deep 0.2)