



Part Number : [1202530423](#)

Product Description : Contrinex Inductive Sensor, M8 Housing, 2mm Operating Distance, Embeddable, NPN, NC, 3-pin M8 Connector, 29mm Housing Length

Series Number : 120253

Status : Not Recommended For New Design

Product Category : Inductive and Photoelectric Sensors

Engineering Number : DW-AS-622-M8-129



Documents & Resources

Specifications

[1202530418-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M8 Housing, 2mm Operating Distance, Embeddable, NPN, NC, 3-pin M8 Connector, 29mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130067084

Electrical

Output	NC
Polarity	NPN
Switching Frequency	≤ 5000 Hz

Physical

Connection	Connector (M8, 3-pin)
Length	29mm
Material - Housing	Stainless Steel
Material - Sensing Face	PA12
Mounting Style	Embeddable
Operating Distance	2mm
Output	NC
Sensor Housing Size	M8
Temperature Range - Operating	-25° to +70°C

This document was generated on Nov 07, 2025