



Part Number : [1202530209](#)
Product Description : Contrinex Inductive Sensor,
M8 Housing, 1.5mm Operating Distance, Embeddable,
PNP, NC, 4-pin M12 Connector, 45mm Housing Length
Series Number : 120253
Status : Not Recommended For New Design
Product Category : Inductive and Photoelectric
Sensors
Engineering Number : DW-AS-604-M8



Documents & Resources

Specifications

[1202530198-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M8 Housing, 1.5mm Operating Distance, Embeddable, PNP, NC, 4-pin M12 Connector, 45mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130063796

Electrical

Output	NC
Polarity	PNP
Switching Frequency	≤ 5000 Hz

Physical

Connection	Connector (M12, 4-pin)
Length	45mm
Material - Housing	Stainless Steel
Material - Sensing Face	PA66
Mounting Style	Embeddable
Operating Distance	1.5mm
Output	NC
Sensor Housing Size	M8

Temperature Range - Operating	-25° to +70°C
-------------------------------	---------------