








NOTES

1.MATERIAL

1-1 HOUSING: LCP THERMOPLASTIC. UL94V-0. COLOR: BLACK.
1-2 CONTACT: HIGH-PERFORMANCE COPPER ALLOY.
1-3 LATCH: STAINLESS STEEL.
1-4 PEG: STAINLESS STEEL.

2.FINISH

2-1 CONTACT: GOLD PLATING 1~3u" ON CONTACT AREA
AND 1~3u" GOLD PLATING ON SOLDER AREA
NICKEL 50u"~150u" UNDER-PLATING ALL OVER


2-2 PEG: 50~150u" TIN PLATING OVER
50~150u" NICKEL UNDER-PLATING ALL OVER

3.MSL LEVEL: MSL(MOISTURE SENSITIVITY LEVEL)=1.



4.IR REFLOW:

THE PEAK TEMPRATURE ON THE BOARD SHALL BE
MAINTAINED FOR 10 SECONDS AT 260±5°C.

TOLERANCE		 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED	
LINEAR	ANGLES		
X,±0.40	X°,± 3°		
.X,±0.30	.X°±	APPD: Jason	MAT'L:
.XX,±0.20	.XX°±	CHKD: Schumi	FINISH:
.XXX,±0.10	.XXX°±	DRWN: Lei Songping	Q'TY:

TITLE: DDR4 SODIMM 8.0H 260PIN STANDARD G/F TYPE.					
PART NO.		D4260-8001SR			
DWG NO.		C-D4260-80			
		UNITS	SCALE	SHEET	REV
		MM	1 : 1	1 OF 2	A0

REV	ECN NO.	NAME	DATE



2.55±0.15

0.30Max.

0.50

260-0.35±0.03

0.10 C B A

0.05 C


DETAIL E

SCALE 2:1

2-0.05

G

2:1



4.70	1.70	1.70	9.30	3.70
3.70	1.20	1.20	8.80	4.20
DIM. H	DIM. A	DIM. B	DIM. C	DIM. D

TITLE: DDR4 SODIMM 8.0H 260PIN STANDARD G/F TYPE.				
PART NO. D4260-8001SR				
DWG NO. C-D4260-80				
	UNITS	SCALE	SHEET	REV
	MM	1 : 1	2 OF 2	A0

	SEE SHEET 1		
REV	ECN NO.	NAME	DATE