

SPECIFICATIONS

Customer	
Product Name	Multi-layer Chip Ceramic Inductor
Sunlord Part Number	SDCL1608C24NJTDF
Customer Part Number	

[☒ New Released, ☐ Revised]

SPEC No.: SDCL0112240016

【This SPEC is total 9 pages including specifications and appendix.】

【ROHS Compliant Parts】

Approved By	Checked By	Issued By
		

Shenzhen Sunlord Electronics Co., Ltd.

Address: Sunlord Industrial Park, Dafuyuan Industrial Zone, Baoan, Shenzhen, China 518110
Tel: 0086-755-29832333 Fax: 0086-755-82269029 E-Mail: sunlord@sunlordinc.com

【For Customer approval Only】

Date: _____

Qualification Status: ☐ Full ☐ Restricted ☐ Rejected

Approved By	Verified By	Re-checked By	Checked By

Comments:

【Version change history】

Rev.	Effective Date	Changed Contents	Change Reasons	Approved By
01	Jun.22,2024	New release	/	Zeng Xiangdong

Caution

All products listed in this specification are developed, designed and intended for use in general electronics equipment. The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require especially high reliability, or whose failure, malfunction or trouble might directly cause damage to society, person, or property. Please understand that we are not in a position to be held responsible for any damage or the like caused by any use exceeding the range or conditions of this specification sheet or by any use in the specific applications. Please contact us for more details if you intend to use our products in the following applications.

1. Aircraft equipment
2. Aerospace equipment
3. Undersea equipment
4. nuclear control equipment
5. military equipment
6. Power plant equipment
7. Medical equipment
8. Transportation equipment (automobiles, trains, ships,etc.)
9. Traffic signal equipment
10. Disaster prevention / crime prevention equipment
11. Data-processing equipment
12. Applications of similar complexity or with reliability requirements comparable to the applications listed in the above

1. Scope

This specification applies to SDCL1608C24NJTDF of multi-layer ceramic chip inductor.

2. Product Description and Identification (Part Number)

- Description
SDCL1608C24NJTDF of multi-layer ceramic chip inductor.
- Product Identification (Part Number)

SDCL 1608 C 24N J I D E
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

①	Type
SDCL	Chip Ceramic Inductor

②	External Dimensions (L X W) (mm)
1608 [0603]	1.6 X 0.8

③	Material Code
C	

④	Nominal Inductance
Example	Nominal Value
24N	24nH

⑤	Inductance Tolerance
J	±5%

⑥	Packing
T	Tape Carrier Package

⑦	Internal Code
D	

⑧	HSF Products
Hazardous Substance Free Products	

3. Electrical Characteristics

Part Number	L (nH)	Q Min.	L, Q Test. Freq. (MHz)	Q (Typ.) Freq. (MHz)			S.R.F (MHz) Min	DCR(Ω) Max.	Ir (mA) Max.
				100	800	1000			
SDCL1608C24NJTDF	24	12	100	16	45	45	1700	0.65	300

- Operating and storage temperature range (individual chip without packing):-55°C~ +125°C
- Storage temperature range (packaging conditions): -10°C~+40°C and RH 70% (Max.)

4. Shape and Dimensions

- Dimensions and recommended PCB pattern for reflow soldering: See Fig.4-1, Fig.4-2 and Table 4-1.
- Structure: See Fig. 4-3 and Fig. 4-4.




Fig. 4-1




Fig. 4-2

[Table 4-1]

Unit: mm [inch]

Type	L	W	T	a	A	B	C
1608 [0603]	1.60±0.15 [0.063±0.006]	0.8±0.15 [0.031±0.006]	0.8±0.15 [0.031±0.006]	0.3±0.2 [0.012±0.008]	0.70	0.70	1.0




Fig. 4-3




Fig. 4-4

- ① Ceramic for SDCL Series
- ② Internal electrode (Ag)
- ③ Pull out electrode (Ag)
- ④-1 Terminal electrode: Inside (Ag)
- ④-2 Outside (Electro-plating Ni-Sn)

3) Material Information: See **Table 4-2**

[Table 4-2]

Code	Part Name	Material Name
①	Ceramic Body	Ceramic Powder
②	Inner Coils	Silver Paste
③	Pull-out Electrode (Ag)	Silver Paste
④-1	Terminal Electrode: Inside Ag	Termination Silver Composition
④-2	Electro-Plating: Ni/Sn plating	Plating Chemicals

5. Test and Measurement Procedures

5.1 Test Conditions

Unless otherwise specified, the standard atmospheric conditions for measurement/test as:

- Ambient Temperature: $20 \pm 15^{\circ}\text{C}$
- Relative Humidity: $65 \pm 20\%$
- Air Pressure: 86kPa to 106kPa

If any doubt on the results, measurements/tests should be made within the following limits:

- Ambient Temperature: $20 \pm 2^{\circ}\text{C}$
- Relative Humidity: $65 \pm 5\%$
- Air Pressure: 86kPa to 106kPa

5.2 Visual Examination

- Inspection Equipment: 20× magnifier

5.3 Electrical Test

5.3.1 DC Resistance (DCR)

- Refer to **Item 3**.
- Test equipment (Analyzer): High Accuracy Milliohmmeter-HP4338B or equivalent.

5.3.2 Inductance (L)

- Refer to **Item 3**.
- Test equipment: High Accuracy RF Impedance /Material Analyzer-E4991A+HP16192A or equivalent.
- Test signal: -20dBm or 50mV
- Test frequency refers to **Item 3**.

5.3.3 Q Factor (Q)

- Refer to **Item 3**.
Test equipment: High Accuracy RF Impedance /Material Analyzer-E4991A+HP16192A or equivalent.
- Test signal: -20dBm or 50mV
- Test frequency refers to **Item 3**.

5.3.4 Self-Resonant Frequency (SRF)

- Refer to **Item 3**.
Test equipment: High Accuracy RF Impedance /Material Analyzer- E4991A+HP16192A or Agilent E5071C Network analyzer(when SRF > 3GHz).
- Test signal: -20dBm or 50 mV

5.3.5 Rated Current

- Refer to **Item 3**.
- Test equipment (see **Fig. 5.3.5-1**): Electric Power, Electric current meter, Thermometer.
- Measurement method (see **Fig. 5.3.5-1**):
 - Set test current to be 0mA.
 - Measure initial temperature of chip surface.
 - Gradually increase voltage and measure chip temperature for corresponding current.
- Definition of Rated Current(Ir): Ir is direct electric current as chip surface temperature rose just 20°C against chip initial surface temperature(Ta) (see **Fig. 5.3.5-2**).




Fig. 5.3.5-1





Fig. 5.3.5-2

5.4 Reliability Test

The land dimensions for reliability test is :

A	B	C
0.70	0.70	1.0

Unit: mm








The thickness of Stencil is 0.08mm~0.1mm, add the standard thickness of solder paste: 0.10mm~0.15mm .


Solder shall be used as shown below.

$$1/3T \leq L \leq T$$

(T: height of electrode)



Items	Requirements	Test Methods and Remarks								
5.4.1 Terminal Strength	<p>No removal or split of the termination or other defects shall occur.</p>  <p>Fig.5.4.1-1</p>	<ol style="list-style-type: none">① Solder the inductor to the testing jig (glass epoxy board shown in Fig. 5.4.1-1) using leadfree solder. Then apply a force in the direction of the arrow.② 5N force for 1608 series.③ Keep time: 10±1s Speed: 1.0mm/s.④ The Scratch tool shall be keep a distance of 0.1mm from the Board.								
5.4.2 Resistance to Flexure	<p>No visible mechanical damage.</p> <table border="1"><thead><tr><th>Type</th><th>a</th><th>b</th><th>c</th></tr></thead><tbody><tr><td>1608[0603]</td><td>1.0</td><td>3.0</td><td>1.2</td></tr></tbody></table> <p>Unit: mm [inch]</p>  <p>Fig. 5.4.2-1</p>	Type	a	b	c	1608[0603]	1.0	3.0	1.2	<ol style="list-style-type: none">① Solder the inductor to the test jig (glass epoxy board shown in Fig. 5.4.2-1) Using a leadfree solder. Then apply a force in the direction shown Fig. 5.4.2-2.② Flexure: 2mm.③ Pressurizing Speed: 0.5mm/sec.④ Keep time: 30 sec.  <p>Fig. 5.4.2-2</p>
Type	a	b	c							
1608[0603]	1.0	3.0	1.2							
5.4.3 Vibration	<ol style="list-style-type: none">① No visible mechanical damage.② Inductance change: Within ±10%.③ Q factor change: Within ±20%.  <p>Glass Epoxy Board</p> <p>Fig. 5.4.3-1</p>	<ol style="list-style-type: none">① Solder the inductor to the testing jig (glass epoxy board shown in Fig. 5.4.3-1) using leadfree solder.② The inductor shall be subjected to a simple harmonic motion having total amplitude of 1.5mm, the frequency being varied uniformly between the approximate limits of 10 and 55 Hz.③ The frequency range from 10 to 55 Hz and return to 10 Hz shall be traversed in approximately 1 minute. This motion shall be applied for a period of 2 hours in each 3 mutually perpendicular directions (total of 6 hours).								
5.4.4 Dropping	<ol style="list-style-type: none">① No visible mechanical damage.② Inductance change: Within ±10%.③ Q factor change: Within ±20%.	Drop chip inductor 10 times on a concrete floor from a height of 100 cm.								
5.4.5 Temperature	Inductance change should be within ±10% of initial value measuring at 20°C.	Temperature range: -55°C to +125°C, Reference temperature: 20°C								

5.4.6 Solderability	① No visible mechanical damage. ② Wetting shall exceed 75% coverage for 0603 series; exceed 95% for others	① Solder temperature: $240 \pm 2^{\circ}\text{C}$ ② Duration: 3 sec. ③ Solder: Sn/3.0Ag/0.5Cu. ④ Flux: 25% Resin and 75% ethanol in weight.
5.4.7 Resistance to Soldering Heat	① No visible mechanical damage. ② Wetting shall exceed 75% coverage for 0603 series; exceed 95% coverage for others ③ Inductance change: Within $\pm 10\%$. ④ Q factor change: Within $\pm 20\%$.	① Solder temperature: $260 \pm 3^{\circ}\text{C}$ ② Duration: 5 sec. ③ Solder: Sn/3.0Ag/0.5Cu. ④ Flux: 25% Resin and 75% ethanol in weight. ⑤ The chip shall be stabilized at normal condition for 1~2 hours before measuring.
5.4.8 Thermal Shock	① No mechanical damage. ② Inductance change: Within $\pm 10\%$. ③ Q factor change: Within $\pm 20\%$. 	① Temperature, Time: (See Fig. 5.4.8-1) -55°C for 30 ± 3 min \rightarrow 125°C for 30 ± 3 min, ② Transforming interval: Max. 20 sec. ③ Tested cycle: 100 cycles. ④ The chip shall be stabilized at normal condition for 1~2 hours before measuring.
5.4.9 Resistance to Low Temperature	① No mechanical damage. ② Inductance change: Within $\pm 10\%$. ③ Q factor change: Within $\pm 20\%$.	① Temperature: $-55 \pm 2^{\circ}\text{C}$, ② Duration: 1000^{+24} hours. ③ The chip shall be stabilized at normal condition for 1~2 hours before measuring.
5.4.10 Resistance to High Temperature	① No mechanical damage. ② Inductance change: Within $\pm 10\%$. ③ Q factor change: Within $\pm 20\%$.	① Temperature: $125 \pm 2^{\circ}\text{C}$, ② Duration: 1000^{+24} hours. ③ The chip shall be stabilized at normal condition for 1~2 hours before measuring.
5.4.11 Damp Heat (Steady States)	① No visible mechanical damage. ② Inductance change: Within $\pm 10\%$. ③ Q factor change: Within $\pm 20\%$.	① Temperature: $60 \pm 2^{\circ}\text{C}$ ② Humidity: 90% to 95% RH. ③ Duration: 1000^{+24} hours. ④ The chip shall be stabilized at normal condition for 1~2 hours before measuring.
5.4.12 Loading Under Damp Heat	① No visible mechanical damage. ② Inductance change: Within $\pm 10\%$. ③ Q factor change: Within $\pm 20\%$.	① Temperature: $60 \pm 2^{\circ}\text{C}$ ② Humidity: 90% to 95% RH. ③ Duration: 1000^{+24} hours. ④ Applied current: Rated current. ⑤ The chip shall be stabilized at normal condition for 1~2 hours before measuring.
5.4.13 Loading at High Temperature (Life Test)	① No visible mechanical damage. ② Inductance change: Within $\pm 10\%$. ③ Q factor change: Within $\pm 20\%$.	① Temperature: $125 \pm 2^{\circ}\text{C}$, ② Duration: 1000^{+24} hours. ③ Applied current: Rated current. ④ The chip shall be stabilized at normal condition for 1~2 hours before measuring.

6. Packaging, Storage

6.1 Packaging

Tape Carrier Packaging:

Packaging code: T

- Tape carrier packaging are specified in attached figure Fig.6.1-1~3
- Tape carrier packaging quantity please see the following table:


Type	1608[0603]
T(mm)	0.8 ± 0.15
Tape	Paper Tape
Quantity	4K

7. Recommended Soldering Technologies

7.1 Re-flowing Profile:

- △ Preheat condition: 150 ~200°C/60~120sec.
- △ Allowed time above 217°C: 60~90sec.
- △ Max temp: 260°C
- △ Max time at max temp: 10sec.
- △ Solder paste: Sn/3.0Ag/0.5Cu
- △ Allowed Reflow time: 2x max

[Note: The reflow profile in the above table is only for qualification and is not meant to specify board assembly profiles. Actual board assembly profiles must be based on the customer's specific board design, solder paste and process, and should not exceed the parameters as the Reflow profile shows.]



7.2 Iron Soldering Profile.

- △ Iron soldering power: Max.30W.
- △ Pre-heating: 150 °C / 60 sec.
- △ Soldering Tip temperature: 350°C Max.
- △ Soldering time: 3sec Max.
- △ Solder paste: Sn/3.0Ag/0.5Cu.
- △ Max.1 times for iron soldering.

[Note: Take care not to apply the tip of the soldering iron to the terminal electrodes.]

