


SM4FJ Series

Transient Voltage Suppressor

Features

- Excellent clamping capability
- Low leakage current
- Low capacitance
- High surge capability
- Glass passivated chip
- Epoxy resin package
- Built-in strain relief
- Will not fatigue
- RoHS Compliant
- Fast response time:
typically less than 1.0ps from 0 Volts to V_{BR} min

Package




Mechanical Characteristics

- Package: SOD-123FL plastic package
- Lead Finish: Matte Tin
- Case Material: Epoxy Molding Compound
- UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020

Applications

- Cellular phones
- Portable devices
- Business machines
- Power supplies
- Consumer applications

Making Code



Summary of Packing Options

Package	Packing Description	Packing Quantity	Industry Standard
SOD-123FL	Tape/Reel, 7" reel	3000	EIA-481-1
	Tape/Reel, 13" reel	10000	EIA-481-1




SM4FJ Series

Transient Voltage Suppressor

Electrical Parameters

Parameter	Definition
C_J	Junction Capacitance - typical capacitance measured with 0V or V_R bias
I_{PP}	Peak Pulse Current - maximum rated peak impulse current
V_C	Clamping Voltage - Peak voltage measured across the suppressor at a specified I_{ppm}
V_{BR}	Breakdown Voltage - Maximum voltage that flows though the TVS at a specified test current (I_T)
I_R	Leakage Current - maximum peak off-state current measured at V_R
V_R	Peak Off-state Voltage - maximum voltage that can be applied while maintaining off state



Absolute Maximum Ratings ($T_A=+25^{\circ}\text{C}$, unless otherwise noted)

Parameter	Symbol	Value	Units
Peak Pulse Power Dissipation(Note1,2)	P_{PPM}	400	W
Steady State Power Dissipation (Note3)	P_D	3.3	W
Peak Forward Surge Current (Note4)	I_{FSM}	40	A
Maximum Instantaneous Forward Voltage at 10A (Note5)	V_{FM}	3.5	V
Typical Thermal Resistance Junction to Lead	$R_{\theta JL}$	100	$^{\circ}\text{C/W}$
Typical Thermal Resistance Junction to Ambient	$R_{\theta JA}$	220	$^{\circ}\text{C/W}$
Operating Junction Temperature Range	T_J	-55 to 150	$^{\circ}\text{C}$
Storage Temperature Range	T_{STG}	-55 to 150	$^{\circ}\text{C}$

Notes:

- (1) Non-repetitive current pulse , 10/1000us Waveform.
- (2) Mounted on copper pad area of 3×3mm to each terminal.
- (3) Infinite Heat Sink at $T_A = 50^{\circ}\text{C}$
- (4) Measured on 8.3ms single half sine wave or equivalent square wave, duty cycle=4 perminute maximum.
- (5) For UnidirectionalOnly.



SM4FJ Series

Transient Voltage Suppressor

Absolute Maximum Ratings ($T_A=+25^{\circ}\text{C}$, unless otherwise noted)

Part Number		Marking Code		Reverse Stand-Off Voltage V_R	Breakdown Voltage $V_{BR}@ I_T$		Test Current I_T	Maximum Clamping Voltage $V_C@ I_{pp}$	Maximum Peak Pulse Current I_{pp}	Maximum Reverse Leakage $I_R@ V_R$
(Uni)	(Bi)	(Uni)	(Bi)	(V)	Min.(V)	Max.(V)	(mA)	(V)	(A)	(μA)
SM4FJ5.0A	SM4FJ5.0CA	5.0A	5.0CA	5	6.4	7	10	9.2	43.5	400
SM4FJ6.0A	SM4FJ6.0CA	6.0A	6.0CA	6	6.67	7.37	10	10.3	38.8	400
SM4FJ6.5A	SM4FJ6.5CA	6.5A	6.5CA	6.5	7.22	7.98	10	11.2	35.7	250
SM4FJ7.0A	SM4FJ7.0CA	7.0A	7.0CA	7	7.78	8.6	10	12	33.3	100
SM4FJ7.5A	SM4FJ7.5CA	7.5A	7.5CA	7.5	8.33	9.21	1	12.9	31	50
SM4FJ8.0A	SM4FJ8.0CA	8.0A	8.0CA	8.0	8.89	9.83	1	13.6	29.4	25
SM4FJ8.5A	SM4FJ8.5CA	8.5A	8.5CA	8.5	9.44	10.4	1	14.4	27.8	10
SM4FJ9.0A	SM4FJ9.0CA	9.0A	9.0CA	9.0	10	11.1	1	15.4	26	5
SM4FJ10A	SM4FJ10CA	10A	10CA	10	11.1	12.3	1	17	23.5	2.5
SM4FJ11A	SM4FJ11CA	11A	11CA	11	12.2	13.5	1	18.2	22	2.5
SM4FJ12A	SM4FJ12CA	12A	12CA	12	13.3	14.7	1	19.9	20.1	2.5
SM4FJ13A	SM4FJ13CA	13A	13CA	13	14.4	15.9	1	21.5	18.6	1
SM4FJ14A	SM4FJ14CA	14A	14CA	14	15.6	17.2	1	23.2	17.2	1
SM4FJ15A	SM4FJ15CA	15A	15CA	15	16.7	18.5	1	24.4	16.4	1
SM4FJ16A	SM4FJ16CA	16A	16CA	16	17.8	19.7	1	26	15.4	1
SM4FJ17A	SM4FJ17CA	17A	17CA	17	18.9	20.9	1	27.6	14.5	1
SM4FJ18A	SM4FJ18CA	18A	18CA	18	20	22.1	1	29.2	13.7	1
SM4FJ20A	SM4FJ20CA	20A	20CA	20	22.2	24.5	1	32.4	12.3	1
SM4FJ22A	SM4FJ22CA	22A	22CA	22	24.4	26.9	1	35.5	11.3	1
SM4FJ24A	SM4FJ24CA	24A	24CA	24	26.7	29.5	1	38.9	10.3	1
SM4FJ26A	SM4FJ26CA	26A	26CA	26	28.9	31.9	1	42.1	9.5	1
SM4FJ28A	SM4FJ28CA	28A	28CA	28	31.1	34.4	1	45.4	8.8	1
SM4FJ30A	SM4FJ30CA	30A	30CA	30	33.3	36.8	1	48.4	8.3	1
SM4FJ33A	SM4FJ33CA	33A	33CA	33	36.7	40.6	1	53.3	7.5	1
SM4FJ36A	SM4FJ36CA	36A	36CA	36	40	44.2	1	58.1	6.9	1
SM4FJ40A	SM4FJ40CA	40A	40CA	40	44.4	49.1	1	64.5	6.2	1
SM4FJ43A	SM4FJ43CA	43A	43CA	43	47.8	52.8	1	69.4	5.8	1
SM4FJ45A	SM4FJ45CA	45A	45CA	45	50	55.3	1	72.7	5.5	1
SM4FJ48A	SM4FJ48CA	48A	48CA	48	53.33	58.9	1	77.4	5.2	1
SM4FJ51A	SM4FJ51CA	51A	51CA	51	56.7	62.7	1	82.4	4.9	1
SM4FJ54A	SM4FJ54CA	54A	54CA	54	60	66.3	1	87.1	4.6	1
SM4FJ58A	SM4FJ58CA	58A	58CA	58	64.4	71.2	1	93.6	4.3	1
SM4FJ60A	SM4FJ60CA	60A	60CA	60	66.7	73.7	1	96.8	4.1	1



SM4FJ Series

Transient Voltage Suppressor

Absolute Maximum Ratings ($T_A=+25^{\circ}\text{C}$, unless otherwise noted)

Part Number		Marking Code		Reverse Stand-Off Voltage V_R	Breakdown Voltage $V_{BR}@ I_T$		Test Current I_T	Maximum Clamping Voltage $V_C@ I_{pp}$	Maximum Peak Pulse Current I_{pp}	Maximum Reverse Leakage $I_R@ V_R$
(Uni)	(Bi)	(Uni)	(Bi)	(V)	Min.(V)	Max.(V)	(mA)	(V)	(A)	(uA)
SM4FJ64A	SM4FJ64CA	64A	64CA	64	71.1	78.6	1	103	3.9	1
SM4FJ70A	SM4FJ70CA	70A	70CA	70	78.8	86	1	113	3.5	1
SM4FJ75A	SM4FJ75CA	75A	75CA	75	83.3	92.1	1	121	3.3	1
SM4FJ78A	SM4FJ78CA	78A	78CA	78	86.7	95.8	1	126	3.2	1
SM4FJ85A	SM4FJ85CA	85A	85CA	85	94.4	104	1	137	2.9	1
SM4FJ90A	SM4FJ90CA	90A	90CA	90	100	111	1	146	2.7	1
SM4FJ100A	SM4FJ100CA	100A	100CA	100	111	123	1	162	2.5	1
SM4FJ110A	SM4FJ110CA	110A	110CA	110	122	135	1	177	2.3	1
SM4FJ120A	SM4FJ120CA	120A	120CA	120	133	147	1	193	2.1	1
SM4FJ130A	SM4FJ130CA	130A	130CA	130	144	159	1	209	1.9	1
SM4FJ150A	SM4FJ150CA	150A	150CA	150	167	185	1	243	1.6	1
SM4FJ160A	SM4FJ160CA	160A	160CA	160	178	197	1	259	1.5	1
SM4FJ170A	SM4FJ170CA	170A	170CA	170	189	209	1	275	1.5	1



SM4FJ Series

Transient Voltage Suppressor

Ratings and Characteristic Curves ($T_A = +25^\circ\text{C}$, unless otherwise noted)

Figure 1: Peak Pulse Power Rating




Figure 2: Pulse Derating Curve




Figure 3: Pulse Waveform




Figure 4: Typical Junction Capacitance




Figure 5: Steady State Power Dissipation Derating

Curve





Figure 6: Maximum Non-Repetitive Peak Forward

Surge Current Uni-Directional Only



Transient Voltage Suppressor


The graph illustrates the temperature profile over time for a fire. The y-axis represents Temperature (t) and the x-axis represents Time(t). Key temperature levels marked on the y-axis are 25, $T_{s(min)}$, $T_{s(max)}$, T_L , and T_P . Key time intervals marked on the x-axis are t_s (Preheat), t_L (Ramp-up), and t_p (Peak). The curve shows a preheat phase, a ramp-up to peak temperature T_P , a peak duration t_p , and a subsequent ramp-down. The ramp-down is divided into a 'Critical Zone' from T_P to T_L and a lower temperature region. The time from T_L to T_P is t_L . The graph is divided into three shaded regions: light gray for preheat, medium gray for the ramp-up, and dark gray for the critical zone.

Reflow Condition		Lead-free assembly
Pre Heat	- Temperature Min ($T_S(\text{min})$)	150°C
	- Temperature Max ($T_S(\text{max})$)	200°C
	- Time (min to max) (t_S)	60 - 180 secs
Average ramp up rate (Liquidus Temp (T_L) to peak)		3°C/second max
$T_S(\text{max})$ to T_L - Ramp-up Rate		3°C/second max
Reflow	- Temperature (T_L) (Liquidus)	217°C
	- Time (t_L)	60 - 150 secs
Peak Temperature (T_P)		260 ^{+0/-5} °C
Time within 5°C of actual peak Temperature (t_p)		20 - 40 secs
Ramp-down Rate		6°C/second max
Time 25°C to peak Temperature (t)		8 minutes Max.
Do not exceed		260°C

SM4FJ Series


Transient Voltage Suppressor

Package Mechanical Data - SOD-123FL




SYMBOL	MILLIMETER		
	MIN.	Typ.	MAX.
A	1.50	1.75	2.00
B	3.40	3.65	3.90
C	0.70	0.95	1.20
D	2.50	2.70	2.90
F	0.05	0.15	0.26
G	0.00	—	0.10
H	0.95	1.15	1.35
L	0.35	0.63	0.90

Packaging Tape - SOD-123FL



SYMBOL	MILLIMETER
A0	2.10±0.1
B0	4.0 ±0.1
d0	1.5±0.1
d1	1.0±0.1
E	1.75±0.1
F	3.50±0.1
K0	1.25±0.1
P	4.00±0.1
P0	4.00±0.1
P1	2.00±0.1
W	8.00±0.1
T	0.2±0.02

Packaging Reel



SYMBOL	MILLIMETER
A	177.8±0.2
B	2.7±0.2
C	13.5±0.2
D	9.6±0.3
E	54.5±0.2
F	12.3±0.3
T1	1.0±0.2
Quantity	3000PCS

