



Part Number : [1202530616](#)
Product Description : Contrinex Inductive Sensor,
M5 Fully Stainless Steel, 3mm Operating Distance,
Non-embeddable, PNP, NC, 0.2m 3-wire PUR Cable, 3-
pin M8 Connector, 30mm Housing Length
Series Number : 120253
Status : Not Recommended For New Design
Product Category : Inductive and Photoelectric
Sensors
Engineering Number : DW-AV-714-M5-276



Documents & Resources

Specifications

[1202530609-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M5 Fully Stainless Steel, 3mm Operating Distance, Non-embeddable, PNP, NC, 0.2m 3-wire PUR Cable, 3-pin M8 Connector, 30mm Housing Length
IP Rating	IP68, IP69K
Product Name	Contrinex
Type	Inductive
UPC	191130064649

Electrical

Output	NC
Polarity	PNP
Switching Frequency	≤ 1200 Hz

Physical

Connection	Cable (PUR 0.2m, 3-wire), Connector (M8, 3-pin)
Length	30mm
Material - Housing	Stainless Steel
Material - Sensing Face	Stainless Steel
Mounting Style	Non-embeddable

Operating Distance	3mm
Output	NC
Sensor Housing Size	M5
Temperature Range - Operating	-25° to +85°C