








| GH1. 25mm贴片      | A-(mm) | B-(mm) | C-(mm) |
|------------------|--------|--------|--------|
| GH1. 25mm-2P-WT  | 1.25   | 3.80   | 5.75   |
| GH1. 25mm-3P-WT  | 2.50   | 5.05   | 7.00   |
| GH1. 25mm-4P-WT  | 3.75   | 6.30   | 8.25   |
| GH1. 25mm-5P-WT  | 5.00   | 7.55   | 9.50   |
| GH1. 25mm-6P-WT  | 6.25   | 8.80   | 10.75  |
| GH1. 25mm-7P-WT  | 7.50   | 10.05  | 12.00  |
| GH1. 25mm-8P-WT  | 8.75   | 11.30  | 13.25  |
| GH1. 25mm-9P-WT  | 10.00  | 12.55  | 14.50  |
| GH1. 25mm-10P-WT | 11.25  | 13.80  | 15.75  |
| GH1. 25mm-11P-WT | 12.50  | 15.05  | 17.00  |
| GH1. 25mm-12P-WT | 13.75  | 16.30  | 18.25  |
| GH1. 25mm-13P-WT | 15.00  | 17.55  | 19.50  |
| GH1. 25mm-14P-WT | 16.25  | 18.80  | 20.75  |
| GH1. 25mm-15P-WT | 17.50  | 20.05  | 22.00  |
| GH1. 25mm-16P-WT | 18.75  | 21.30  | 23.25  |

## 技术要求

### 1: 外观要求

1-1. 插针表面光洁、无损伤、锈蚀等缺陷。

1-2. 基座表面无脏污、飞边、排气不良等缺陷。

### 2: 电气性能:

2-1. 额度电流: 1.0A

2-2. 额定电压: 50V

2-3. 耐 电 压: 500V

2-4. 接触电阻:  $\leq 20\text{m}\Omega$

2-5. 绝缘电阻:  $\geq 100\text{m}\Omega$

### 3: 工作温度: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

|        |  |                                                                                                                                                                             |                                                                                                     |      |                 |     |      |         |
|--------|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------|------|-----------------|-----|------|---------|
| >20    |  | ±0.25                                                                                                                                                                       | 序号                                                                                                  | 材料名称 | 数量              | 材质  | 镀涂   | REMARK  |
| >10≤20 |  | ±0.2                                                                                                                                                                        | ①                                                                                                   | 卧贴针  | n               | 磷铜  | 高温亮锡 | GP PASS |
| >3≤10  |  | ±0.15                                                                                                                                                                       | ②                                                                                                   | 塑件   | 1               | LCP | /    | GP PASS |
| 3≤     |  | ±0.1                                                                                                                                                                        | ③                                                                                                   | 焊片   | 2               | 磷铜  | 高温亮锡 | GP PASS |
| 尺寸范围   |  | 公差                                                                                                                                                                          |                                                                                                     |      |                 |     |      |         |
| 设计     |  |                                                                                                                                                                             | 产品名称                                                                                                |      | GH1. 25mm-6P-卧贴 |     |      |         |
| 审核     |  |                                                                                                                                                                             |                                                                                                     |      |                 |     |      |         |
| 批准     |  |                                                                                                                                                                             |                                                                                                     |      |                 |     |      |         |
| 单位: mm |  |   |  连兴旺电子(深圳)有限公司 |      |                 |     |      |         |
|        |  |                                                                                                                                                                             | LXWCONN ELECTRONICS (SHENZHEN) CO., LTD                                                             |      |                 |     |      |         |