



### Features

- Epitaxial planar die construction
- Built-in biasing resistors ( $R_1$ : 22k $\Omega$ ,  $R_2$ : 47k $\Omega$ )
- Also available in lead free version
- RoHS compliant with Halogen-free

### Mechanical Data

- Case: SOT-23
- Molding Compound: UL Flammability Classification Rating 94V-0
- Terminals: Matte tin-plated leads; solderability-per MIL-STD-202, Method 208



### Ordering Information

Part Number	Package	Shipping Quantity
DDTC124XCA	SOT-23	3000 pcs / Tape & Reel

### Maximum Ratings (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Value	Unit
		SOT-23	
Supply Voltage	$V_{CC}$	50	V
Input Voltage	$V_I$	-10 to +40	V
Output Current	$I_O$	50	mA
Collector Current	$I_{C(\text{Max})}$	100	mA
Power Dissipation	$P_D$	200	mW
Junction Temperature Range	$T_J$	-55 ~ +150	$^\circ\text{C}$
Storage Temperature Range	$T_{STG}$	-55 ~ +150	$^\circ\text{C}$

### Electrical Characteristics (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Input Voltage	$V_{I(OFF)}$	$V_{CC} = 5V, I_o = 100\mu A$	0.4	-	-	V
Input Voltage	$V_{I(ON)}$	$V_o = 0.3V, I_o = 2mA$	-	-	2.5	V
Output Voltage	$V_{O(on)}$	$I_o = 10mA, I_i = 0.5mA$	-	-	0.3	V
Input Current	$I_i$	$V_i = 5V$	-	-	0.36	mA
Output Current	$I_{O(off)}$	$V_{CC} = 50V, V_i = 0V$	-	-	0.5	$\mu A$
DC Current Gain	$G_i$	$V_o = 5V, I_o = 10mA$	68	-	-	-
Input Resistor	$R_i$		15.4	22	28.6	k $\Omega$
Resistance ratio	$R_2/R_1$		1.7	2.1	2.6	-
Gain-Bandwidth Product	$f_T$	$V_{CE} = 10V, I_E = 5mA$ $f = 100MHz$	-	250	-	MHz

### Ratings and Characteristic Curves (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)




Fig 1 Input Voltage vs Output Current




Fig 2 Output Current vs Input Voltage




Fig 3 DC Current Gain vs Output Current





Fig 4 Output Voltage vs Output Current

**Package information (Unit: mm)**

**SOT-23**



**Mounting Pad Layout (Unit: mm)**

