


### Features

- High Accurate  $\pm 2\%$
- Precision VCC Monitoring of +2.5V, +3V, +3.3V and +5V Supplies
- Power Supply Transient Immunity
- Guaranteed Reset Valid to  $VCC=+1V$
- Fully Specified Over Temperature
- 2 $\mu$ A Supply Current
- Available in One Output Configuration: Open-Drain Active-Low  $\overline{\text{RESET}}$  Output
- Packages SOT-23

### Applications

- Computers
- Embedded Systems
- Battery-Powered Equipments
- Intelligent Instruments
- CPU and Logic Circuit Reset
- Power Fail Detectors
- Automotive

### Pin Definition



### Ordering Information

TPMCP120T-315/TT

RESET VOLTAGE:

475=4.63V  
450=4.38V  
315=3.08V  
300=2.93V  
270=2.63V


### PIN CONFIGURATION

PIN	NAME	FUNCTION
1	GND	Ground
2	$\overline{\text{RESET}}$	$\overline{\text{RESET}}$ Output remains low while VCC is below the reset threshold, and for at least 140ms after VCC rises above the reset threshold.
3	VCC	+5V, +3.3V, +3V or +2.5V Supply Voltage .


### Absolute Maximum Ratings

Symbol	Parameter	Value	UNIT
VCC	Supply Voltage	-0.3 to +6.0	V
	$\overline{\text{RESET}}$	-0.3 to +6.0	V
ICC	Input Current, VCC	20	mA
IO	Output Current, $\overline{\text{RESET}}$	20	mA
	Rate of Rise, VCC	100	V/ $\mu$ s
PD	Continuous Power Dissipation Derate 4mW/ $^{\circ}$ C above 70 $^{\circ}$ C	320	mW
TA	Operating Temperature Range	-40 to +105	$^{\circ}$ C
TSTG	Storage Temperature Range	-65 to +150	$^{\circ}$ C
$R_{\theta JC}$	Thermal Resistance from Junction to Case	110	$^{\circ}$ C/W
$R_{\theta JA}$	Thermal Resistance from Junction to Ambient	250	$^{\circ}$ C/W

### TYPICAL APPLICATION CIRCUIT



### FUNCTIONAL BLOCK DIAGRAM




**Electrical Characteristics**


Symbol	Parameter	Conditions	MIN	Typ	MAX	UNIT			
VCC	Supply Voltage Range	TA=0°C to +70°C	1.0	--	5.5	V			
ICC	Supply Current		--	2.0	--	uA			
VTH	Reset Threshold	475 Version	TA=+25°C	4.56	4.63	4.70	V		
			TA=-40°C to +85°C	4.50	--	4.75			
		450 Version	TA=+25°C	4.31	4.38	4.45			
			TA=-40°C to +85°C	4.25	--	4.50			
		315 Version	TA=+25°C	3.04	3.08	3.11			
			TA=-40°C to +85°C	3.00	--	3.15			
		300 Version	TA=+25°C	2.89	2.93	2.96			
			TA=-40°C to +85°C	2.85	--	3.00			
		270 Version	TA=+25°C	2.59	2.63	2.66			
			TA=-40°C to +85°C	2.55	--	2.70			
			Reset Threshold Tempco		--	150		--	ppm/°C
			VCC to Reset Delay	VCC=VTH to (VTH-100mV)	--	10		--	μS
TRP	Reset Active Timeout Period		140	240	560	mS			
VOL	RESET Output Voltage Low	VCC=VTH min, ISINK=1.2mA, T_/S_/R_/Z_	--	--	0.3	V			
		VCC=VTH min, ISINK=3.2mA, T_/S_/R_/Z_	--	--	0.4				
		VCC>1.0V, ISINK=50μA	--	--	0.3				
	RESET Open-Drain Output Leakage Current	VCC>VTH, RESET Deasserted	--	--	1	μA			

**Typical Operating Characteristics**( $T_A=+25^{\circ}\text{C}$ , unless otherwise noted.)


**Supply Current vs. Temperature**



**Power-Down RESET Delay vs. Temperature**




**Power-Up RESET Timeout vs. Temperature**



**Package Outline Dimensions (unit: mm)**

SOT-23



**Mounting Pad Layout (unit: mm)**

