





SH1.0mm贴片	A-(mm)	B-(mm)	C-(mm)
SH1.0mm-2P-LT	1.0	2.6	4.4
SH1.0mm-3P-LT	2.0	3.6	5.4
SH1.0mm-4P-LT	3.0	4.6	6.4
SH1.0mm-5P-LT	4.0	5.6	7.4
SH1.0mm-6P-LT	5.0	6.6	8.4
SH1.0mm-7P-LT	6.0	7.6	9.4
SH1.0mm-8P-LT	7.0	8.6	10.4
SH1.0mm-9P-LT	8.0	9.6	11.4
SH1.0mm-10P-LT	9.0	10.6	12.4
SH1.0mm-11P-LT	10.0	11.6	13.4
SH1.0mm-12P-LT	11.0	12.6	14.4
SH1.0mm-13P-LT	12.0	13.6	15.4
SH1.0mm-14P-LT	13.0	14.6	16.4
SH1.0mm-15P-LT	14.0	15.6	17.4
SH1.0mm-16P-LT	15.0	16.6	18.4



P.C.B LAYOUT

技术要求

1: 外观要求

1-1. 插针表面光洁、无损伤、锈蚀等缺陷。

1-2. 基座表面无脏污、飞边、排气不良等缺陷。

2:电气性能:

2-1. 额度电流: 1.0A

2-2. 额定电压: 50V

2-3.耐电压: 500V

2-4. 接触电阻: $\leq 20\text{m}\Omega$

2-5. 绝缘电阻: $\geq 100\text{m}\Omega$

3: 工作温度: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

>20	±0.25	序号	材料名称	数量	材质	镀涂	REMARK
>10≤20	±0.2	①	立贴针	n	磷铜	高温亮锡	GP PAS
>3≤10	±0.15	②	塑件	1	LCP	／	GP PAS
3≤	±0.1	③	焊片	2	磷铜	高温亮锡	GP PAS
尺寸范围	公差	③	吸附盖	1	／	／	GP PAS
设计		产品名称		SH1.0mm-4P-立贴-加盖			
审核							
批准							
单位: mm	 			连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD			