



REV.	ECN NO	LOCATIONS	DESCRIPTION	DATE



Specification:

- Electrical Characteristics:**
Contact Current Rating: 3 Amperes Max.
Rated Voltage: 30V Max.
Dielectric Withstanding Voltage: AC 100V r.m.s.
Insulation Resistance: 100 MΩ Minimum.
Contact Resistance: 40 mΩ Maximum.
- Environmental:**
Operating Temperature: -40°C~+85°C.
- Mechanical Characteristics:**
Insertion Force: 5~20Nf.
Withdrawal Force: 6~20Nf.
Durability Cycles: 5000 Cycles.
- ⊗ Make is FAI test Dimension
▼ Make is major test Dimension

A5	CC1	B5	CC2
A9	VBUS	B9	VBUS
A12	GND	B12	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME



① 01 S B X X X X X X X X - 6
② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪ ⑫ ⑬ ⑭ ⑮ ⑯ ⑰ ⑱ ⑲ ⑳ ㉑ ㉒ ㉓ ㉔ ㉕ ㉖ ㉗ ㉘ ㉙ ㉚ ㉛ ㉜ ㉝ ㉞ ㉟ ㊱ ㊲ ㊳ ㊴ ㊵ ㊶ ㊷ ㊸ ㊹ ㊺ ㊻ ㊼ ㊽ ㊾ ㊿

外壳材质
1:C2680R-H
2:SUS201R-H
6:SUS201R-H
7:SUS304R-1/2H

外壳电镀
1:Ni80u''
2:Sn80u''
3:Ni+Au1u'' (脚)

端子电镀01:Ni+Au1u'' ;02:Au1.5u'' ;03:Au3u''

主体颜色A:灰 B:黑色 G:绿色

主体材质 1:LCP 2:PA9T

端子材质1:C2680R-EH 3:C5191R-EH

RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

PART NO: 5		A01SB2111A01-67		MATERIAL: SEE NOTE	
MODEL NO:		XX		FINISH: SEE NOTE	
UNIT: MM		SIZE: A4		COLOR: SEE NOTE	
TOLERANCE UNSPECIFIED				DR:	
.x		±0.15		CHK:	
.xx		±0.10		APP:	
.xxx		±0.05			
Ang.		±1°			

 连兴旺电子(深圳)有限公司		LXWCONN ELECTRONICS (SHENZHEN) CO., LTD	
TITLE: TYPE-C 6PIN板上四脚插6.8无弹SMT			
DWG NO: A067		REV: A	
SCALE: 1:1	DATE: 2021.02.25		