




REV.	EC#	DESCRIPTION	DATE	DRAWING
A0		NEW RELEASE	07/12'16	YZZ
A1	ECN2101009	NEW RELEASE	01/12'21	QY
A2		Modify the view	11/17'22	LHP.LIU

---

**NOTES:**

1. MATERIAL:
    - 1.1 HOUSING: LCP UL94V-0; COLOR: BLACK
    - 1.2 TERMINAL: C5191
    - 1.3 SHELL: SUS201
  2. FINISH:
    - 2.1 TERMINAL: G/F PLATED ON CONTACT AREA;  
G/F PLATED ON SOLDER AREA;  
Ni 20 $\mu$ " MIN. UNDERPLATED OVERALL.
    - 2.2 SHELL: G/F PLATED ON SOLDER AREA;  
Ni 20 $\mu$ " MIN. PLATED OVERALL
  3. ELECTRICAL SPECIFICATION:
    - 3.1 RATED CURRENT: 0.5A.
    - 3.2 RATED VOLTAGE: 30V.
    - 3.3 CONTACT RESISTANCE: 100m $\Omega$  MAX.
    - 3.4 INSULATION RESISTANCE: 1000M $\Omega$  MIN 500V DC.
    - 3.5 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC .
  4. MACHINERY SPECIFICATION:
    - 4.1 MATING FORCE: 40N MAX.  
UNMATING FORCE: 0.5N~40N.
    - 4.2 DURABILITY: 3000 CYCLES MIN.
  5. ENVIRONMENTAL SPECIFICATION:
    - 5.1 OPERATING CONDITION: TEMPERATURE -40°C~+85°C;  
HUMIDITY 80% R.H MAX
    - 5.2 SALT SPRAY: 24H(CONTACT AREA)
  6. SOLDER ABILITY: 245±5°C, 5±0.5s
  7. IR REFLOW: THE PEAK TEMPERATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260°C.



MILLIMETERS	INCH
X.* $\pm 2^{\circ}$	X.* $\pm 2^{\circ}$
X . $\pm 0.30$	.X . $\pm 0.012$
XX . $\pm 0.20$	.XX . $\pm 0.008$
XXX . $\pm 0.10$	.XXX . $\pm 0.004$

THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF DongGuAn JinBiLai  
Metal Plastic Technology Co.,Ltd  
COPIED OR USED IN ANY MANNER WITHOUT THE  
PRIOR WRITTEN CONSENT OF DongGuAn  
JinBiLai Metal Plastic Technology Co.,Ltd




东莞市金比莱五金塑胶科技有限公司  
DONGGUAN JBL TECH CO., LTD



TITLE	1.5H TF 短体开关中间PIN B版本			DR		
PART NO.	402012262-A			CHKD		
PRO J.	PAGE	1/2	UNITS	mm	APPD	
	SIZE	A4	SCALE	1:1	DIS NO.	

1 2 3 4 5 6 7

RoHS




USER DIRECTION OF UNREELING




## NOTES

1. NUMBER OF CONNECTORS: 2500PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 27500PCS/CARTON



MILLIMETERS	INCH
X. ±2'	X. ±2"
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF Dongguan JinBilai  
Metal Plastic Technology Co.,Ltd  
COPIED OR USED IN ANY MANNER WITHOUT THE  
PRIOR WRITTEN CONSENT OF Dongguan  
JinBilai Metal Plastic Technology Co.,Ltd



东莞市金比莱五金塑胶科技有限公司  
DONGGUAN JBL TECH CO., LTD

TITLE	1.5H TF 短体开关中间PIN B版本	DR	
PART NO.	402012262-A	CHKD	
PRO J.	PAGE 2/2 UNITS mm	APPD	
	SIZE A4 SCALE 1:1	DIS NO.	