







	COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE
△						.	△						.
△						.							.
△						.	△						.



NOTE 1 . ALL LEAD CO-PLANARITY SHALL BE 0.08mm MAX.
2 . CONTACT PLATING SPECIFICATIONS
CONTACT AREA : GOLD 0.05 μ m MIN
SMT LEAD : GOLD 0.05 μ m MIN
UNDERPLATING : NICKEL 1 μ m MIN
(SURFACE : SEALING)
3 . CAV NO. ARE INDICATED IN APPROX POSITION SHOWN.




SIGNAL CONTACT



POWER CONTACT


4	PS	CLEAR (EMBOSSED CARRIER TAPE)			
3	COPPER ALLOY	[Z]			
2	COPPER ALLOY	[Z]	6	PS	BLACK (PLASTIC REEL)
1	LCP	UL94 V-0, BLACK	5	POLYESTER	CLEAR (COVER TAPE)
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
REMARKS			DRAWN J. M. YEOM 20. 09. 18	DESIGNED J. M. YEOM 20. 09. 18	CHECKED H. W. JO 20. 09. 18
				APPROVED H. W. JO 20. 09. 18	RELEASED 20. 09. 18
CODE NO. (COLD)		DRAWING NO. EDC3-632913-95	PART NO. BK13C06-40DS/2-0.35V(895)		
	SCALE 10:1	 HIROSE KOREA CO., LTD.	CODE NO. CL 6665-0010-9-895		
	UNITS mm		1/3		

5 RECOMMENDED PCB LAYOUT




RECOMMENDED METAL MASK DIMENSIONS

METAL MASK THICKNESS : $80 \mu\text{m}$



4 RECOMMENDED REFLOW TEMPERATURE PROFILE USING LEAD-FREE SOLDER PASTE.



REFLOW METHOD : N_2 REFLOW
NUMBER OF REFLOW CYCLES : 2 CYCLES MAX.

- 1) REFLOW TIME
DURATION ABOVE 220°C: 60 SEC MAX.
(PEAK TEMPERATURE : 250°C MAX)
- 2) PRE-HEAT TIME
PRE-HEAT TEMPERATURE(MIN): 150°C
PRE-HEAT TEMPERATURE(MAX): 180°C
PRE-HEAT TIME: 90-120 SEC.


4. THIS TEMPERATURE PROFILE IS PER THE CONDITIONS SHOWN ABOVE. ADDITIONAL FACTORS SUCH AS SOLDER PASTE TYPE, PCB SIZE AND OTHER MOUNTED COMPONENTS COULD AFFECT THE PROFILE. THEREFORE, A THOROUGH EVALUATION OF MOUNTING CONDITION IS REQUIRED PRIOR TO PRODUCTION. TEMPERATURE IS MEASURED AT CONTACT LEAD.

5. PLEASE CONTACT US IN CASE YOU WILL MAKE DIFFERENT SETTINGS FROM OUR RECOMMENDATION.
6. THIS PRODUCT SATISFIES HALOGEN FREE REQUIREMENTS DEFINED AS 900ppm MAXIMUM CHLORINE, 900ppm MAXIMUM BROMINE, AND 1500ppm MAXIMUM TOTAL OF CHLORINE AND BROMINE.
 7. THIS PRODUCT COMPLY WITH RoHS.


	DRAWING NO.	EDC3-632913-95	PART NO.	BK13C06-40DS/2-0.35V(895)
	SCALE	10:1	CODE NO	CL 6665-0010-9-895
UNITS	HRS HIROSE KOREA CO., LTD.			2/3

Oct.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
use of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspond


EMBOSSED CARRIER TAPE PACKAGING (5:1)



D-D (5:1)




STYLE AND DIMENSION OF REEL (FREE)



C-C (5:1)

DIRECTION OF UNREELING




TRAILER

LEADER

TAPING(FREE)

E (10:1)



DETAIL OF PART NO. LABEL

SUPPLIER	HIROSE
QUANTITY	1,000
PART NO.	BK13C06-40DS/2-0.35V(895)
CODE NO.	CL 6665-0010-9-895
DATE OF MANUFACTURED	2025.01.01
生産月日	年 月 日
図番	** ** *
品名	BK13C06-40DS/2-0.35V(895)
納入数量	1,000個
納入者	HIROSE KOREA

8 . PER REEL 1,000 CONNECTORS.

9 . THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

10 REFER TO JIS C 0806, IEC-60286-3 (PACKAGING OF COMPONENTS FOR AUTOMATIC HANDLING)

DRAWING NO.	EDC3-632913-95	PART NO.	BK13C06-40DS/2-0.35V(895)
SCALE	10:1	CODE NO.	CL 6665-0010-9-895
UNITS	mm		
	HIROSE KOREA CO., LTD.		