



Specifications:

- 1.Rated Voltage :125V AC/DC
- 2.Rated Current : 2A AC,DC
- 3.Withstand Voltage :200V AC/minute
- 4.Contact Resistance:50mΩ (MAX.)
- 5.Insulation Resistance:100mΩ (MIN.)
- 6.Storage Temperature Range:-40°C~+85°C;
- 7.Operation Temperature Range:-25°C~+70°C;

Rev No.	Description of Revision	Date	Name	Approved	ECN No.



PIN数	MID. A	MID. B	MID. C
2P	1.50	6.00	1.50
3P	3.00	7.50	3.00
4P	4.50	9.00	4.50
5P	6.00	10.50	6.00

(3)	圆针	黄铜H65	镀亮锡	5PCS
(2)	固定片	黄铜H65	镀亮锡	2PCS
(1)	塑胶主体	LCP	本色	1PCS
序号	配件名称	材质	电镀	颜色

UNLESS OTHERWISE SPECIFIED TOLERANCES	® HANXIA 深圳市韩下电子有限公司			
DECIMALS:	ANGLES	TITLE: HX-ZH1.5-4ALB		
X. ±0.15	X'. ±2°	Drawn:	黄彬	PART NO. WF005-LT15002-02
X.X ±0.10	X.X' ±1°	Checked:	张伟	SCALE 1:8
X.XX ±0.05	X.XX' ±0.5°	Approved:	罗小春	UNIT mm SIZE A4 SHEET 1 OF 1 REV. A
X.XXX ±0.03		CUSTOMER COPY		



® 深圳市韩下电子有限公司
Shenzhen Hanxia Electronic Co., Ltd
Tel: 0755-23086569

承 认 书

SPECIFICATION FOR APPROVAL

产品编码
Material code:

产品名称 Project: 针座

规格型号 Part No: HX-ZH1.5-4ALB

贵公司承认印 Approval signatures

料号/Part No.	签章/Signatures

日期 Date:

拟制/Drawn	黄彬	
审核/Check	张伟	
批准/Approved	罗小春	