

PRODUCT CHARACTERISTICS

V_{DS}	-30V
$R_{DS(ON)}$ Typ(@ $V_{GS}=-10V$)	36m Ω
$R_{DS(ON)}$ Typ(@ $V_{GS}=-4.5V$)	49m Ω
I_D	-4.1A

APPLICATIONS

- * High efficiency switch mode power supplies
- * Electronic lamp ballasts based on half bridge
- * LED power supplies

FEATURE

- * High Switching Speed
- * Improved dv/dt capability

ORDER INFORMATION



Order Codes		Package	Packing
Halogen-Free	Halogen		
N/A	MOT3407B2	SOT-23	3000 pieces/Reel

ABSOLUTE MAXIMUM RATINGS($T_A=25^{\circ}C$, unless otherwise specified)

Parameter	Symbol	Ratings	Unit
Drain-Source Voltage	V_{DS}	-30	V
Gate-Source Voltage	V_{GS}	± 20	V
Drain Current Continuous(@ $V_{GS}=-10V$, $T_A=25^{\circ}C$)	I_D	-4.1	A
Drain Current Pulsed	I_{DM}	16.4	A
Power Dissipation	P_D	1.28	W
Junction Temperature	T_J	+150	$^{\circ}C$
Storage Temperature	T_{STG}	-55~ +150	$^{\circ}C$

THERMAL CHARACTERISTICS

Parameter	Symbol	Typ	Unit
Junction to Ambient	R_{thJA}	97	$^{\circ}C/W$



SOT-23



■ ELECTRICAL CHARACTERISTICS ($T_C=25^{\circ}\text{C}$, unless otherwise noted)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Off characteristics						
Drain to Source Breakdown Voltage	V _{DSS}	V _{GS} =0V,I _D =-250μA	-30	-	-	V
Drain to Source Leakage Current	I _{DSS}	V _{DS} =-30V,V _{GS} =0V	-	-	-1	μA
Gate to Source Forward Leakage	I _{GSS(F)}	V _{GS} =+20V,V _{DS} =0V	-	-	100	nA
Gate to Source Reverse Leakage	I _{GSS(R)}	V _{GS} =-20V ,V _{DS} =0V	-	-	-100	nA
On characteristics						
Drain to Source On-Resistance	R _{DS(ON)}	V _{GS} =-10V,I _D =-4 A	-	36	53	mΩ
		V _{GS} =-4.5V,I _D =-3 A	-	49	70	mΩ
Gate Threshold Voltage	V _{GS(TH)}	V _{DS} =V _{GS} ,I _D =-250μA	-1	-1.7	-2.5	V
Dynamic characteristics						
Input Capacitance	C _{iss}	V _{DS} =-15V,V _{GS} =0V f=1.0MHz	-	540	-	pF
Output Capacitance	C _{oss}		-	75	-	pF
Reverse Transfer Capacitance	C _{rss}		-	57	-	pF
Resistive Switching Characteristics						
Turn-on Delay Time	t _{d(ON)}	V _{GS} =-10V,V _{DS} =-15V, I _D =-2 A,R _G =3Ω	-	2	-	ns
Rise Time	t _r		-	3	-	ns
Turn-off Delay Time	t _{d(OFF)}		-	26	-	ns
Fall Time	t _f		-	15	-	ns
Total Gate Charge	Q _g	I _D =-2 A, V _{DS} =-15V V _{GS} =-10V	-	11	-	nC
Gate to Source Charge	Q _{gs}		-	2	-	nC
Gate to Drain("Miller") Charge	Q _{gd}		-	2	-	nC
Source-Drain Diode Characteristics						
Continuous Source Current(Body Diode)	I _S		-	-	-4.1	A
Maximum Pulsed Current(Body Diode)	I _{SM}		-	-	-16.4	A
Diode Forward Voltage	V _{SD}	I _{SD} =-1A, V _{GS} =0V	-	-0.78	-1.2	V
Reverse Recovery Time	t _{rr}	I _{SD} =-2 A, T _J =25°C dI/dt=100A/μs	-	9	-	ns
Reverse Recovery Charge	Q _{rr}		-	3	-	nC

■ TYPICAL CHARACTERISTICS




Figure 1: Output Characteristics




Figure 2: Transfer Characteristics




Figure 3: $R_{DS(ON)}$ vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics




Figure 6: Capacitance Characteristics

■ TYPICAL CHARACTERISTICS(Cont.)




Figure 7: Normalized Breakdown voltage vs Junction Temperature




Figure 8: Normalized On-resistance vs. Junction Temperature




Figure 9: Current De-rating





Figure 10: Safe Operating Area

SOT-23 PACKAGE OUTLINE DIMENSIONS

单位 (UNIT) : mm



序号	数值及公差
A	2.90±0.10
B	1.30±0.10
C	1.00±0.10
D	0.40±0.10
E	2.40±0.20
G	1.90±0.10
H	0.95±0.05
J	0.13±0.05
K	0.00-0.10
M	≥0.20
N	0.60±0.10
P	7±2°
Packing SOT-23 包装规格 SMD片式表面贴封装 包装方式: 载带卷盘包装 Tape & Reel, 3Kpcs/Reel 每卷数量3000只 (3Kpcs/Reel) 每盒数量45000只 (45Kpcs/BOX) 每箱数量180000只 (180Kpcs/Cartons)	