







RECOMMENDED REFLOW TEMPERATURE PROFILE USING LEAD-FREE SOLDER PASTE

NOTES:

- 1.0 VOLTAGE: 60V AC/DC
- 2.0 IMPEDANCE: 50Ω
- 3.0 OPERATION TEMPERATURE: -40° C TO +85° C
- 4.0 CONTACT RESISTANCE: 10mΩ MAX CENTER, 20mΩ MAX OUTSIDE
- 5.0 INSULATION RESISTANCE: 500MΩ MIN INITIAL, 100MΩ MIN AFTER TEST
- 6.0 DIELECTRIC WITHSTANDING VOLTAGE: 200V AC FOR ONE MINUTE
- 7.0 DURABILITY: 30 CYCLES
- 8.0 IR REFLOW CYCLE: 2 CYCLES MAX.
- 9.0 VSWR:
1.3 MAX. at 0.1~3 GHz ; 1.4 MAX. at 3~6 GHz




深圳市华宇创精密电子有限公司

TOLERANCE:

x.x ±0.30
x.xx ±0.25
x.xxx ±0.15

x' ±2" x.x' ±0.5"



UNIT: mm [inch]

SCALE: 1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

RF一代板端天线座

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW26-RF3031-125B

MOLD NO.

APPROVED BY:

邱敏

DATE :




2014-02-23

DRAW NO:


HYC-2511251131

SHEET NO.

1 OF 1



RECOMMENDED FOOTPRINT PATTERN(TOLERANCE:±0.05)



		深圳市华宇创精密电子有限公司			
TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.* ±2* X.X* ±0.5*		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 包装图	
 UNIT: mm [inch]		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	
				MOLD NO.	
SCALE:1:1 SIZE: A4		APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	
				SHEET NO.	1 OF 1