

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
100V	1.35mΩ@10V	275A



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- Fast Switching
- Low Gate Charge and Rdson
- Advanced Split Gate Trench Technology
- 100% Single Pulse avalanche energy Test

Applications


- Power switching application
- DC-DC Converter
- Power Management

Package




TO-247(1:G 2:D 3:S)

Circuit diagram



Marking



SP010N01BGHTF : Product code
** : Week code

Order Information

Device	Package	Unit/Tube
SP010N01BGHTF	TO-247	30

Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter		Symbol	Rating	Units
Drain-Source Voltage		V_{DS}	100	V
Gate-Source Voltage		V_{GS}	± 20	V
Continuous Drain Current (Tc=25°C)	Package Limit	I_D	275	A
Continuous Drain Current (Tc=100°C)		I_D	183	A
Pulsed Drain Current		I_{DM}	1100	A
Single Pulse Avalanche Energy ¹		E_{AS}	2601	mJ
Power Dissipation (Tc=25°C)		P_D	340	W
Power Dissipation (Tc=100°C)		P_D	136	W
Thermal Resistance Junction-to-Case		$R_{\theta JC}$	0.37	°C/W
Storage Temperature Range		T_{STG}	-55 to 150	°C
Operating Junction Temperature Range		T_J	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Characteristics	Symbol	Test Condition	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=250uA	100	-	-	V
Drain Cut-Off Current	I _{DSS}	VDS=80V , VGS=0V , TJ=25℃	-	-	1	μA
Gate Leakage Current	I _{GSS}	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	V _{GS(th)}	VGS=VDS , ID =250uA	2	3	4	V
Drain-Source ON Resistance	R _{DS(ON)}	VGS=10V , ID=20A	-	1.35	1.75	mΩ
Gate Resistance	R _G	VDS=50V , VGS=0V , f=1MHz	-	4.1	-	Ω
Dynamic Characteristics						
Input Capacitance	C _{iss}	VDS=50V , VGS=0V , f=1MHz	-	12142	-	pF
Output Capacitance	C _{Oss}		-	4588	-	
Reverse Transfer Capacitance	C _{rss}		-	129	-	
Total Gate Charge	Q _g	VDS=50V , VGS=10V , ID=125A	-	218	-	nC
Gate-Source Charge	Q _{gs}		-	66	-	
Gate-Drain Charge	Q _{gd}		-	57	-	
Gate Plateau Vlotage	V _{plateau}		-	5	-	V
Switching Characteristics						
Turn-On Delay Time	t _{d(on)}	VDD=50V , VGS=10V , RG=1.6Ω , ID=125A	-	43	-	nS
Rise Time	t _r		-	71	-	
Turn-Off Delay Time	t _{d(off)}		-	149	-	
Fall Time	t _f		-	89	-	
Drain-Source Body Diode Characteristics						
Source-Drain Diode Forward Voltage	V _{SD}	IS=1A , VGS=0V	-	-	1.2	V
Maximum Body-Diode Continuous Current	I _S		-	-	275	A
Reverse Recovery Time	Trr	IS=20A , di/dt=100A/us , TJ=25℃	-	136	-	nS
Reverse Recovery Charge	Qrr		-	380	-	nC


Note :

1. The test condition is $V_{DD}=50V, V_{GS}=10V, L=0.5mH, R_G=25\Omega$


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




RDS(on) VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage





Maximum Transient Thermal Impedance





Safe Operation Area

Test Circuit



Gate Charge





Resistive Load Switching Time




Un-clamped Inductive Load Switching



Drain-Source Body Diode Reverse Recovery



**Temperature Profile for IR Reflow Soldering(Pb-Free)****Note:**


1. Preheating: 25 ~ 150 °C, Time: 60 ~ 90 sec.
2. Peak Temp.: 245 ± 5 °C, Duration: 5 ± 0.5 sec.
3. Cooling Speed: 2 ~ 10 °C/sec.

Resistance to Soldering Heat Test Conditions

Temp.: 260 ± 5 °C Time: 10 ± 1 sec



TO-247 Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	4.850	5.150	0.191	0.200
A1	2.200	2.600	0.087	0.102
b	1.000	1.400	0.039	0.055
b1	2.800	3.200	0.110	0.126
b2	1.800	2.200	0.071	0.087
c	0.500	0.700	0.020	0.028
c1	1.900	2.100	0.075	0.083
D	15.450	15.750	0.608	0.620
E1	3.500 REF.		0.138 REF.	
E2	3.600 REF.		0.142 REF.	
L	40.900	41.300	1.610	1.626
L1	24.800	25.100	0.976	0.988
L2	20.300	20.600	0.799	0.811
Φ	7.100	7.300	0.280	0.287
e	5.450 TYP.		0.215 TYP.	
H	5.980 REF.		0.235 REF.	
h	0.000	0.300	0.000	0.012