

PRODUCT CHARACTERISTICS

V_{DS}	800V
$R_{DS(ON)}$ Typ(@ $V_{GS}=10V$)	1.5 Ω
Q_g @typ	31nC
I_D	7A

APPLICATIONS

- * High efficiency switch mode power supplies
- * Electronic lamp ballasts based on half bridge
- * LED power supplies

FEATURE

- * High Switching Speed
- * Improved dv/dt capability

ORDER INFORMATION

Order Codes		Package	Packing
Halogen-Free	Halogen		
N/A	MOT7N80F	TO-220F	50 pieces/Tube



ABSOLUTE MAXIMUM RATINGS($T_A=25^{\circ}C$, unless otherwise specified)

Parameter	Symbol	Ratings	Unit
Drain-Source Voltage	V_{DS}	800	V
Gate-Source Voltage	V_{GS}	± 30	V
Drain Current Continuous(@ $V_{GS}=10V, T_A=25^{\circ}C$)	I_D	7	A
Drain Current Pulsed	I_{DM}	28	A
Avalanche Energy *	E_{AS}	703	mJ
Peak Diode Recovery dv/dt	dv/dt	5.0	V/ns
Power Dissipation	P_D	33	W
Junction Temperature	T_J	+150	$^{\circ}C$
Storage Temperature	T_{STG}	-55~ +150	$^{\circ}C$

THERMAL CHARACTERISTICS

Parameter	Symbol	Typ	Unit
Junction to Ambient	R_{thJA}	62.5	$^{\circ}C/W$
Junction to Case	R_{thJC}	3.8	$^{\circ}C/W$

Note: * EAS condition: $T_J=25^{\circ}C, V_{DD}=50V, V_G=10V, L=10mH, R_g=25\Omega$



■ ELECTRICAL CHARACTERISTICS ($T_C=25^{\circ}\text{C}$, unless otherwise noted)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Off characteristics						
Drain to Source Breakdown Voltage	V _{DSS}	V _{GS} =0V, I _D =250μA	800	-	-	V
Drain to Source Leakage Current	I _{DSS}	V _{DS} =800V, V _{GS} =0V	-	-	1	μA
Gate to Source Forward Leakage	I _{GSS(F)}	V _{DS} =0V, V _{GS} =+30V	-	-	100	nA
Gate to Source Reverse Leakage	I _{GSS(R)}	V _{DS} =0V, V _{GS} =-30V	-	-	-100	nA
On characteristics						
Drain to Source On-Resistance	R _{DS(ON)}	V _{GS} =10V, I _D =3.5 A	-	1.5	1.7	Ω
Gate Threshold Voltage	V _{GS(TH)}	V _{DS} =V _{GS} , I _D =250μA	2	-	4	V
Dynamic characteristics						
Gate capacitance	R _g	V _{GS} =0V, V _{DS} =0V ,f=1.0MHz	-	2.1	-	Ω
Forward Transconductance	g _{fs}	V _{DS} =10V, I _D =3A	-	7	-	S
Input Capacitance	C _{iss}	V _{DS} =25V, V _{GS} =0V f=1.0MHz	-	1200	-	pF
Output Capacitance	C _{oss}		-	114	-	pF
Reverse Transfer Capacitance	C _{rss}		-	10.7	-	pF
Resistive Switching Characteristics						
Turn-on Delay Time	t _{d(ON)}	I _D =7A, V _{DS} =400V R _G =10Ω V _{GS} =10V	-	20.5	-	ns
Rise Time	t _r		-	17	-	ns
Turn-off Delay Time	t _{d(OFF)}		-	49.4	-	ns
Fall Time	t _f		-	11.2	-	ns
Total Gate Charge	Q _g	I _D =7A, V _{DS} =400V V _{GS} =10V	-	31	-	nC
Gate to Source Charge	Q _{gs}		-	6.7	-	nC
Gate to Drain("Miller") Charge	Q _{gd}		-	16.2	-	nC
Source-Drain Diode Characteristics						
Continuous Source Current(Body Diode)	I _S		-	-	7	A
Maximum Pulsed Current(Body Diode)	I _{SM}		-	-	28	A
Diode Forward Voltage	V _{SD}	I _{SD} =1A, V _{GS} =0V	-	0.74	1.2	V
Reverse Recovery Time	t _{rr}	I _{SD} =7A, T _J =25 °C	-	626	-	ns
Reverse Recovery Charge	Q _{rr}	dI/dt=100A/μs	-	4990	-	nC

■ TYPICAL CHARACTERISTICS




Figure 1: Transfer Characteristics




Figure 2: Body Diode Characteristics




Figure 3: Drain to Source On-Resistance vs Drain Current




Figure 4: Drain to Source On-Resistance vs. Junction Temperature




Figure 5: Threshold Voltage vs Junction Temperature




Figure 6: Breakdown Voltage vs Junction Temperature

■ TYPICAL CHARACTERISTICS(Cont.)




Figure 7: Capacitance vs Drain to Source Voltage




Figure 8: Gate Charge vs Gate to Source Voltage




Figure 9: Continuous Drain vs Case Temperature




Figure 10: Output characteristics




Figure 11: Power Dissipation vs Case Temperature




Figure 12: Safe Operating Area

■ TO-220F PACKAGE OUTLINE DIMENSIONS

