


Ordering Information:
A2008WV-S-XP-LCP - ***
1 2

1.Part NO.

2.Finish:

(Blank): Tin over Nickel

G:Gold over Nickel(Au:1u" All area)


G3: Gold over Nickel (Au:3u" All area)

G5: Gold over Nickel (Au:5u" All area)

G10: Gold over Nickel (Au:10u" All area)

G15: Gold over Nickel (Au:15u" All area)

G30: Gold over Nickel (Au:30u" All area)



SPECIFICATIONS:

Current Rating: 3A AC,DC

Voltage Rating: 250V AC,DC

Temperature Range: -40°C ~ +105°C

Contact Resistance: 20mΩ Max.

Insulation Resistance: 1000MΩ Min.

Withstanding Voltage: 1000V AC/minute


PIN Material: Brass

Solder Tabs:Phosphor Bronze/Tin over Nickel

Material: LCP UL94V-0(Beige)



Ordering Information & Dimensions

Part NO.	Dimensions(mm)	
	A	B
A2008WV-S-2P	2.00	8.00
A2008WV-S-3P	4.00	10.00
A2008WV-S-4P	6.00	12.00
A2008WV-S-5P	8.00	14.00
A2008WV-S-6P	10.00	16.00
A2008WV-S-7P	12.00	18.00
A2008WV-S-8P	14.00	20.00
A2008WV-S-9P	16.00	22.00
A2008WV-S-10P	18.00	24.00
A2008WV-S-11P	20.00	26.00
A2008WV-S-12P	22.00	28.00
A2008WV-S-13P	24.00	30.00
A2008WV-S-14P	26.00	32.00
A2008WV-S-15P	28.00	34.00
A2008WV-S-16P	30.00	36.00



Cap
(For pick and
place systems)

2.90±0.20
Mating Area



A8	JL-GC-ECN00931	2025.11.11	CHANGJIANG CONNECTORS CO.,LTD.			
A7	JL-GC-ECN00767	2025.07.24	Unit	Scale	Sheet	TITLE 2.00mm PITCH VERTICAL WAFER - SMD TYPE
A6	JL-GC-ECN00467	2024.12.17	mm	4:1	1 of 1	
A5	CHANGE THE DRAWING	2023.01.05	DRAWN	CHK'D	APPR	
A4	CHANGE THE DRAWING	2021.12.23	Chengbiao Ye	Diankui Wan	Jack Yin	DRAWING NO. A2008WV-S-XP-LCP
A3	ADD THE DRAWING OF CAP	2020.07.30	General Tolerances		THIRD ANGLE PROJECTION	
A2	CHANGE THE DRAWING	2019.05.08	x,xx±0.25 x,xxx±0.20 x,xxxx±0.15			
A1	MODIFY THE MATERIAL	2016.03.26	ANGLES ±1°			
REV	DESCRIPTION	DATE				REV A8