

NOTES:

MATERIAL:

- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER(UL94V-0).
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE $\phi 0.46\text{mm}$ (C5100).
- 3.PLATING :GOLD PLATING OVER NICKEL.
- 4.SHIELD: COPPER ALLOY 0.20mm THICKNESS PLATING NI.

ELECTRICAL:

- 1.VOLTAGE RATING :125 VAC RMS.
- 2.CURRENT RATING :1.5 AMP.
- 3.CONTACT RESISTANCE :50 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC.
- 5.DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 50Hz. 1MIN.

MECHANICAL:

- 1.DURRABILITY :750 CYCLES MIN.
- 2.PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

- 1.STORAGE : -40°C TO $+85^{\circ}\text{C}$.
2. OPERATION : 0°C TO 70°C .

MATES WITH MODULAR PLUG CONFORMING TO FCC PART 68,SUBPART F.

PART NUMBER:

▲98-0316610X×0X

98 SERIES
PCB JACK
(98系列PCB接口)

SHIELD (屏蔽壳):

- 1-W/O SHIELD (无屏蔽)
- 2-HALF SHIELD (半包)
- 3-FULL SHIELD (全包)

PORTS (端口):

- 1-1X1 (一端口) .2-1X2 (二端口)
- 4-1X4 (四端口) .5-1X5 (五端口)
- 6-1X6 (六端口) .8-1X8 (八端口)

POSITIONS (金针位置):

- 4-4POSITIONS (4P)
- 6-6POSITIONS (6P)
- 8-8POSITIONS (8P)
- 0-10POSITIONS (10P)

CONTACTS (金针数量):

- 2-2CONTACTS (2C) .4-4CONTACTS (4C)
- 6-6CONTACTS (6C) .8-8CONTACTS (8C)
- 0-10CONTACTS (10C)

PEG/TAB (定位位/脚):

- 0-W/O PEG (无脚) .1-FRONT PEG 3.05 (前脚3.05)
- 2-FRONT PEG3.68 (前脚3.68) .3-FRONT PEG4.57 (前脚4.57)
- 4-BACK PEG3.05 (后脚3.05)

GOLD PLATING

- (镀金厚度)
- 1-F U". 2-1.5U"
 - 3-3U".4-6U"
 - 5-15U".6-30U"
 - 7-50U"

LOGO (标识): 0-W/O LOGO (无标识).

- 1-W/ HAXN (有HAXN标识)
- 2-W/ UL (有UL标识).
- 3-W/ HAXN. UL (有HAXN. UL)
- 4-W/ GST(有GST)



- COLOR (颜色):
- 1-BLACK (黑色)
 - 2-WHITE (白色) .3-GRAY (灰色)
 - 4-IVORY (象牙色) .5-YELLOE (黄色)
 - 6-RED (红色) .7-GREEN (绿色)

PLASTIC (塑料):



- 1-PBT.2-NYLON66 (尼龙66) .
- 3-NYLON46 (尼龙46) .4-ABS

BACK PEG (后定位脚):

- 0-W/O BACK PEG (无后定位脚)
- 1-1BACK PEG (1个后定位脚)
- 2-2BACK PEG (2个后定位脚)
- 3-3BACK PEG (3个后定位脚)



PEG/TAB



PC Board Layout

REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD
△		原始版本	PEILEI	05.10.05
△		增加料号.更改图号	zushiyong	7.01.25
△		增加LOGO	zushiyong	07.05.22

DETACHED LISTS		设计 新	日期 05.10.07
一 般 公 差 栏		审核 GANBO	日期 05.10.07
MM	(INCH)	批准 xushiyong	日期 05.10.07
±0.20	±	材料: 材料	
±0.15	±	数量: 数量	
±0.075	±	表面处理: 表面处理	
角度 ±0.01°		比例: 比例	
第三角视图			

浙江创都电子科技有限公司

RJ58 - 6P6C-QBWL

图号: △ 图号

料号: 料号

不 按 比 例

第 页