



N-Channel MOSFET


SOT-23



MARKING : 337*



SOT-23



1. GATE
2. SOURCE
3. DRAIN

FEATURE

- High dense cell design for extremely low $R_{DS(on)}$
- Exceptional on-resistance and maximum DC current capability

APPLICATION

- Load/Power Switching
- Interfacing Switching

$V_{(BR)DSS}$	$R_{DS(on)}$ Typ	I_D
30 V	32 mΩ@ 10V	5.7A
	37 mΩ@ 4.5V	
	52 mΩ@ 2.5V	

Maximum ratings ($T_a=25^{\circ}\text{C}$ unless otherwise noted)


Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	30	V
Gate-Source Voltage	V_{GS}	±12	V
Continuous Drain Current	I_D	5.7	A
Drain Current-Pulsed ^①	I_{DM}	22	A
Power Dissipation	P_D	1.4	W
Thermal Resistance from Junction to Ambient	$R_{\theta JA}$	130	°C/W
Operation Junction and Storage Temperature Range	T_J, T_{STG}	-55~+150	°C

$T_a=25^{\circ}\text{C}$ unless otherwise specified


Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Off Characteristics						
Drain-source breakdown voltage	V _{(BR) DSS}	V _{GS} = 0V, I _D =250μA	30			V
Zero gate voltage drain current	I _{DSS}	V _{DS} =24V,V _{GS} = 0V,T _J =25 ℃			1	μA
		V _{DS} =24V,V _{GS} = 0V,T _J =125 ℃			1	mA
Gate-source leakage current	I _{GSS}	V _{GS} =±12V, V _{DS} = 0V			±100	nA
On characteristics						
Drain-source on-resistance ②	R _{DS(on)}	V _{GS} =10V, I _D =4A		32	40	mΩ
		V _{GS} =4.5V, I _D =3A		37	46	mΩ
		V _{GS} =2.5V, I _D =2A		52	70	mΩ
Forward transconductance	g _{FS}	V _{DS} =5V, I _D =5A	8			S
Gate threshold voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250μA	0.7	0.9	1.4	V
Dynamic Characteristics ③						
Input capacitance	C _{iss}	V _{DS} =15V,V _{GS} =0V,f =1MHz		820	1050	pF
Output capacitance	C _{oss}			99		pF
Reverse transfer capacitance	C _{rss}			77		pF
Gate resistance	R _g	V _{DS} =0V,V _{GS} =0V,f =1MHz		3.6		Ω
Switching Characteristics ③						
Turn-on delay time	t _{d(on)}	V _{GS} =10V,V _{DS} =15V, R _L =2.7Ω,R _{GEN} =3Ω		3.3	5	ns
Turn-on rise time	t _r			4.8	7	ns
Turn-off delay time	t _{d(off)}			26	40	ns
Turn-off fall time	t _f			4	6	ns
Total Gate Charge	Q _g	V _{DS} =10V,I _D =5A, V _{GS} =6V		9.5		nC
Gate-Source Charge	Q _{gs}			1.5		nC
Gate-Drain Charge	Q _{gd}			3		nC
Drain-source diode characteristics and maximum ratings						
Diode forward voltage ②	V _{SD}	I _S =1A,V _{GS} =0V			1	V
Continuous drain-source diode forward current	I _S				5.7	A
Pulsed drain-source diode forward current①	I _{SM}				22	A

Typical Characteristics


Output Characteristics




Transfer Characteristics




$R_{DS(ON)}$ — I_D




$R_{DS(ON)}$ — V_{GS}



I_S — V_{SD}




Threshold Voltage



Plastic surface mounted package

SOT-23



SOLDERING FOOTPRINT

