

HSF



ROHS

CONTACT SURFACE

0.025 (.001)

0.13 (.005)

CONTACT MUST PROTRUDE
BEYOND BASE TO MAX. OF. 0.13 (.005)

± 0.10 A

SOLDER TAIL

3.38 (.133)

(2) PLS

24.7
SECTION A-A

28.37 (1.117)

$\phi 22.35 (\phi .880)$

$\phi 20.27 (\phi .798)$
REF

3.51 (.138) ± 0.15
(2) PLS

5.97 (.235)

7.85 (.309)

Pad Layout

3.5 (0.138) SQR
MIN (2) PLS

11.1 (0.673) MAX

24.7 MIN

NOTES:

1. BASE:

MAT'L-PA9T, UL 94V-0, BLACK COLOR

2. POS/T/VE CONTACTS:

MAT'L-, 009[0.23] TH'K PHOSPHOR BRONZE
FINISH:GOLD FLASH, OVER NICKEL PLATING

3. NEGAT/VE CONTACTS:

MAT'L-, 009[0.23] TH'K STAINLESS STEEL
FINISH:GOLD FLASH, OVER NICKEL PLATING

Order code:

BT — M — GO — R — CR2032P
① ② ③ ④ ⑤

① BT: Coin Cell Holders

② Apperance for the product
M:SMT TYPE

③ Contact Plating
SN:tin

GO:Gold flash
G1: 3U" Gold
G2: 5U" Gold
G3:10U" Gold
G4:15U" Gold
G5:30U" Gold

④ Packing method
A: Tray packing
R: Tape & reel packing

⑤ Product number
CR2032P

Unless Otherwise specified tolerance
X. ± 0.35 X.XX: ± 0.20
X.X: ± 0.25 X.XXX: ± 0.15

SCALE:
As Shown
DRAW
Lv Xun Hua
CHECK
BobYang

UNIT:
mm
DATE
23/03/2019
DATE
23/03/2019

Antenk®

TITLE:

Coin Cell Holders For CR2032

DRAWING NO: BT-M-SN-R-CR2032P

PRODUCT NO: BT-M-SN-R-CR2032P

Change 24.36 to 24.7

07/06/2022

ADD Pad Layout

05/07/2021

REV

DESCRIPTION

DATE



3rd ANGLE PROJECTION