

## UMSB Plastic-Encapsulate Bridge Rectifier

### Features

- Ideal for printed circuit board
- Low forward voltage drop
- High surge current capability
- Glass passivated chip junction

### Applications




General purpose 1 phase Bridgerectifier applications

### Mechanical Data

- Case: UMSB  
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

### Function Diagram

Reverse Voltage  
50-1000 V  
Forward Current  
4.0 Ampere







### Maximum Ratings (Ta=25°C Unless otherwise specified)

| PARAMETER                                                                               | SYMBOL             | UNIT             | MSB<br>40A-S | MSB<br>40B-S | MSB<br>40D-S | MSB<br>40G-S | MSB<br>40J-S | MSB<br>40K-S | MSB<br>40M-S |
|-----------------------------------------------------------------------------------------|--------------------|------------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|
| Device marking code                                                                     |                    |                  | MSB40AS      | MSB40BS      | MSB40DS      | MSB40GS      | MSB40JS      | MSB40KS      | MSB40MS      |
| Maximum Repetitive Peak Reverse Voltage                                                 | V <sub>RRM</sub>   | V                | 50           | 100          | 200          | 400          | 600          | 800          | 1000         |
| Maximum RMS Voltage                                                                     | V <sub>RMS</sub>   | V                | 35           | 70           | 140          | 280          | 420          | 560          | 700          |
| Maximum DC blocking Voltage                                                             | V <sub>DC</sub>    | V                | 50           | 100          | 200          | 400          | 600          | 800          | 1000         |
| Maximum Average Forward Rectified Current<br>@60Hz sinewave, Resistance load,TL (Fig.1) | I <sub>F(AV)</sub> | A                | 4.0          |              |              |              |              |              |              |
| Non-repetitive Peak Forward Surge Current<br>@ t=8.3ms Half-sine wave                   | I <sub>FSM</sub>   | A                | 100          |              |              |              |              |              |              |
| Rating for fusing (t=8.3ms, Ta=25 °C )                                                  | I <sup>2</sup> t   | A <sup>2</sup> S | 41.5         |              |              |              |              |              |              |
| Storage temperature                                                                     | T <sub>stg</sub>   | °C               | -55 ~ +150   |              |              |              |              |              |              |
| Junction temperature                                                                    | T <sub>J</sub>     | °C               | -55 ~ +150   |              |              |              |              |              |              |
| Typical Thermal Resistance                                                              | R <sub>θJ-A</sub>  | °C /W            | 55           |              |              |              |              |              |              |
|                                                                                         | R <sub>θJ-L</sub>  | °C /W            | 15           |              |              |              |              |              |              |

● **Electrical Characteristics** (Ta=25°C Unless otherwise noted)

| PARAMETER                                               | TEST CONDITIONS                | SYMBOL   | UNIT    | MSB 40A-S | MSB 40B-S | MSB 40D-S | MSB 40G-S | MSB 40J-S | MSB 40K-S | MSB 40M-S |
|---------------------------------------------------------|--------------------------------|----------|---------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|
| Maximum instantaneous forward voltage                   | $I_F=4.0A$                     | $V_F$    | V       | 1.1       |           |           |           |           |           |           |
| Maximum DC reverse current at rated DC blocking voltage | $V_R=V_{DC}, T_A=25^{\circ}C$  | $I_{R1}$ | $\mu A$ | 5.0       |           |           |           |           |           |           |
|                                                         | $V_R=V_{DC}, T_A=100^{\circ}C$ | $I_{R2}$ |         | 500       |           |           |           |           |           |           |

● **Ratings And Characteristics Curves** (Ta=25°C Unless otherwise specified)



● Ordering Information

| PACKAGE | PACKAGE CODE | REEL(pcs) | BOX(pcs) | CARTON(pcs) | DELIVERY MODE |
|---------|--------------|-----------|----------|-------------|---------------|
| UMSB    | R3           | 3000      | 6000     | 42000       | 13"           |

● Package Outline Dimensions (UMSB)

| Symbol | Dimensions  |      |        |       |
|--------|-------------|------|--------|-------|
|        | Millimeters |      | Inches |       |
|        | Min.        | Max. | Min.   | Max.  |
| A      | 1.3         | 1.5  | 0.051  | 0.059 |
| C      | 0.27        | 0.40 | 0.011  | 0.016 |
| D      | 6.5         | 7.0  | 0.256  | 0.276 |
| E      | 7.2         | 7.4  | 0.283  | 0.291 |
| E1     | 7.9         | 8.6  | 0.311  | 0.339 |
| L      | 0.65        | 1.05 | 0.026  | 0.041 |
| e      | 5.0         | 5.2  | 0.197  | 0.205 |
| b      | 0.95        | 1.15 | 0.037  | 0.045 |
| θ      | 10°         |      |        |       |

Top view: Dimensions E, D, L, e, b, and θ. Detail view: Dimensions A, C, and E1. Note: ALL ROUND.

● Suggested Pad Layout

| Symbol | Dimensions  |      |        |       |
|--------|-------------|------|--------|-------|
|        | Millimeters |      | Inches |       |
|        | Min.        | Max. | Min.   | Max.  |
| N      | 5.1         | 5.3  | 0.201  | 0.209 |
| M      | 7.1         | 7.3  | 0.280  | 0.287 |
| X      | 1.8         | 2.0  | 0.071  | 0.079 |
| Y      | 1.3         | 1.5  | 0.051  | 0.059 |

Diagram showing the suggested pad layout with dimensions M, N, X, and Y.