





Kinghelm®



## SPECIFICATIONS

Current Rating: 1.5 Amps  
Insulation Resistance: 1000M $\Omega$ , Min  
Contact Resistance: 20m $\Omega$ , Max  
Withstanding Voltage: AC 500V  
Operation Temperature: -40° to +105°  
Contact Material: Brass  
Standard: PA6T  
Insulator Material: Polyester (UL 94V-0)  
Contact Plating: Gold Flash  
Max. Processing Temp: 240° C for 30-60 seconds  
(260° C for 5 seconds)

## RECOMMEND P.C.B LAYOUT

PCB TOLERANCE:  $\pm 0.05$  (TOP VIEW)

深圳市金航标电子有限公司

www.kinghelm.com

KH-2.0DC3-2X8P-H5.7

0755-28190160

UNLESS OTHERWISE SPECIFIED TOLERANCE

X :  $\pm 0.30$  X° :  $\pm 5^\circ$   
X.X :  $\pm 0.25$  X.X° :  $\pm 1^\circ$   
X.XX :  $\pm 0.20$  X.XX° :  $\pm 0.5^\circ$

DRAWN NAME: 2.0DC3-nPin H5.7 180度 PC2.8 L8.0 6T

|      |    |       |     |            |
|------|----|-------|-----|------------|
| SIZE | A4 | SCALE | N:1 | PROUCT NO. |
| REV  | A  | UNIT  | mm  | PROJECT    |

CHECKED: 陈超凡 2022/05/10 CHECKED: / / APPROVED: / /

| No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 6      | 4.00   | 6.00   | 24     | 22.00  | 24.00  | 42     | 40.00  | 42.00  | 60     | 58.00  | 60.00  |
| 8      | 6.00   | 8.00   | 26     | 24.00  | 26.00  | 44     | 42.00  | 44.00  | 62     | 60.00  | 62.00  |
| 10     | 8.00   | 10.00  | 28     | 26.00  | 28.00  | 46     | 44.00  | 46.00  | 64     | 62.00  | 64.00  |
| 12     | 10.00  | 12.00  | 30     | 28.00  | 30.00  | 48     | 46.00  | 48.00  | 66     | 64.00  | 66.00  |
| 14     | 12.00  | 14.00  | 32     | 30.00  | 32.00  | 50     | 48.00  | 50.00  | 68     | 66.00  | 68.00  |
| 16     | 14.00  | 16.00  | 34     | 32.00  | 34.00  | 52     | 50.00  | 52.00  | 70     | 68.00  | 70.00  |
| 18     | 16.00  | 18.00  | 36     | 34.00  | 36.00  | 54     | 52.00  | 54.00  |        |        |        |
| 20     | 18.00  | 20.00  | 38     | 36.00  | 38.00  | 56     | 54.00  | 56.00  |        |        |        |
| 22     | 20.00  | 22.00  | 40     | 38.00  | 40.00  | 58     | 56.00  | 58.00  |        |        |        |