







RoHS Compliant



RECOMMENDED PCB LAYOUT
TOL: (±0.05)

P8	DAT1
P7	DAT0
P6	VSS
P5	CLK
G1	SWITCH
P4	VDD
P3	CMD
P2	CD/DAT3
P1	DAT2
PIN NUMBER	PIN NUMBER

NOTES:

1) MATERIAL:

HOUSING: HIGHT-TEMP. PLASIC UL 94V-0

CONTACT: COPPER ALLOY,T=0.15

SHELL: STAINLESS STEEL ,T=0.15

2) FINISH :

CONTACT: Au 1u" PLATED ON CONTACT AREA;
Au 1u" PLATING ON SOLDER TAILS,

SHELL: NICKEL PLATED OVERALL,

Au 1u" PLATING ON SOLDER TAILS,

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名 (ITEM NO)	TF 短体卡座 1.5H (中间带侦测 pin)		
		料号 (PART NO)	MLD-TF-H15		
单位 (UNIT): MM	未注公差 TOLERANCE UNSPECIFIED X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	版次 (REV): A/0	页次 (PAGE): 1/1	设计 (DESIGN)	柯南
比例 (SCALE) 1:1		模号 (MODEL NO)	图号 (DWG NO)	审核 (CHECKED)	邱敏
				核准 (APPROVED)	陈镇
			MLD-2509031032		