








AFTER MATING



G-Switch USB-C Specification:


- 1.Current rated: 5A on vbus/1.25A on vconn/0.25A on other
Voltage rating: 24V AC
- 2.Withstanding voltage: 100V AC/minute
- 3.Contact resistance: 40mΩ Max
- 4.Insulation resistance: 100MΩ Min
- 5.Operating temperature: -40°C ~ +85°C
- 6.Mating force: 5N~20N
- 7.Unmating force: 8N~20N
- 8.Durability cycle:10,000 cycles



RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SBU1	VBUS			GND
First			First	Second	Second	Second	Second	First			First
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND			VBUS	SBU2	D-	D+	CC2	VBUS			GND
First			First	Second	Second	Second	Second	First			First

1	SHELL	STAINLESS STEEL	Ni PLATED
2	MID PLATE	STAINLESS STEEL	Ni PLATED
3	HOUSING	HIGH TEMPERATURE PLASTIC	WHITE UL 94V-0
4	TERMINALS	COPPER ALLOY	Au3u PLATING ON CONTACT AREA G/F PLATING ON SOLDER AREA
NO.	PARTS	MATERIAL	REMARKS



RoHS
Compliant
EU RoHS Standards



SCALE:	UNIT: mm
SIZE: A4	

Unless otherwise	
General Tolerance:	
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.10
Y°	±5°

Title:	Horizontal Type-c 16P Female SMT CH=1.67 L=8.33mm White plastic
--------	--

Molde Code: GT-USB-7004

DRAWN	CHECKED	APPROVED	DATE
Wu	Xia	Chen	2024.11.14

 品赞科技[®]
www.dg-switch.com

REV: A1	SHEET: 1/1
---------	------------