

NOTES:

MATERIAL:

- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER(UL94V-0).
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE $\phi 0.46\text{mm}$ (C5100).
- 3.PLATING :GOLD PLATING OVER NICKEL.
- 4.SHIELD: COPPER ALLOY(OR STEEL ALLOY) 0.20mm THICKNESS PLATING NI.
- 5.LED: OPTION.

ELECTRICAL:

- 1.VOLTAGE RATING :125 VAC RMS.
- 2.CURRENT RATING :1.5 AMP.
- 3.CONTACT RESISTANCE :50 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC.
- 5.DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 50Hz. 1MIN.
- 6.LED RATINGS:FORWARD VOLTAGE:2.2 VOLTS TYPICAL.
REVERSE VOLTAGE:5 VOLTS MAXIMUM.

MECHANICAL:

- 1.DURRABILITY:750 CYCLES MIN.
- 2.PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

- 1.STORAGE : -40°C TO $+85^{\circ}\text{C}$.
2. OPERATION: 0°C TO 70°C .

MATES WITH MODULAR PLUG CONFORMING TO

FCC PART 68,SUBPART F.

PART NUMBER:

56LED-03488421X1X11X

56LED SERIES PCB JACK

(56LED系列PCB接口)

SHIELD (屏蔽壳) :1-W/O SHIELD(非屏)

2-HALF SHIELD (半包) 3-FULL SHIELD (全包)

PORTS (插口) :1-1X1 (一口) .2-1X2 (二口)

4-1X4 (四口) .6-1X6 (六口) .8-1X8 (八口)

POSITIONS (金针位置) :8-8POSITIONS (8P)

CONTACTS (金针根数) :8-8CONTACTS (8C)

PEG/TAB (边定位铁脚) :0-W/O PEG (无铁脚) .

4-BACK PEG3.56 (后脚3.56) 5-BACK PEG3.43 (后脚3.43)

BACK PEG (后背铁脚) :0-W/O BACK PEG (无后背铁脚) .

1-1BACK PEG (1个后背铁脚) 2-2BACK PEG (2个后背铁脚) .

3-3BACK PEG (3个后背铁脚)

SHIELD MATERIAL STYLE (屏蔽壳材料分类) :

1-COPPER ALLOY (黄铜) ;2-STEEL ALLOY (钢片) ;3-W/O (不作定义)

LED STYLE: (LED 颜色类型) :0-W/O LED (不带灯)

1-L LED; GREEN, R LED; YELLOW (左绿右黄) ;2-L LED; YELLOW, R LED; GREEN (左黄右绿)

3-L LED; GREEN, R LED; GREEN (双绿) ;4-L LED; RED, R LED; GREEN (左红右绿)

5-L LED; YELLOW, R LED; YELLOW (双黄) ;6-L LED; GREEN, R LED; RED (左绿右红)

GOLD PLATING

(镀金厚度)

1-F U". 2-1.5U"

3-3U". 4-6U"

5-15U". 6-30U"

7-50U"

LOGO (标识) :

0-W/O LOGO (无标识) .

COLOR (颜色) :1-BLACK (黑色)

PLASTIC (塑料) :

1-PBT. 2-NYLON66 (尼龙66)

3-NYLON46 (尼龙46)

EMI (弹片) :1-W/O EMI (无弹片)


2-W/ EMI (带弹片)

10  9



12  11

L-LED黄


R-LED绿



PC Board Layout



REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD

DETACHED LISTS	MM (INCH)		设计 ZHANG WEI	日期 13.03.10
	一 般 公 差 栏		审核	日期
	MM	±	批准 ZHANG KE	日期 13.03.10
	.0 ± 0.30	±	材料: 材料	
	.00 ± 0.25	±	数量: 数量	
	.000 ± 0.15	±	表面处理: 表面处理	
	角度 ± 0.01°		比例: 比例	
				
	第三角视图			

浙江创都电子科技有限公司				
系列	RJ56DL			
系列				
图号:				版本
料号:				版本
不 按 比 例			共 X 页	第 Y 页