

N-Ch 150V Fast Switching MOSFETs

Features

- Split Gate Trench MOSFET technology
- Excellent package for heat dissipation
- High density cell design for low $R_{DS(ON)}$

Applications



- DC-DC Converters
- Power management functions
- Synchronous-rectification applications

Product Summary



BVDSS	RDSON	ID
150V	4.2mΩ	180A

TO247 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	150	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_C=25^\circ\text{C}$	Continuous Drain Current, $V_{GS} @ 10V^{1,6}$	200	A
$I_D@T_C=100^\circ\text{C}$	Continuous Drain Current, $V_{GS} @ 10V^{1,6}$	119	A
I_{DM}	Pulsed Drain Current ²	640	A
EAS	Single Pulse Avalanche Energy ³	1225	mJ
I_{AS}	Avalanche Current	70	A
$P_D@T_C=25^\circ\text{C}$	Total Power Dissipation ⁴	310	W
T_{STG}	Storage Temperature Range	-55 to 150	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	-55 to 150	$^\circ\text{C}$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-Ambient ¹	---	62	$^\circ\text{C/W}$
$R_{\theta JC}$	Thermal Resistance Junction-Case ¹	---	0.40	$^\circ\text{C/W}$

Electrical Characteristics ($T_J=25^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	150	---	---	V
$\Delta BV_{DSS}/\Delta T_J$	BV_{DSS} Temperature Coefficient	Reference to 25°C , $I_D=1\text{mA}$	---	---	---	$V/^\circ\text{C}$
$R_{DS(ON)}$	Static Drain-Source On-Resistance ²	$V_{GS}=10V$, $I_D=90A$	---	4.2	5.2	$m\Omega$
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	2	3	4	V
$\Delta V_{GS(th)}$	$V_{GS(th)}$ Temperature Coefficient		---	---	---	$mV/^\circ\text{C}$
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=150V$, $V_{GS}=0V$, $T_J=25^\circ\text{C}$	---	---	1	μA
		$V_{DS}=150V$, $V_{GS}=0V$, $T_J=100^\circ\text{C}$	---	---	100	
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
gfs	Forward Transconductance	$V_{DS}=5V$, $I_D=60A$	---	106.0	---	S
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	3.7	---	Ω
Q_g	Total Gate Charge	$V_{DS}=75V$, $V_{GS}=10V$, $I_D=60A$	---	77.9	---	nC
Q_{gs}	Gate-Source Charge		---	34.2	---	
Q_{gd}	Gate-Drain Charge		---	15.3	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{GS}=10V$, $V_{DD}=75V$, $R_G=2.7\Omega$, $I_D=60A$	---	22.5	---	ns
T_r	Rise Time		---	107.8	---	
$T_{d(off)}$	Turn-Off Delay Time		---	54.9	---	
T_f	Fall Time		---	105.7	---	
C_{iss}	Input Capacitance	$V_{DS}=75V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	5643	---	pF
C_{oss}	Output Capacitance		---	802	---	
C_{rss}	Reverse Transfer Capacitance		---	29	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current ^{1,4}	$V_G=V_D=0V$, Force Current	---	---	180	A
V_{SD}	Diode Forward Voltage ²	$V_{GS}=0V$, $I_S=60A$, $T_J=25^\circ\text{C}$	---	---	1.4	V
t_{rr}	Reverse Recovery Time	$I_F=60A$, $di/dt=100A/\mu s$, $T_J=25^\circ\text{C}$	---	102.6	---	nS
Q_{rr}	Reverse Recovery Charge		---	293.4	---	nC

Notes:

1. Repetitive rating, pulse width limited by junction temperature $T_{J(MAX)}=150^\circ\text{C}$
2. The EAS data shows Max. rating . The test condition is $V_{DD}=75V$, $V_{GS}=10V$, $L=0.5\text{mH}$
3. The data tested by surface mounted on a 1 inch² FR-4 board with 20Z copper, The value in any given application depends on the user's specific board design.
4. The data tested by pulsed , pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$.
5. This value is guaranteed by design hence it is not included in the production test.

Typical Performance Characteristics

Fig 1: Output Characteristics




Fig 2: Transfer Characteristics




Fig 3: $R_{DS(on)}$ vs Drain Current and Gate Voltage




Fig 4: $R_{DS(on)}$ vs Gate Voltage




Fig 5: $R_{DS(on)}$ vs. Temperature




Fig 6: $V_{GS(th)}$ vs. Temperature




Fig 7: BVDss vs. Temperature




Fig 8: Capacitance Characteristics




Fig 9: Gate Charge Characteristics




Fig 10: Body-diode Forward Characteristics




Fig 11: Power Dissipation




Fig 12: Drain Current Derating




Fig 13: Safe Operating Area







Fig 14: Max. Transient Thermal Impedance





Test Circuit & Waveform



Gate Charge Test Circuit & Waveform





Resistive Switching Test Circuit & Waveforms



Unclamped Inductive Switching (UIS) Test Circuit & Waveforms




Diode Recovery Test Circuit & Waveforms



Mechanical Dimensions for TO-247

COMMON DIMENSIONS



SYMBOL	MM	
	MIN	MAX
A	4.80	5.20
A1	2.21	2.61
A2	1.85	2.15
b	1.11	1.36
b2	1.91	2.21
b4	2.91	3.21
c	0.51	0.75
D	20.70	21.30
D1	16.25	16.85
E	15.50	16.10
E1	13.00	13.60
E2	4.80	5.20
E3	2.30	2.70
e	5.44BSC	
L	19.62	20.22
L1	—	4.30
ØP	3.40	3.80
ØP1	—	7.30
S	6.15BSC	