

Specification for approval

客户名称:

(Customer Name)

产品名称:

DC-LINK直流薄膜电容器

(Product Name)

DC-LINK DC Thin Film Capacitor

客户料号:

(Customer part number)

科尼盛料号:

228CB0081

(KNSCHA number)

型号规格:

DC-LINK 40 μ F/600V P=37.5mm 42*45*30mm
P1=20.3mm L=5.5mm $\pm$ 0.5mm/1.2CU铜线*4PIN

(Specifications)

日期:

2025.10.1

DATE

制 造 Manufacture	
核 准 APPROVAL	制 作 PREPARED
王师	张优美

客 户 承 认 栏 CUSTOMER APPROVED		
核 准 APPROVED	确 认 CHECKED	经 办 DESIGNED

广东科尼盛电子科技有限公司

KNSCHA ELECTRONICS CO.,LIMITED

地址: 广东省东莞市东坑镇汇金展拓科技园 A2-A3栋


Buildings A2-A3, Huijin Zhantuo Science and Technology Park,
Dongkeng Town, Dongguan City, Guangdong Province

TEL:0769-83698067 81035570 FAX: 0769-83861559

Email: sales@knscha.com Website: <http://www.knscha.com>



capacitor	物料编码	228CB0081
<u>main data</u>		
额定容量 C _n Rated Capacitance	[μF]	40
容量偏差 Capacitance tolerance	[%]	±10
额定电压 U _n Rated Voltage	[Vdc]	600
损耗 tg δ Tangent of loss angle		≤20x10 ⁻⁴ (1KHz, 20℃)
最大电流 I _{max} Maximum current	[A]	28.99
等效串联电阻 ESR	mΩ	≤3.1 (1kHz)
最大峰值电流 $\hat{I}$ Maximum peak current $\hat{I}$	[A]	1200
电压变化率 dv/dt	v/ μs	30
预期寿命		100000h @U _n , θ _{amb} ≤70℃
极间测试 U _{test} Test voltage terminal to terminal	[Vdc]	900 - 10s
绝缘电阻 IR×CN Insulation Resistance		≥100000s (20℃ , 100VDC, 60s)
运行温度 θ _{amb} Operating Temperature	[℃]	-40 / +85
线径 D	[mm]	4-Φ1.2
长度 L	[mm]	42
宽度 W	[mm]	30
高度 H	[mm]	45
中心距 P	[mm]	37.5
中心距 D	[mm]	20.3
绝缘介质 insulation medium		聚丙烯薄膜Polypropylene film
填充介质 Filling medium		环氧树脂 epoxy



remark	designer	Revision Description				Changed by	change date
Design	xia.zhang	2025.10.01	Outline drawing	proportion	1: 1	edition	A
auditing standard				KNSCHA 40μF±10%600VDC MPD			
approved							
KNSCHA ELECTRONICSCO., LIMITED							